

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

AJ

16

P

LTR

DESCRIPTION

DATE

DWN

APVD


D

REV PER 0U20-0410-00

13SEP00


MO

KW



RECOMMENDED STRIP LENGTHS

- 1 CRIMP CONTACT USING MIL HAND TOOL M22520/2-01 WITH DANIELS POSITIONER K1041, SET AT POSITION NUMBER 4.
- 2 CRIMP CABLE BRAID USING MIL HAND TOOL M22520/5-02 WITH DANIELS DIE SET HX4-1607 (.128 INCH HEX) OR USE AMP PRO-CRIMPER II WITH DIE SET NUMBER 58489-1.
- 3 CRIMP CABLE BRAID USING MIL HAND TOOL M22520/5-01 WITH DANIELS DIE SET Y138 (.151 INCH HEX) OR USE AMP PRO-CRIMPER II WITH DIE SET NUMBER 58425-3.
- 4 SEE DRAWING 414948-1 FOR INFORMATION SPECIFIC TO THIS PART NUMBER.



3	1	RD-188, & -316	1-413889-4	414187-2	414960-1	414948-3
2	1	RG-179, & -187/U	1-413889-3	414187-4	414960-1	414948-2
4	-	-	-	-	-	414948-1
BRAID CRIMP	CONTACT CRIMP	CABLE	3 FERRULE QTY=1	2 CONTACT QTY=1	1 JACK ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN B. MOYER 090CT96

CHK J. CABARLO 100CT96

APVD J. CABARLO 100CT96

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMPAMP Incorporated
Harrisburg, PA 17105-3608NAME
CABLE JACK, STRAIGHT,
50 OHM, SMBSIZE
A3

CAGE CODE

00779

DRAWING NO

C-414948

SCALE 8:1

SHEET 1 OF 1

REV D