

**RoHS Compliant
Pb - Lead Free**

Ltr	Revisions	Date	Appr

Electrical Specifications:

Frequency Range		12.000 to 52.000	MHz
Mode of Oscillation	Fundamental	12.000 to 52.000	MHZ
Frequency Tolerance at 25°C	Standard	±30	PPM Max (Note 1)
	Optional	±25	
		±20	
		±15	
		±10	
Frequency Stability over Temperature Range	Standard	±50	PPM Max (Note 1)
	Optional	±30	
		±25	
		±20	
		±15	
Operating Temperature Range	Standard	-10 to +70	° C
	Extended	-40 to +85	
Storage Temperature Range		-55 to +125	
Aging		±3	PPM Max/Year
Load Capacitance		7 to 32 and Series Resonance	pF
Shunt Capacitance		5.0	
Equivalent Series Resistance (ESR)		See ESR Table	Ohm
Drive Level		100	uW Max
Insulation Resistance		500 at 100 Vdc ± 15 Vdc	M Ohm

Frequency Range and ESR Values:

Frequency Range in MHz	ESR Ohm Max	Mode of Operation
12.000 to 29.900	100	Fundamental
30.000 to 52.000	50	Fundamental



11-3 Chien-Kuo Rd T.E.P.Z. 4027 Taiwan, ROC

All dimensions are millimeters.

CAD: TCR

Review: EG

Appr: JL


Page: 1/4 Date: June 10, 2006

Specification Title:

**Microprocessor Crystal Unit
Low Profile
2.5 x 3.2 millimeter Surface Mount
General Product Specification**

Part Number: **C3E Series**

Mechanical Outline:



Package is Seam Sealed Ceramic-Metal.
Dimensions are millimeters.

1.5 Dia



The graph illustrates the temperature profile for a reflow soldering process. The Y-axis represents Temperature in degrees Celsius (°C), with marked values at 150°C, 230°C, and 260°C. The X-axis represents Time in seconds. The profile consists of a pre-heat phase, a reflow phase, and a cooling phase. The pre-heat phase is defined by a dwell time of 120 ± 20 seconds at 150°C. The reflow phase is defined by a dwell time of 50 ± 20 seconds at the peak temperature of 260°C. The cooling phase is labeled 'Cooling'.

Phase	Temperature (°C)	Duration (seconds)
Pre-heat	150	120 ± 20
Reflow	260	50 ± 20
Cooling	260 to 150	-

How to build a Part Number:

Series		C	Parameter
Package		3E	3.2 x 2.5 mm
		-	
Frequency		12.000 to 52.000	MHz
		-	
Load Capacitance		7	7 pF
		10	10 pF
		12	12 pF
		16	16 pF
		18	18 pF
		20	20 pF
		32	32 pF
		S	Series
		-	
Frequency Tolerance (Note 1)	Standard	30	±30 PPM
	Option	25	±25 PPM
		20	±20 PPM
		15	± 15 PPM
		10	±10 PPM
Frequency Stability (Note 1)	Standard	50	±50 PPM
	Option	30	±30 PPM
		25	±25 PPM
		20	±20 PPM
		15	±15 PPM
		10	±10 PPM
		-	
Temperature Range	Standard	See Notes	-10 to +70 °C
	Extended	X	-40 to +85 °C
		-	
Packaging		R	Tape and Reel

Part Number Example:

C3E-32.768-18-3050-X-R

C3E- 2.5 x 3.2 mm SMD Seam Seal Crystal Unit

32.768 MHz Nominal Frequency

18 pF Load Capacitance

3050: ±30 PPM Frequency Tolerance and ±50 PPM Frequency Stability

Fundamental Mode

X: -40 to +85° C Temperature Range

R: Tape and Reel Packaging

Notes:

- 1- Frequency Tolerance and Stability options are limited due to physical size.
- 2- Standard Temperature Range does not need to be included in Part Number description.
- 3- Product is shipped in Tape and Reel configuration. Each reel contains 3000 pieces.
- 4- Quantities less than 3000 are shipped bulk in ESD pouches.
- 5- Specification subject to change without notice.