


- Designed for Complementary Use with TIP100, TIP101 and TIP102
- 80 W at 25°C Case Temperature
- 8 A Continuous Collector Current
- Maximum $V_{CE(sat)}$ of 2.5 V at $I_C = 8$ A

TO-220 PACKAGE
(TOP VIEW)



This series is obsolete and not recommended for new designs.

Pin 2 is in electrical contact with the mounting base.

MDTRACA

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING		SYMBOL	VALUE	UNIT
Collector-base voltage ($I_E = 0$)	TIP105	V_{CBO}	-60	V
	TIP106		-80	
	TIP107		-100	
Collector-emitter voltage ($I_B = 0$)	TIP105	V_{CEO}	-60	V
	TIP106		-80	
	TIP107		-100	
Emitter-base voltage		V_{EBO}	-5	V
Continuous collector current		I_C	-8	A
Peak collector current (see Note 1)		I_{CM}	-15	A
Continuous base current		I_B	-1	A
Continuous device dissipation at (or below) 25°C case temperature (see Note 2)		P_{tot}	80	W
Continuous device dissipation at (or below) 25°C free air temperature (see Note 3)		P_{tot}	2	W
Unclamped inductive load energy (see Note 4)		$\frac{1}{2}LI_C^2$	10	mJ
Operating junction temperature range		T_j	-65 to +150	°C
Storage temperature range		T_{stg}	-65 to +150	°C
Lead temperature 3.2 mm from case for 10 seconds		T_L	260	°C

NOTES: 1. This value applies for $t_p \leq 0.3$ ms, duty cycle $\leq 10\%$.
2. Derate linearly to 150°C case temperature at the rate of 0.64 W/°C.
3. Derate linearly to 150°C free air temperature at the rate of 16 mW/°C.
4. This rating is based on the capability of the transistor to operate safely in a circuit of: $L = 20$ mH, $I_{B(on)} = -5$ mA, $R_{BE} = 100 \Omega$, $V_{BE(off)} = 0$, $R_S = 0.1 \Omega$, $V_{CC} = -20$ V.

PRODUCT INFORMATION

electrical characteristics at 25°C case temperature

PARAMETER	TEST CONDITIONS			MIN	TYP	MAX	UNIT
$V_{(BR)CEO}$ Collector-emitter breakdown voltage	$I_C = -30 \text{ mA}$ (see Note 5)	$I_B = 0$	TIP105 TIP106 TIP107	-60 -80 -100			V
I_{CEO} Collector-emitter cut-off current	$V_{CE} = -30 \text{ V}$ $V_{CE} = -40 \text{ V}$ $V_{CE} = -50 \text{ V}$	$I_B = 0$ $I_B = 0$ $I_B = 0$	TIP105 TIP106 TIP107			-50 -50 -50	μA
I_{CBO} Collector cut-off current	$V_{CB} = -60 \text{ V}$ $V_{CB} = -80 \text{ V}$ $V_{CB} = -100 \text{ V}$	$I_E = 0$ $I_E = 0$ $I_E = 0$	TIP105 TIP106 TIP107			-50 -50 -50	μA
I_{EBO} Emitter cut-off current	$V_{EB} = -5 \text{ V}$	$I_C = 0$				-8	mA
h_{FE} Forward current transfer ratio	$V_{CE} = -4 \text{ V}$ $V_{CE} = -4 \text{ V}$	$I_C = -3 \text{ A}$ $I_C = -8 \text{ A}$	(see Notes 5 and 6)	1000 200		20000	
$V_{CE(sat)}$ Collector-emitter saturation voltage	$I_B = -6 \text{ mA}$ $I_B = -80 \text{ mA}$	$I_C = -3 \text{ A}$ $I_C = -8 \text{ A}$	(see Notes 5 and 6)			-2 -2.5	V
V_{BE} Base-emitter voltage	$V_{CE} = -4 \text{ V}$	$I_C = -8 \text{ A}$	(see Notes 5 and 6)			-2.8	V
V_{EC} Parallel diode forward voltage	$I_E = -8 \text{ A}$	$I_B = 0$	(see Notes 5 and 6)			-3.5	V

NOTES: 5. These parameters must be measured using pulse techniques, $t_p = 300 \mu\text{s}$, duty cycle $\leq 2\%$.

6. These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

thermal characteristics

PARAMETER	MIN	TYP	MAX	UNIT
$R_{\theta JC}$ Junction to case thermal resistance			1.56	$^{\circ}\text{C}/\text{W}$
$R_{\theta JA}$ Junction to free air thermal resistance			62.5	$^{\circ}\text{C}/\text{W}$
$C_{\theta C}$ Thermal capacitance of case		0.9		$\text{J}/^{\circ}\text{C}$

resistive-load-switching characteristics at 25°C case temperature

PARAMETER	TEST CONDITIONS [†]			MIN	TYP	MAX	UNIT
t_d Delay time	$I_C = -8 \text{ A}$ $V_{BE(off)} = 5 \text{ V}$	$I_{B(on)} = -80 \text{ mA}$ $R_L = 5 \Omega$	$I_{B(off)} = 80 \text{ mA}$ $t_p = 20 \mu\text{s}$, dc $\leq 2\%$		35		ns
t_r Rise time					300		ns
t_s Storage time					900		ns
t_f Fall time					1.3		μs

[†] Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.

TYPICAL CHARACTERISTICS




Figure 1.




Figure 2.




Figure 3.

PRODUCT INFORMATION

AUGUST 1978 - REVISED SEPTEMBER 2002
Specifications are subject to change without notice.

MAXIMUM SAFE OPERATING REGIONS




Figure 4.

THERMAL INFORMATION




Figure 5.

PRODUCT INFORMATION

AUGUST 1978 - REVISED SEPTEMBER 2002
Specifications are subject to change without notice.