








© COPYRIGHT 1978 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION		
		H		REV PER 0G3C-0026-05	24JAN05	DS



1. .010 MAX CUT-OFF TAB FOR LOOSE PIECE.
2. GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000015 GOLD ON CONTACT AREA.
3. GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT .000030 GOLD ON CONTACT AREA.
4. .000016 MIN. TIN.
5. LUBRICATED
6. POINT OF MEASUREMENT FOR PLATING THICKNESS.
7. .000015 GOLD ON CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
8. .000030 GOLD ON CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
9. OBSOLETE PART NUMBER.



REV	DATE	DESCRIPTION	PART NO
1	102106-5	102102-7	
2	102106-4	102102-6	
3	102106-3	102102-5	
4	102106-2	102102-2	
5	102106-1	102102-1	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.
TOLERANCES ON:
DECIMALS $\pm .005$
ANGLES $\pm$

MATERIAL
PHOS. BRONZE

FINISH
SEE TABLE

CONTRACT NO

DR
H. Bedin 4-12-78CHK
B. Wolfe 4-27-78APPD
J. Zimmerman 4/28/78APPD
B. Bennett 5/1/78

DSGN APPD

OTHER APPD

AMP INCORPORATED
Harrisburg, Pa.

NAME

CONTACT, MOD I, RECEPTACLE, CRIMP
SNAP-IN, HIGH PRESSURE,
#22 - #26 AWG, SIDE FEED

SIZE

CODE IDENT NO
00779

DRAWING NO

102102

SCALE

SHEET