

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:22-28-6361

Status:Active

Overview:KK® Interconnect System - Molex

Description:KK® 254 Breakaway Header, Right-Angle, 36 Circuits, Tin (Sn) Plating, Mating Pin Length 10.29mm (.405")



Series

image - Reference only

Documents:

- 3D Model
- Drawing (PDF)
- Product Specification PS-10-07 (PDF)
- RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Application Tooling Part Link

Overview

Product Name

UPC

PCB Headers

42376

Board-to-Board, Signal, Wire-to-Board

11-20-1230

KK® Interconnect System - Molex

KK® 254

800754239974

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Compliant

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Yes

36

36

Black

25

94V-0

No

Brass

Tin

Tin

High Temperature Thermoplastic

3.168/g

1

Right Angle

3.05mm

No

None

1.60mm

Bag

2.54mm

2.540µm

2.540µm

No

No

No

No

No

No

See Product Specification

Through Hole

Electrical

Current - Maximum per Contact

4A

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

42376Series

Mates With

KK® Crimp Housing [2695](#) , [6471](#) , [7880](#) ,
KK® PC Board Connector [4455](#)

Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235
Material Info	
Old Part Number	42376-0141
Reference - Drawing Numbers	
Product Specification	PS-10-07
Sales Drawing	SD-42376-001

This document was generated on 08/18/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[22-28-6361](#)