




DATE	ECO NO	DESCRIPTION	BY
Sep 27 1993	CDN 93024		A.K
Oct 4 1993	DCN 93025	Revise	A.K
Sep 5 1994		Revise	A.K






RECOMMENDED IC REF

Performance.

1. Insulation Resistance : 1000 M min. at 500V.D.C
2. Dielectric Withstanding Voltage : 600 V.A.C RMS
3. Contact Resistance : 30 m max. at 20mV max.
4. Temperature Range : -40℃ +150℃

④	CONTACT- 2	Be Cu	8	PLATING : Au
③	CONTACT- 1	Be Cu	8	PLATING : Au
②	BASE-16P	PEI	1	COLOR :BLACK
①	COVER-16P	PEI	1	COLOR :BLACK
P.NO	PART DESCRIPTION	MATERIAL	QTY	NOTE
GENERAL TOLERANCES		 WELLS JAPAN LIMITED ウエルズ・ジャパン株式会社		
±0.3 ±.012				
UNIT	SCALE	ANGLE	TITLE	
mm in.	—	3rd.		
DRAWN		/ /	SOP 16P SOCKET	
CHECKED		/ /		
APPROVED		/ /	DWG NO.	
			652B0162211	



FOOTPRINT
FOOTPRINT AS VIEWED LOOKING DOWN
FROM TOP OF SOCKET