




LOC		DIST		REVISIONS			
CM	00	P	LTR	DESCRIPTION		DATE	DWN
		P2	REVISED	PER	ECR-12-011660	24JAN13	KH

- 1 PARTS MUST COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- 2 CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN STRIPED WITH 0.00076 [.000030] GOLD IN CONTACT AREA INDICATED AND TIN-LEAD ON SOLDER TAIL END.
- 3 CCIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 4 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 5 SUPERSEDED BY 350764-5

PH BRZ GOLD 4	NYLON, NATURAL	350764-5
PH BRZ TIN	NYLON, NATURAL	350764-4
PH BRZ GOLD 2	NYLON, NATURAL	350764-3
CONTACT		HOUSING
CONTACT		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 11OCT2005	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK S. RIDGILL 11OCT2005		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. RIDGILL 11OCT2005	NAME	
0 PLC ±		PRODUCT SPEC	12 CIRCUIT UNIVERSAL MATE-N-LOK (TM) P.C. BOARD SOCKET HEADER ASSEMBLY	
1 PLC ±		APPLICATION SPEC		
2 PLC ±		—	SIZE	
3 PLC ± 0.13 [.005]		—	CAGE CODE	
4 PLC ±		—	DRAWING NO	
ANGLES ±		—	RESTRICTED TO	
FINISH		—	A1 00779 350764	
MATERIAL SEE TABLE		WEIGHT	CUSTOMER DRAWING	
SEE TABLE		SCALE	5:1	
		SHEET	1 OF 1	
		REV	P2	