



Wiha Torque VDE screwdrivers.

Precise and high repeat accuracy.



Wiha TorqueVario®-SVDE with integrated scale.

For controlled tightening of the screw while providing user safety for electrical applications we offer the TorqueVario®-SVDE with an integrated window scale in combination with Wiha Torque VDE interchangeable blades. All VDE handles and blades are individually tested and provide safety up to 1000 V AC/ 1500 V DC. The Torque Vario®-SVDE series has three models covering torque ranges from 0.6 Nm up to 8.0 Nm.



slimTECHNOLOGY:
Up to 33% reduction of the blade diameter in the critical working area allows effortless access to low-lying fastening/ spring elements.



When working with VDE tools, observe the national safety and accident prevention regulations.



Wiha Torque VDE screwdrivers.

- Clearly audible and perceptible click on attaining the pre-set torque
- Torque accuracy $\pm 6\%$ of the pre-set scale value
- Delivered with factory calibration certificate
- Each tool is individually tested and marked with an identification number
- Safety when working with live equipment up to 1000 V AC and 1500 V DC
- Each screwdriver is individually tested in a water bath at 10.000 Volts according to IEC 60900:2004
- Compact and particularly low weight design
- Ergonomic handle sizes that are proportional to the torque ranges
- Fulfills all accuracy requirements as defined by EN ISO 6789, BS EN 26789 and ASME B 107.14M

TorqueVario®-S VDE. Torque VDE interchangeable blades.



2872 TorqueVario®-S VDE torque screwdriver.
Insulation up to 1000 V AC, GS-mark.
Torque value can be set via window scale.
Automatic release.

Handle: Torque infinitely adjustable with Torque-Setter setting tool (also supplied). Ergonomic multi-component handle, insulation up to 1000 V AC, GS mark. Handle sizes proportioned to optimise torque setting. Audible and perceptible click when the pre-set torque has been attained.

Standards: Manufactured acc. to IEC 60900:2004. EN ISO 6798, BS EN 26789, ASME B107.14M.

Accuracy: $\pm 6\%$, traceable to national standards.

Application: For electrical applications up to 1000 V AC where recommended torque settings are important. Use in combination with a Wiha torque VDE interchangeable blade.

Extra: Delivered in practical plastic box, incl. factory calibration certificate.

Order-No.	Nm	Ø	↔	↔	max. Nm	↔
26625 7	0.6-2.0	3.8	131	30		1
26626 4	1.0-5.0	3.8	138	36		1
26627 1	2.0-8.0	3.8	142	41		1



285-900 Torque-Setter.
Setting tool for variable torque screwdrivers.
Included in every torque screwdriver delivery.

Blade: Octagonal blade, through hardened, zinc-plated.

Handle: Cellulose acetate with micro-fine surface structure.

Order-No.	↔	↔	↔
26864 0	80	150	1



2879 Torque VDE TORX® interchangeable blade.
Insulation up to 1000 V AC, GS-mark.
Exclusively for Wiha VDE torque screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish. Insulation moulded directly onto blade.

Standards: Manufactured acc. to IEC 60900:2004, each tool individually tested at 10 000 volts.

Application: For controlled fastening on live parts up to 1000 V AC.

Order-No.						
27956 1	T8	3.8	220	65	1.3	5
27957 8	T9	3.8	220	65	2.5	5
27958 5	T10	3.8	220	65	3.8	5
27959 2	T15	3.8	220	65	5.5	5
27960 8	T20	3.8	220	65	8.0	5
27961 5	T25	3.8	220	65	8.0	5

Products on this page are VDE-tested

Torque VDE interchangeable blades.



2879 Torque VDE slotted interchangeable blade.
Insulation up to 1000 V AC, GS-mark.
Exclusively for Wiha VDE torque screwdrivers.

Standards: Tip DIN ISO 2380.

Order-No.						max. Nm	
26687 5	0.5	3.0	3.8	220	65	0.6	5
26688 2	0.6	3.5	3.8	220	65	1.1	5
26689 9	0.8	4.0	3.8	220	65	2.5	5
26690 5	1.0	5.5	3.8	220	65	3.8	5



NEW
2879 Torque VDE Xeno interchangeable blade for terminal screws (slotted/ Phillips).
Insulation up to 1000 V AC, GS-mark.
Exclusively for Wiha VDE torque screwdrivers.

Order-No.					max. Nm	
33585 4	SL/PH1	3.8	220	65	3.8	5
33571 7	SL/PH2	3.8	220	65	5.5 slim version	5



NEW
2879 Torque VDE Xeno interchangeable blade for terminal screws (slotted/ Pozidriv).
Insulation up to 1000 V AC, GS-mark.
Exclusively for Wiha VDE torque screwdrivers.

Order-No.					max. Nm	
33572 4	SL/PZ1	3.8	220	65	3.8	5
33586 1	SL/PZ2	3.8	220	65	5.5 slim version	5



NEW
2879 Torque VDE Phillips interchangeable blade.
Insulation up to 1000 V AC, GS-mark.
Exclusively for Wiha VDE torque screwdrivers.

Standards: Tip DIN ISO 8764.

Order-No.					max. Nm	
26691 2	PH0	3.8	220	65	0.9	5
26692 9	PH1	3.8	220	65	3.8	5
26693 6	PH2	3.8	220	65	5.5 slim version	5



NEW
2879 Torque VDE Pozidriv interchangeable blade.
Insulation up to 1000 V AC, GS-mark.
Exclusively for Wiha VDE torque screwdrivers.

Standards: Tip DIN ISO 8764.

Order-No.					max. Nm	
26694 3	PZ0	3.8	220	65	0.9	5
26695 0	PZ1	3.8	220	65	3.8	5
26696 7	PZ2	3.8	220	65	5.5 slim version	5