

A fully screened robust range of DIN connectors for use in instrumentation and audio applications. Available in two finishes; bright nickel and non-reflective electrically conductive matt black. Robust construction incorporating cable grip and strain relief.

Manufactured to DIN 41524, 45322, 45326, 45327 and 45329.

MATERIALS
HOUSING

: Zinc Alloy

Sprayed with matt black
Conductive paint

MOULDING
CONTACTS

: Nylon
: Brass

CABLE CLAMP

: Silver Plated
: Mild Steel
zinc plated

GROMMET

: Black P.V.C.

ELECTRICAL RATINGS

Working Voltage

100 Vd.c. or a.c. peak

Test Voltage

1000 Vd.c.

Insulation Resist.

$10^{11} \Omega$ min at 100 Vd.c.

Current Rating

4 A

Contact Resist.

10 m Ω max


Capacity (mated)

3 pF

Temp. Range

-25°C to +70°C

Dimensions



Type	Deltron No
3 Way	611-0300
4 Way	611-0400
4 Way Switched	611-0410
5 Way 45°	611-0500
5 Way 60°	611-0510
5 Way Dice	611-0520
6 Way	611-0600
7 Way	611-0700
8 Way	611-0800

CONVERTED FROM PS0487 ISS3 (08.07.96) IN JAN 2003

DrgnNo 611 SERIES TITLE SCREENED DIN CONNECTOR STANDARD PLUG (BLACK)

ALL DIMENSIONS IN MM
ANGLES IN DECIMAL DEGREES



DELTRON Components

ISS

3

GENERAL SPECIFICATION
FOR 611 SERIES

CUSTOMER

Aprvd Date 10/02/03

Aprvd By MC

Drwn by BFS

Scale: NTS

Sheet 1 / 1