


## Surface Mount Schottky Barrier Rectifier

### FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guardring for overvoltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



### MECHANICAL DATA

**Case:** DO-214AC (SMA)

Molding compound, UL flammability classification rating 94V-0

Base P/N with suffix "G" on packing code - halogen-free

Base P/N with prefix "H" on packing code - AEC-Q101 qualified

**Terminal:** Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 1A whisker test

with prefix "H" on packing code meet JESD 201 class 2 whisker test

**Polarity:** Indicated by cathode band

**Weight:** 0.07 g (approximately)

**DO-214AC (SMA)**

| MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T <sub>A</sub> =25℃ unless otherwise noted)                 |                    |              |           |           |           |           |              |            |            |      |    |
|-------------------------------------------------------------------------------------------------------------|--------------------|--------------|-----------|-----------|-----------|-----------|--------------|------------|------------|------|----|
| PARAMETER                                                                                                   | SYMBOL             | SK<br>22A    | SK<br>23A | SK<br>24A | SK<br>25A | SK<br>26A | SK<br>29A    | SK<br>210A | SK<br>215A | Unit |    |
| Maximum repetitive peak reverse voltage                                                                     | V <sub>RRM</sub>   | 20           | 30        | 40        | 50        | 60        | 90           | 100        | 150        | V    |    |
| Maximum RMS voltage                                                                                         | V <sub>RMS</sub>   | 14           | 21        | 28        | 35        | 42        | 63           | 70         | 105        | V    |    |
| Maximum DC blocking voltage                                                                                 | V <sub>DC</sub>    | 20           | 30        | 40        | 50        | 60        | 90           | 100        | 150        | V    |    |
| Maximum average forward rectified current                                                                   | I <sub>F(AV)</sub> | 2            |           |           |           |           |              |            |            | A    |    |
| Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load                         | I <sub>FSM</sub>   | 50           |           |           |           |           |              |            |            | A    |    |
| Maximum instantaneous forward voltage (Note 1)<br>@ 2 A                                                     | V <sub>F</sub>     | 0.50         |           |           | 0.70      |           | 0.85         |            | 0.95       | V    |    |
| Maximum reverse current @ rated VR    T <sub>J</sub> =25 ℃<br>T <sub>J</sub> =100℃<br>T <sub>J</sub> =125 ℃ | I <sub>R</sub>     | 0.5          |           |           |           |           | 0.1          |            |            | mA   |    |
|                                                                                                             |                    | 10           |           |           | 5         |           | -            |            |            |      |    |
|                                                                                                             |                    | -            |           |           |           |           | 2.0          |            |            |      |    |
| Voltage Rate of Change (Rated V <sub>R</sub> )                                                              | dV/dt              | 10000        |           |           |           |           |              |            |            | V/μs |    |
| Non-repetitive peak reverse avalanche energy L=40mH Ta=25℃ max prior to surge, Inductive load switched off  | E <sub>RSM</sub>   | 20           |           |           |           |           |              |            |            | mJ   |    |
| Typical thermal resistance                                                                                  | R <sub>θJA</sub>   | 88           |           |           |           |           |              |            |            | °C/W |    |
| Operating junction temperature range                                                                        | T <sub>J</sub>     | - 55 to +125 |           |           |           |           | - 55 to +150 |            |            |      | °C |
| Storage temperature range                                                                                   | T <sub>STG</sub>   | - 55 to +150 |           |           |           |           |              |            |            | °C   |    |

Note 1: Pulse test with PW=300μs, 1% duty cycle

| ORDERING INFORMATION |                    |              |                     |            |                          |
|----------------------|--------------------|--------------|---------------------|------------|--------------------------|
| PART NO.             | AEC-Q101 QUALIFIED | PACKING CODE | GREEN COMPOUND CODE | PACKAGE    | PACKING                  |
| SK2xxA<br>(Note 1)   | Prefix "H"         | R3           | Suffix "G"          | SMA        | 1,800 / 7" Plastic reel  |
|                      |                    | R2           |                     | SMA        | 7,500 / 13" Paper reel   |
|                      |                    | M2           |                     | SMA        | 7,500 / 13" Plastic reel |
|                      |                    | F3           |                     | Folded SMA | 1,800 / 7" Plastic reel  |
|                      |                    | F2           |                     | Folded SMA | 7,500 / 13" Paper reel   |
|                      |                    | F4           |                     | Folded SMA | 7,500 / 13" Plastic reel |
|                      | N/A                | E3           |                     | Clip SMA   | 1,800 / 7" Plastic reel  |
|                      |                    | E2           |                     | Clip SMA   | 7,500 / 13" Paper reel   |
|                      |                    |              |                     |            |                          |

Note 1: "xx" defines voltage from 20V (SK22A) to 150V (SK215A)

| EXAMPLE       |          |                    |              |                     |                    |
|---------------|----------|--------------------|--------------|---------------------|--------------------|
| PREFERRED P/N | PART NO. | AEC-Q101 QUALIFIED | PACKING CODE | GREEN COMPOUND CODE | DESCRIPTION        |
| SK26A R3      | SK26A    |                    | R3           |                     |                    |
| SK26A R3G     | SK26A    |                    | R3           | G                   | Green compound     |
| SK26AHR3      | SK26A    | H                  | R3           |                     | AEC-Q101 qualified |

## RATINGS AND CHARACTERISTICS CURVES

(TA=25°C unless otherwise noted)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG. 2- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3- TYPICAL FORWARD CHARACTERISTICS




Fig. 4- TYPICAL REVERSE CHARACTERISTICS




FIG. 5- TYPICAL JUNCTION CAPACITANCE






FIG. 6- TYPICAL TRANSIENT THERMAL CHARACTERISTICS




## PACKAGE OUTLINE DIMENSIONS



| DIM. | Unit (mm) |      | Unit (inch) |       |
|------|-----------|------|-------------|-------|
|      | Min       | Max  | Min         | Max   |
| A    | 1.27      | 1.58 | 0.050       | 0.062 |
| B    | 4.06      | 4.60 | 0.160       | 0.181 |
| C    | 2.29      | 2.83 | 0.090       | 0.111 |
| D    | 1.99      | 2.50 | 0.078       | 0.098 |
| E    | 0.90      | 1.41 | 0.035       | 0.056 |
| F    | 4.95      | 5.33 | 0.195       | 0.210 |
| G    | 0.10      | 0.20 | 0.004       | 0.008 |
| H    | 0.15      | 0.31 | 0.006       | 0.012 |

## SUGGESTED PAD LAYOUT



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| A      | 1.68      | 0.066       |
| B      | 1.52      | 0.060       |
| C      | 3.93      | 0.155       |
| D      | 2.41      | 0.095       |
| E      | 5.45      | 0.215       |

## MARKING DIAGRAM



P/N = Specific Device Code  
G = Green Compound  
YW = Date Code  
F = Factory Code