





| Applicable Wire<br>mm <sup>2</sup> (AWG#) | Stud Size<br>Metric | Part No.   | Nominal Size<br>DIN46234 | Dimensions mm (in.) |                 |              |             |               |                  |               | Tool No. | Qty/box |  |
|-------------------------------------------|---------------------|------------|--------------------------|---------------------|-----------------|--------------|-------------|---------------|------------------|---------------|----------|---------|--|
|                                           |                     |            |                          | ød <sub>2</sub>     | ød <sub>3</sub> | r            | ℓ           | a             | ø d <sub>1</sub> | s             |          |         |  |
| 0.1 to 0.5<br>(26 to 22)                  | 2                   | GS2-0.5    | 2-0.5                    | 2.2 (.087)          | 5.0 (.197)      | 5.0 (.197)   | 9.8 (.386)  | 4.0<br>(.157) | 1.0<br>(.039)    | 0.5<br>(.020) | —        | 2,000   |  |
|                                           | 2.5                 | GS2.5-0.5  | 2.5-0.5                  | 2.7 (.106)          | 5.0 (.197)      | 5.0 (.197)   | 9.8 (.386)  |               |                  |               |          |         |  |
|                                           | 3                   | GS3-0.5    | 3-0.5                    | 3.2 (.126)          | 5.0 (.197)      | 5.0 (.197)   | 9.8 (.386)  |               |                  |               |          |         |  |
|                                           | 3.5                 | GS3.5-0.5  | 3.5-0.5                  | 3.7 (.146)          | 6.0 (.236)      | 5.0 (.197)   | 12.0 (.472) |               |                  |               |          |         |  |
|                                           | 4                   | GS4-0.5    | 4-0.5                    | 4.3 (.169)          | 6.5 (.256)      | 6.0 (.236)   | 11.7 (.461) |               |                  |               |          |         |  |
|                                           | 5                   | GS5-0.5    | 5-0.5                    | 5.3 (.209)          | 8.0 (.315)      | 6.5 (.256)   | 11.0 (.433) |               |                  |               |          |         |  |
| 0.25 to 1.5<br>(22 to 16)                 | 2                   | GS2-1      |                          | 2.2 (.087)          | 6.0 (.236)      | 4.5 (.177)   | 11.0 (.433) | 5.0 (.197)    | 1.6<br>(.063)    | 0.8<br>(.031) | JCH-10   | 2,000   |  |
|                                           | 2.5                 | GS2.5-1    | 2.5-1                    | 2.7 (.106)          | 6.0 (.236)      | 4.5 (.177)   | 11.0 (.433) | 5.0 (.197)    |                  |               |          |         |  |
|                                           | 3                   | GS3-1      | 3-1                      | 3.2 (.126)          | 6.0 (.236)      | 4.5 (.177)   | 11.0 (.433) | 5.0 (.197)    |                  |               |          |         |  |
|                                           | 3                   | GS3L-1     |                          | 3.2 (.126)          | 6.5 (.256)      | 3.5 (.138)   | 8.0 (.315)  | 4.0 (.157)    |                  |               |          |         |  |
|                                           | 3.5                 | GS3.5-1    | 3.5-1                    | 3.7 (.146)          | 6.0 (.236)      | 4.5 (.177)   | 11.0 (.433) | 5.0 (.197)    |                  |               |          |         |  |
|                                           | 3.5                 | GS3.5L-1   |                          | 3.7 (.146)          | 6.5 (.256)      | 3.5 (.138)   | 8.0 (.315)  | 4.0 (.157)    |                  |               |          |         |  |
|                                           | 4                   | GS4S-1     |                          | 4.3 (.169)          | 6.5 (.256)      | 3.5 (.138)   | 8.0 (.315)  | 4.0 (.157)    |                  |               |          |         |  |
|                                           | 4                   | GS4M-1     |                          | 4.3 (.169)          | 7.0 (.276)      | 5.5 (.217)   | 11.0 (.433) | 5.0 (.197)    |                  |               |          |         |  |
|                                           | 4                   | GS4-1      | 4-1                      | 4.3 (.169)          | 8.0 (.315)      | 6.0 (.236)   | 12.0 (.472) | 5.0 (.197)    |                  |               |          |         |  |
|                                           | 5                   | GS5S-1     |                          | 5.3 (.209)          | 8.0 (.315)      | 6.0 (.236)   | 12.0 (.472) | 5.0 (.197)    |                  |               |          |         |  |
|                                           | 5                   | GS5-1      | 5-1                      | 5.3 (.209)          | 10.0 (.394)     | 6.5 (.256)   | 13.0 (.512) | 5.0 (.197)    |                  |               |          |         |  |
|                                           | 6                   | GS6S-1     |                          | 6.5 (.256)          | 10.0 (.394)     | 6.5 (.256)   | 13.0 (.512) | 5.0 (.197)    |                  |               |          |         |  |
|                                           | 6                   | GS6-1      |                          | 6.5 (.256)          | 12.0 (.472)     | 10.0 (.394)  | 17.0 (.669) | 5.0 (.197)    |                  |               |          |         |  |
| 8                                         | GS8-1               |            | 8.4 (.331)               | 12.0 (.472)         | 10.0 (.394)     | 17.0 (.669)  | 5.0 (.197)  | 1,000         |                  |               |          |         |  |
| >1 to 2.5<br>(16 to 14)                   | 3                   | GS3-2.5    | 3-2.5                    | 3.2 (.126)          | 6.0 (.236)      | 4.5 (.177)   | 11.0 (.433) | 5.0<br>(.197) | 2.3<br>(.091)    | 0.8<br>(.031) | JCH-10   | 2,000   |  |
|                                           | 3.5                 | GS3.5-2.5  | 3.5-2.5                  | 3.7 (.146)          | 6.0 (.236)      | 4.5 (.177)   | 11.0 (.433) |               |                  |               |          |         |  |
|                                           | 3.5                 | GS3.5L-2.5 |                          | 3.7 (.146)          | 6.8 (.268)      | 4.5 (.177)   | 11.0 (.433) |               |                  |               |          |         |  |
|                                           | 4                   | GS4S-2.5   |                          | 4.3 (.169)          | 6.8 (.268)      | 4.5 (.177)   | 11.0 (.433) |               |                  |               |          |         |  |
|                                           | 4                   | GS4-2.5    | 4-2.5                    | 4.3 (.169)          | 8.0 (.315)      | 6.0 (.236)   | 12.0 (.472) |               |                  |               |          |         |  |
|                                           | 5                   | GS5S-2.5   |                          | 5.3 (.209)          | 8.0 (.315)      | 6.0 (.236)   | 12.0 (.472) |               |                  |               |          |         |  |
|                                           | 5                   | GS5-2.5    | 5-2.5                    | 5.3 (.209)          | 10.0 (.394)     | 6.5 (.256)   | 14.0 (.551) | 4.8 (.189)    |                  |               |          |         |  |
|                                           | 5                   | GS5M-2.5   |                          | 5.3 (.209)          | 9.5 (.374)      | 6.5 (.256)   | 12.0 (.472) |               |                  |               |          |         |  |
|                                           | 6                   | GS6S-2.5   |                          | 6.5 (.256)          | 10.0 (.394)     | 6.5 (.256)   | 14.0 (.551) |               |                  |               |          |         |  |
|                                           | 6                   | GS6-2.5    | 6-2.5                    | 6.5 (.256)          | 11.0 (.433)     | 7.5 (.295)   | 16.0 (.630) |               |                  |               |          |         |  |
|                                           | 8                   | GS8-2.5    | 8-2.5                    | 8.4 (.331)          | 14.0 (.551)     | 10.0 (.394)  | 17.0 (.669) |               |                  |               |          |         |  |
|                                           | 10                  | GS10-2.5   |                          | 10.5 (.413)         | 18.0 (.709)     | 12.0 (.472)  | 20.0 (.787) |               |                  |               |          |         |  |
|                                           | 12                  | GS12-2.5   |                          | 13.0 (.512)         | 18.0 (.709)     | 12.0 (.472)  | 20.0 (.787) |               |                  |               |          |         |  |
| 16                                        | GS16-2.5            |            | 17.0 (.669)              | 27.0 (1.063)        | 16.0 (.630)     | 26.0 (1.024) | 4.8 (.189)  | 500           |                  |               |          |         |  |
| >2.5 to 6<br>(12 to 10)                   | 4                   | GS4-6      | 4-6                      | 4.3 (.169)          | 8.0 (.315)      | 6.0 (.236)   | 14.0 (.551) | 6.0<br>(.236) | 3.6<br>(.142)    | 1.0<br>(.039) | JCH-10   | 1,000   |  |
|                                           | 5                   | GS5-6      | 5-6                      | 5.3 (.209)          | 10.0 (.394)     | 6.5 (.256)   | 15.0 (.591) |               |                  |               |          |         |  |
|                                           | 6                   | GS6-6      | 6-6                      | 6.5 (.256)          | 11.0 (.433)     | 7.5 (.295)   | 16.0 (.630) |               |                  |               |          |         |  |
|                                           | 8                   | GS8-6      | 8-6                      | 8.4 (.331)          | 14.0 (.551)     | 10.0 (.394)  | 19.0 (.748) |               |                  |               |          |         |  |
|                                           | 10                  | GS10-6     | 10-6                     | 10.5 (.413)         | 18.0 (.709)     | 12.0 (.472)  | 21.0 (.827) |               |                  |               |          |         |  |
|                                           | 12                  | GS12-6     |                          | 13.0 (.512)         | 18.0 (.709)     | 12.0 (.472)  | 21.0 (.827) |               |                  |               |          |         |  |

Note:1) Contact J.S.T. Europe N.V., Belgium for the above tools.


2) Delivery lead times may vary depending on the product. Contact JST for details.



| Applicable Wire<br>mm² (AWG#) | Stud Size<br>Metric | Part No. | Nominal Size<br>DIN46234 | Dimensions mm (in.) |              |             |              |                |                |               | Tool No.                                 | Qty/box      |
|-------------------------------|---------------------|----------|--------------------------|---------------------|--------------|-------------|--------------|----------------|----------------|---------------|------------------------------------------|--------------|
|                               |                     |          |                          | ød₂                 | ød₃          | r           | ℓ            | a              | ø d₁           | s             |                                          |              |
| >6 to 10<br>(8)               | 4                   | GS4-10   |                          | 4.3 (.169)          | 10.0 (.394)  | 6.5 (.256)  | 16.0 (.630)  | 8.0<br>(.315)  | 4.5<br>(.177)  | 1.1<br>(.043) | JCS-350<br>YH-540                        | 500          |
|                               | 5                   | GS5-10   | 5-10                     | 5.3 (.209)          | 10.0 (.394)  | 6.5 (.256)  | 16.0 (.630)  |                |                |               |                                          |              |
|                               | 6                   | GS6-10   | 6-10                     | 6.5 (.256)          | 11.0 (.433)  | 7.5 (.295)  | 17.0 (.669)  |                |                |               |                                          |              |
|                               | 8                   | GS8-10   | 8-10                     | 8.4 (.331)          | 14.0 (.551)  | 10.0 (.394) | 20.0 (.787)  |                |                |               |                                          |              |
|                               | 10                  | GS10-10  | 10-10                    | 10.5 (.413)         | 18.0 (.709)  | 12.0 (.472) | 21.0 (.827)  |                |                |               |                                          |              |
|                               | 12                  | GS12-10  | 12-10                    | 13.0 (.512)         | 22.0 (.866)  | 13.0 (.512) | 23.0 (.906)  |                |                |               |                                          | 250          |
| >10 to 16<br>(6)              | 5                   | GS5-16   | 5-16                     | 5.3 (.209)          | 11.0 (.433)  | 7.5 (.295)  | 20.0 (.787)  | 10.0<br>(.394) | 5.8<br>(.228)  | 1.2<br>(.047) | JCS-350<br>YH-540                        | 200          |
|                               | 6                   | GS6-16   | 6-16                     | 6.5 (.256)          | 11.0 (.433)  | 7.5 (.295)  | 20.0 (.787)  |                |                |               |                                          |              |
|                               | 8                   | GS8-16   | 8-16                     | 8.4 (.331)          | 14.0 (.551)  | 10.0 (.394) | 22.0 (.866)  |                |                |               |                                          |              |
|                               | 10                  | GS10-16  | 10-16                    | 10.5 (.413)         | 18.0 (.709)  | 12.0 (.472) | 24.0 (.945)  |                |                |               |                                          |              |
|                               |                     | 12       | GS12-16                  | 12-16               | 13.0 (.512)  | 22.0 (.866) | 13.0 (.512)  |                |                |               |                                          | 26.0 (1.024) |
| >16 to 25<br>(4)              | 5                   | GS5-25   | 5-25                     | 5.3 (.209)          | 12.0 (.472)  | 7.5 (.295)  | 25.0 (.984)  | 11.0<br>(.433) | 7.5<br>(.295)  | 1.5<br>(.059) | JCS-350<br>YH-540<br>JS-150D<br>JSHR-150 | 100          |
|                               | 6                   | GS6-25   | 6-25                     | 6.5 (.256)          | 12.0 (.472)  | 7.5 (.295)  | 25.0 (.984)  |                |                |               |                                          |              |
|                               | 6                   | GS6L-25  |                          | 6.5 (.256)          | 16.0 (.630)  | 10.0 (.394) | 25.0 (.984)  |                |                |               |                                          |              |
|                               | 8                   | GS8-25   | 8-25                     | 8.4 (.331)          | 16.0 (.630)  | 10.0 (.394) | 25.0 (.984)  |                |                |               |                                          |              |
|                               | 10                  | GS10-25  | 10-25                    | 10.5 (.413)         | 18.0 (.709)  | 12.0 (.472) | 26.0 (1.024) |                |                |               |                                          |              |
|                               | 12                  | GS12-25  | 12-25                    | 13.0 (.512)         | 22.0 (.866)  | 13.0 (.512) | 31.0 (1.220) |                |                |               |                                          |              |
|                               | 16                  | GS16-25  | 16-25                    | 17.0 (.669)         | 28.0 (1.102) | 16.0 (.630) | 35.0 (1.378) |                |                |               |                                          |              |
| >25 to 35<br>(2)              | 6                   | GS6-35   | 6-35                     | 6.5 (.256)          | 15.0 (.591)  | 10.0 (.394) | 26.0 (1.024) | 12.0<br>(.472) | 9.0<br>(.354)  | 1.6<br>(.063) | JCS-350<br>YH-540<br>JS-150D<br>JSHR-150 | 100          |
|                               | 8                   | GS8-35   | 8-35                     | 8.4 (.331)          | 16.0 (.630)  | 10.0 (.394) | 26.0 (1.024) |                |                |               |                                          |              |
|                               | 10                  | GS10-35  | 10-35                    | 10.5 (.413)         | 18.0 (.709)  | 12.0 (.472) | 27.0 (1.063) |                |                |               |                                          |              |
|                               | 12                  | GS12-35  | 12-35                    | 13.0 (.512)         | 22.0 (.866)  | 13.0 (.512) | 31.0 (1.220) |                |                |               |                                          |              |
|                               | 16                  | GS16-35  | 16-35                    | 17.0 (.669)         | 28.0 (1.102) | 16.0 (.630) | 36.0 (1.417) |                |                |               |                                          |              |
|                               | 16                  | GS16L-35 |                          | 17.0 (.669)         | 30.0 (1.181) | 18.0 (.709) | 37.5 (1.476) | 14.0<br>(.551) | 9.4<br>(.370)  | 1.8<br>(.071) |                                          |              |
|                               | 20                  | GS20-35  |                          | 21.0 (.827)         | 30.0 (1.181) | 18.0 (.709) | 37.5 (1.476) |                |                |               |                                          |              |
| >35 to 50<br>(1/0)            | 6                   | GS6-50   | 6-50                     | 6.5 (.256)          | 18.0 (.709)  | 12.0 (.472) | 34.0 (1.339) | 16.0<br>(.630) | 11.0<br>(.433) | 1.8<br>(.071) | YH-540D<br>JS-150D<br>JSHR-150           | 50           |
|                               | 8                   | GS8-50   | 8-50                     | 8.4 (.331)          | 18.0 (.709)  | 12.0 (.472) | 34.0 (1.339) |                |                |               |                                          |              |
|                               | 10                  | GS10-50  | 10-50                    | 10.5 (.413)         | 18.0 (.709)  | 12.0 (.472) | 34.0 (1.339) |                |                |               |                                          |              |
|                               | 12                  | GS12-50  | 12-50                    | 13.0 (.512)         | 22.0 (.866)  | 13.0 (.512) | 36.0 (1.417) |                |                |               |                                          |              |
|                               | 16                  | GS16-50  | 16-50                    | 17.0 (.669)         | 28.0 (1.102) | 16.0 (.630) | 40.0 (1.575) |                |                |               |                                          |              |
|                               | 20                  | GS20-50  |                          | 21.0 (.827)         | 32.0 (1.260) | 18.0 (.709) | 41.5 (1.634) | 18.0(.709)     | 11.4(.449)     | 2.0 (.079)    |                                          |              |
| >50 to 70<br>(2/0)            | 6                   | GS6-70   | 6-70                     | 6.5 (.256)          | 22.0 (.866)  | 13.0 (.512) | 38.0 (1.496) | 18.0<br>(.709) | 13.0<br>(.512) | 2.0<br>(.079) | YH-540<br>JS-150D<br>JSHR-150            | 50           |
|                               | 8                   | GS8-70   | 8-70                     | 8.4 (.331)          | 22.0 (.866)  | 13.0 (.512) | 38.0 (1.496) |                |                |               |                                          |              |
|                               | 10                  | GS10-70  | 10-70                    | 10.5 (.413)         | 22.0 (.866)  | 13.0 (.512) | 38.0 (1.496) |                |                |               |                                          |              |
|                               | 12                  | GS12-70  | 12-70                    | 13.0 (.512)         | 22.0 (.866)  | 13.0 (.512) | 38.0 (1.496) |                |                |               |                                          |              |
|                               | 16                  | GS16-70  | 16-70                    | 17.0 (.669)         | 28.0 (1.102) | 16.0 (.630) | 42.0 (1.654) |                |                |               |                                          |              |
|                               | 16                  | GS16L-70 |                          | 17.0 (.669)         | 32.0 (1.260) | 18.0 (.709) | 45.0 (1.772) | 19.0<br>(.748) | 13.3<br>(.524) |               |                                          |              |
|                               | 20                  | GS20-70  |                          | 21.0 (.827)         | 32.0 (1.260) | 18.0 (.709) | 45.0 (1.772) |                |                |               |                                          |              |

Note:1) Contact J.S.T. Europe N.V., Belgium for the above tools.

2) Delivery lead times may vary depending on the product. Contact JST for details.



| Applicable Wire<br>mm² (AWG#)  | Stud Size<br>Metric | Part No.  | Nominal Size<br>DIN46234 | Dimensions mm (in.) |                 |                |                 |                 |                 |                 | Tool No.                      | Qty/box |            |
|--------------------------------|---------------------|-----------|--------------------------|---------------------|-----------------|----------------|-----------------|-----------------|-----------------|-----------------|-------------------------------|---------|------------|
|                                |                     |           |                          | ød₂                 | ød₃             | r              | ℓ               | a               | ø d₁            | s               |                               |         |            |
| >70 to 95<br>(3/0)             | 8                   | GS8-95    | 8-95                     | 8.4 (.331)          | 24.0 (.945)     | 13.0 (.512)    | 42.0 (1.654)    | 20.0<br>(.787)  | 15.0(.591)      | 2.5 (.098)      | YH-540<br>JS-150D<br>JSHR-150 | 25      |            |
|                                | 10                  | GS10-95   | 10-95                    | 10.5 (.413)         | 24.0 (.945)     | 13.0 (.512)    | 42.0 (1.654)    |                 | 15.0(.591)      | 2.5 (.098)      |                               |         |            |
|                                | 10                  | GS10L-95  |                          | 10.5 (.413)         | 27.0 (1.063)    | 14.0 (.551)    | 40.7 (1.602)    |                 | 14.5(.571)      | 2.3 (.091)      |                               |         |            |
|                                | 12                  | GS12-95   | 12-95                    | 13.0 (.512)         | 24.0 (.945)     | 13.0 (.512)    | 42.0 (1.654)    |                 | 15.0(.591)      | 2.5 (.098)      |                               |         |            |
|                                | 12                  | GS12L-95  |                          | 13.0 (.512)         | 27.0 (1.063)    | 14.0 (.551)    | 40.7 (1.602)    |                 | 14.5(.571)      | 2.3 (.091)      |                               |         |            |
|                                | 16                  | GS16-95   | 16-95                    | 17.0 (.669)         | 28.0 (1.102)    | 16.0 (.630)    | 44.0 (1.732)    |                 | 15.0(.591)      | 2.5 (.098)      |                               |         |            |
|                                | 16                  | GS16LL-95 |                          | 17.0 (.669)         | 32.0 (1.260)    | 18.0 (.709)    | 52.0 (2.047)    |                 | 14.5(.571)      | 2.3 (.091)      |                               |         |            |
|                                | 20                  | GS20L-95  |                          | 21.0 (.827)         | 32.0 (1.260)    | 18.0 (.709)    | 52.0 (2.047)    |                 | 14.5(.571)      | 2.3 (.091)      |                               |         |            |
| >95 to 120<br>(4/0)            | 8                   | GS8-120   | 8-120                    | 8.4 (.331)          | 24.0 (.945)     | 13.0 (.512)    | 44.0 (1.732)    | 22.0<br>(.866)  | 16.5<br>(.650)  | 3.0 (.118)      | YH-540<br>JS-150D<br>JSHR-150 | 25      |            |
|                                | 10                  | GS10-120  | 10-120                   | 10.5 (.413)         | 24.0 (.945)     | 13.0 (.512)    | 44.0 (1.732)    |                 |                 | 3.0 (.118)      |                               |         |            |
|                                | 12                  | GS12-120  | 12-120                   | 13.0 (.512)         | 24.0 (.945)     | 13.0 (.512)    | 44.0 (1.732)    |                 |                 | 3.0 (.118)      |                               |         |            |
|                                | 16                  | GS16-120  | 16-120                   | 17.0 (.669)         | 28.0 (1.102)    | 16.0 (.630)    | 48.0 (1.890)    |                 |                 | 3.0 (.118)      |                               |         |            |
|                                | 16                  | GS16S-120 |                          | 17.0 (.669)         | 32.0 (1.260)    | 20.0 (.787)    | 53.0 (2.087)    |                 |                 | 2.6 (.102)      |                               | 50      |            |
|                                | 20                  | GS20-120  |                          | 21.0 (.827)         | 32.0 (1.260)    | 25.0 (.984)    | 53.0 (2.087)    |                 |                 | 21.0(.827)      |                               |         | 2.6 (.102) |
| >120 to 150<br>(250 to 300MCM) | 10                  | GS10-150  | 10-150                   | 10.5 (.413)         | 30.0 (1.181)    | 16.0 (.630)    | 50.0 (1.969)    | 24.0<br>(.946)  | 19.0<br>(.748)  | 3.2<br>(.126)   | JS-150D<br>JSHR-150           | 25      |            |
|                                | 12                  | GS12-150  | 12-150                   | 13.0 (.512)         | 30.0 (1.181)    | 16.0 (.630)    | 50.0 (1.969)    |                 |                 |                 |                               |         |            |
|                                | 16                  | GS16-150  | 16-150                   | 17.0 (.669)         | 30.0 (1.181)    | 16.0 (.630)    | 50.0 (1.969)    |                 |                 |                 |                               |         |            |
|                                | 18                  | GS18-150  | 18-150                   | 19.0 (.748)         | 36.0 (1.417)    | 20.0 (.787)    | 63.0 (2.480)    | 27.0<br>(1.063) | 19.5<br>(.768)  |                 |                               |         |            |
|                                | 20                  | GS20-150  |                          | 21.0 (.827)         | 36.0 (1.417)    | 30.0 (1.181)   | 63.0 (2.480)    |                 |                 |                 |                               |         |            |
| >150 to 185<br>(300 to 350MCM) | 10                  | GS10-185  | 10-185                   | 10.5 (.413)         | 36.0<br>(1.417) | 16.0<br>(.630) | 50.0<br>(1.969) | 28.0<br>(1.102) | 21.0<br>(.827)  | 3.5<br>(.138)   | JSH-325                       | 20      |            |
|                                | 12                  | GS12-185  | 12-185                   | 13.0 (.512)         |                 |                |                 |                 |                 |                 |                               |         |            |
|                                | 16                  | GS16-185  | 16-185                   | 17.0 (.669)         |                 |                |                 |                 |                 |                 |                               |         |            |
| >185 to 240<br>(350 to 450MCM) | 10                  | GS10-240  | 10-240                   | 10.5 (.413)         | 38.0 (1.496)    | 20.0 (.787)    | 56.0 (2.205)    | 32.0(1.260)     | 23.5(.925)      | 4.0<br>(.157)   | JSH-325                       | 10      |            |
|                                | 12                  | GS12-240  | 12-240                   | 13.0 (.512)         | 38.0 (1.496)    | 20.0 (.787)    | 56.0 (2.205)    | 32.0(1.260)     | 23.5(.925)      |                 |                               |         |            |
|                                | 12                  | GS12L-240 |                          | 13.0 (.512)         | 44.0 (1.732)    | 25.0 (.984)    | 69.0 (2.717)    | 31.5(1.240)     | 24.0(.945)      |                 |                               |         |            |
|                                | 16                  | GS16-240  | 16-240                   | 17.0 (.669)         | 38.0 (1.496)    | 20.0 (.787)    | 56.0 (2.205)    | 32.0(1.260)     | 23.5(.925)      |                 |                               |         |            |
|                                | 16                  | GS16L-240 |                          | 17.0 (.669)         | 44.0 (1.732)    | 25.0 (.984)    | 69.0 (2.717)    | 31.5(1.240)     | 24.0(.945)      |                 |                               |         |            |
|                                | 22                  | GS22L-240 |                          | 23.0 (.906)         | 44.0 (1.732)    | 25.0 (.984)    | 69.0 (2.717)    | 31.5(1.240)     | 24.0(.945)      |                 |                               |         |            |
| >240 to 300<br>(500 to 600MCM) | 10                  | GS10-300  |                          | 10.5 (.413)         | 50.5<br>(1.988) |                | 26.0 (1.024)    | 69.0 (2.717)    | 35.5<br>(1.398) | 28.0<br>(1.102) | 4.5<br>(.177)                 | —       | 5          |
|                                | 12                  | GS12-300  |                          | 13.0 (.512)         |                 |                | 26.0 (1.024)    | 69.0 (2.717)    |                 |                 |                               |         | 25         |
|                                | 12                  | GS12L-300 |                          | 13.0 (.512)         |                 |                | 30.0 (1.181)    | 80.5 (3.169)    |                 |                 |                               |         | 5          |
|                                | 16                  | GS16-300  |                          | 17.0 (.669)         |                 |                | 26.0 (1.024)    | 69.0 (2.717)    |                 |                 |                               |         | 25         |
|                                | 22                  | GS22L-300 |                          | 23.0 (.906)         |                 |                | 30.0 (1.181)    | 80.5 (3.169)    |                 |                 |                               |         | 5          |
|                                |                     |           |                          |                     |                 |                |                 |                 |                 |                 |                               |         |            |

Note :1) Contact J.S.T. Europe N.V., Belgium for the above tools.

2) Delivery lead times may vary depending on the product. Contact JST for details.