





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		M7	REVISED PER ECR-13-011067	16JUL13	KH	PD

- 1 ALL DIMENSIONS APPLY TO A MOISTURIZED HOUSING.
- 2 PRELIMINARY – NOT FOR PRODUCTION
- 3 OFFERED FOR CONSIDERATION IN "NON-DRIP" HOUSING MATERIAL APPLICATIONS.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING I PER D.RENAUD/D.SINIS
- 5 PREPRODUCTION-FASR REQUIRED

SUGGESTED MATING TAB



- 1 – MATL: ½ H BRASS OR NICKEL PL STEEL.
- 2 – NO BURRS PERMISSIBLE AT HOLE.
- 3 – MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- 4 – TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225° F
- 5 – HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



3D VIEW

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	7/3/96	 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK	MS FEHER	7/3/96				
		APVD	J GILLISPIE	7/3/96	NAME HOUSING, RECEPTACLE, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES —			
		PRODUCT SPEC		—				
MATERIAL SEE TABLE		APPLICATION SPEC		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT		—	A2	00779	 521120	—
TOLERANCES UNLESS OTHERWISE SPECIFIED:		FINISH			CUSTOMER DRAWING			
0 PLC ± —		SEE TABLE			SCALE	5:1	SHEET	1 of 2
1 PLC ± —					REV	MZ		
2 PLC ± 0.25 [.010]								
3 PLC ± —								
4 PLC ± —								
ANGLES ± —								

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

	BROWN	66/6 NYLON, V0		2-521120-5	
	YELLOW	66/6 NYLON, V0		2-521120-4	
	GREEN	66/6 NYLON, V0		2-521120-3	
	RED	66/6 NYLON, V0		2-521120-2	
	BLUE	66/6 NYLON, V0		2-521120-1	
	BROWN	6/6 NYLON, V2		2-521120-0	
	YELLOW	6/6 NYLON, V2		1-521120-9	
	GREEN	6/6 NYLON, V2		1-521120-8	
	NATURAL	6/6 NYLON, V2		1-521120-7	
	BLACK	66/6 NYLON, V0		1-521120-6	
	NATURAL	 66/6 OR 66 NYLON, V0		1-521120-5	
	NATURAL	6/6 NYLON, V0		1-521120-4	
	NATURAL	66/6 OR 66 NYLON, V0		1-521120-3	
	 OBSOLETE	YELLOW	6/6 NYLON		1-521120-2
		BLUE	6/6 NYLON		1-521120-1
GREEN		6/6 NYLON		1-521120-0	
RED		6/6 NYLON		-521120-9-	
BLACK		6/6 NYLON		521120-8	
NATURAL		6/6 NYLON		521120-7	
BLACK		4/6 NYLON		521120-6	
RED		6/6 NYLON		521120-5	
BLUE		6/6 NYLON		521120-4	
 OBSOLETE	PUTTY	6/6 NYLON		-521120-2-	
	NATURAL	6/6 NYLON		521120-1	
	COLOR	MATERIAL		PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 7/3/96		 TE Connectivity									
		CHK MS FEHER 7/3/96											
		APVD J GILLISPIE 7/3/96											
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME									
		0 PLC ± —		HOUSING, RECEPTACLE, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES —									
		1 PLC ± —											
		2 PLC ± 0.25 [.010]											
		3 PLC ± —		SIZECAGE CODEDRAWING NORESTRICTED TO									
		4 PLC ± —											
		ANGLES ± —											
MATERIAL		FINISH		WEIGHT		A200779C-521120		—					
SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE 5:1		SHEET 2 OF 2		REV MZ	