





4

3

2

1

REVISIONS					
ZONE	REV	ECO	DESCRIPTION	CHECK	DATE
.	A	.	PRODUCTION RELEASE	BRL	1-20-05




4X M3 X 0.5 THD
0.16[4.0] MAX SCREW PENETRATION

2X M3 X 0.5 THD
0.16[4.0] MAX SCREW PENETRATION

A

4. FINISH: CLEAR ZINC PLATE PER ASTM-B633/78, TYPE III, SC 3.
3. MATERIAL: 20 GA (.036) THK C1008 CRS SHEET
ALTERNATE: 1mm (.039) THK C1008 CRS SHEET
2. METRIC TOLERANCES: .X $\pm$ 0.5, .XX $\pm$ 0.25.
1. UNITS: PRIMARY (IMPERIAL) XXX
ALTERNATE (METRIC) [XXX]

NOTES: UNLESS OTHERWISE SPECIFIED



PLOTTED
01-20-2005

THE INFORMATION, HEREON IS THE PROPERTY OF XPiQ, INC. AND IS UNCLASSIFIED, UNCONTROLLED, AND NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN AUTHORIZATION FROM XPiQ, INC.			
CONTRACT NO.	DATE	TITLE	SCALE
APPROVALS	1-19-05	OUTLINE DWG, ECM40/60 WITH COVERS	1/1
DESIGNED BY B. LILLEMØEN	1-20-05	SIZE C	10004702
CHECKED BY BRL	1-20-05	ENG'D BY BRL	REV A
UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES	0.02	0.10	0.30
XX	XXX	ANGLE	10004702.DWG
NEXT ASSY	USED ON		

DWG NO.	10004702
SHT	1
REV	A

4

3

2

1