

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL INTERNATIONAL RIGHTS RESERVED.

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

J1

REVISED PER ECR-10-004379

22MAR10

HMR

JR

INSULATION

SLEEVE

SERRATIONS

BODY

0.79
[.031]
MIN7.14
[.281]
MIN15.54
[.612]
MAX19.43
[.765]
MAX7.62
[.300] ϕ "A" ± 0.08 [.003]
(FOR #B STUD)

SUPERSEDED BY 52124-1

2 MILITARY RANGE: 26-24
COMMERCIAL RANGE: 26-223 FOR 1.27[.050] TO 2.08[.082]
WIRE INSULATION DIA4 TONGUE MATERIAL THK
 0.46 ± 0.05 [.018 $\pm$.002]APPLIES FROM EDGE OF METAL
BARREL TO CENTERLINE OF STUD HOLE.

OBSOLETE	#10	.197	1	WIRE TERMINAL	52124-3	BODY: COPPER ASTM-B152 TIN PL ASTM-B545 SLEEVE: COPPER ASTM-B152 TIN PL ASTM-B545 INSULATION: NYLON ASTM-D4066 TYPE I COLOR: YELLOW	52124-1
	#8	.171	1		52124-2		
	"B"	"A"	QTY		PART NO ON TAPE		52124
				DESCRIPTION	MATERIAL & FINISH	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN RAGHAVENDRA 22MAR10

CHK JEFF RUTH 22MAR10

APVD TOM MICHIELUTTI 22MAR10

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, PA 17105-3608NAME
TERMINAL PIDG - NYLON - RING TONGUE
WIRE SIZE: 26-22

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-52124

SCALE 10:1 SHEET 1 OF 1 REV J1