

RG-Series

Single/Double Pole Lighted Rocker & Paddle Switches

PRODUCT WEBPAGE

request sample, configure part



The double pole version of the R-Series incorporates the same sleek lines as the original Corvette, in a double pole envelope. Features include silver-plated butt-action contacts which afford ratings to 20A/125, 15A 250VAC and withstand peak inrush currents up to 100 amps. Paddle or rocker actuators and a choice of solder lug, .250 Tab and wire lead terminations enable this switch to adapt to high current applications.

1-2

Poles

10-20

Amps

125-250

VAC

6-24

VDC

Typical Applications

- Power Supply
- Appliances
- Exercise Equipment
- Music Equipment

Tech Specs

Dielectric Strength

UL/CSA: 1000V - live to dead metal parts
& opposite polarity
VDE: 4000V - live to dead metal parts;
1250V - opposite polarity & across open
contacts

Electrical Life

50,000 cycles

Operating Temperature

-40°F to 185°F (-40°C to 85°C)

Ordering Scheme

Sample
Part Number

RGSCA901 - R - B - B - A

Selection

1

2

3

4

5

1. SERIES

15A 250 VAC, 20A 125 VAC, 3/4 HP 125-250 VAC, 14(6)A 250 VAC
Solder Lugs .250 Tabs Wire Leads

Standard Base

	RGSCA900	RGSCA901	RGSCA905
OFF-NONE-ON (Single Pole)	RGSCB900	RGSCB901	RGSCB905
ON-NONE-ON (Single Pole)	RGSCC900	RGSCC901	RGSCC905
OFF-NONE-ON (Double Pole)	RGSCD900	RGSCD901	RGSCD905

European Base (22 x 30 mm cutout)

	RGSEA900	RGSEA901	RGSEA905
OFF-NONE-ON (Single Pole)	RGSEB900	RGSEB901	RGSEB905
ON-NONE-ON (Single Pole)	RGSEC900	RGSEC901	RGSEC905
OFF-NONE-ON (Double Pole)	RGSED900	RGSED901	RGSED905

4. BEZEL COLOR

1

B Black

W White

5. ROCKER LEGEND

NO LEGEND	hot stamp
OFF-ON vertical	O
OFF-ON horizontal	A
O-I horizontal	B
O-I vertical	D
Dual OFF-ON, O-I vertical	E
Dual OFF-ON, O-I horizontal	H
	J

2. ACTUATOR STYLE

P Paddle

R Rocker

3. ACTUATOR COLOR

1

B Black

W White

Notes:

1 Additional ratings, colors and clear style actuators are available. Consult factory.

[Configure Complete Part Number >](#)

[Browse Standard Parts >](#)

Dimensional Specs

inches [millimeters]

