

High Voltage Power Operational Amplifiers



FEATURES

- 1140V P-P SIGNAL OUTPUT
- WIDE SUPPLY RANGE — $\pm 75V$ to $\pm 600V$
- PROGRAMMABLE CURRENT LIMIT
- 75 mA CONTINUOUS OUTPUT CURRENT
- HERMETIC SEALED PACKAGE
- INPUT PROTECTION

APPLICATIONS



- PIEZOELECTRIC POSITIONING
- HIGH VOLTAGE INSTRUMENTATION
- ELECTROSTATIC DEFLECTION
- SEMICONDUCTOR TESTING

DESCRIPTION

The PA89 is an ultra high voltage, MOSFET operational amplifier designed for output currents up to 75 mA. Output voltages can swing over 1000V p-p. The safe operating area (SOA) has no second breakdown limitations and can be observed with all types of loads by choosing an appropriate current limiting resistor. High accuracy is achieved with a cascode input circuit configuration and 120dB open loop gain. All internal biasing is referenced to a bootstrapped zener-MOSFET current source, giving the PA89 a wide supply range and excellent supply rejection. The MOSFET output stage is biased for class A/B linear operation. External compensation provides user flexibility. The PA89 is 100% gross leak tested to military standards for long term reliability.

This hybrid integrated circuit utilizes a beryllia (BeO) substrate, thick film resistors, ceramic capacitors and semiconductor chips to maximize reliability, minimize size and give top performance. Ultrasonically bonded aluminum wires provide reliable interconnections at all operating temperatures. The MO-127 High Voltage, Power Dip™ package is hermetically sealed and electrically isolated. The use of compressible thermal washers will void the product warranty.

SIMPLIFIED SCHEMATIC




PATENTED

**HIGH VOLTAGE MO-127
PACKAGE STYLE DC**


TYPICAL APPLICATION

Ultra-high voltage capability combined with the bridge amplifier configuration makes it possible to develop ± 1000 volt peak swings across a piezo element. A high gain of -50 for A1 insures stability with the capacitive load, while “noise-gain” compensation R_n and C_n on A2 insure the stability of A2 by operating in a noise gain of 50.



SINGLE AXIS MICRO-POSITIONING

EXTERNAL CONNECTIONS



PHASE COMPENSATION

Gain	C_c	R_c
1	470pF	470 Ω
10	68pF	220 Ω
15	33pF	220 Ω
100	15pF	220 Ω

Note: C_c must be rated for full supply voltage $-V_s$ to $+V_s$.
See details under “EXTERNAL COMPONENTS”

ABSOLUTE MAXIMUM RATINGS

SUPPLY VOLTAGE, $+V_S$ to $-V_S$	1200V
OUTPUT CURRENT, within SOA	100mA
POWER DISSIPATION, internal at $T_C = 25^\circ\text{C}$	40W
INPUT VOLTAGE, differential	$\pm 25\text{V}$
INPUT VOLTAGE, common mode	$\pm V_S \mp 50\text{V}$
TEMPERATURE, pin solder - 10s max	350°C
TEMPERATURE, junction ²	150°C
TEMPERATURE, storage	-65 to 125°C
OPERATING TEMPERATURE RANGE, case	-55 to 125°C

SPECIFICATIONS

PARAMETER		TEST CONDITIONS ¹	MIN	PA89 TYP	MAX	MIN	PA89A TYP	MAX	UNITS
INPUT									
OFFSET VOLTAGE, initial	Full temperature range			.5	2		.25	.5	mV
OFFSET VOLTAGE, vs. temperature			10	30		5	10	$\mu\text{V}/^{\circ}\text{C}$	
OFFSET VOLTAGE, vs. supply			7			*		$\mu\text{V}/\text{V}$	
OFFSET VOLTAGE, vs. time			75			*		$\mu\text{V}/\text{kh}$	
BIAS CURRENT, initial ³			5	50		3	10	pA	
BIAS CURRENT,vs. supply	Full temperature range		.01			*		pA/V	
OFFSET CURRENT, initial ³			5	50		3	20	pA	
INPUT IMPEDANCE, DC			10^5			*		M Ω	
INPUT CAPACITANCE			4			*		pF	
COMMON MODE VOLTAGE RANGE ⁴		Full temperature range	$\pm V_S \mp 50$			*		V	
COMMON MODE REJECTION, DC	Full temperature range, $V_{CM} = \pm 90\text{V}$	96	110		*	*		dB	
INPUT NOISE	10kHz BW, $R_S = 10\text{K}$, $C_C = 15\text{pF}$		4					$\mu\text{V RMS}$	
GAIN									
OPEN LOOP GAIN at 15Hz	$R_L = 10\text{k}$, $C_C = 15\text{pF}$	108	120		*	*		dB	
GAIN BANDWIDTH PRODUCT	$R_L = 10\text{k}$, $C_C = 15\text{pF}$, $A_v = 100$		10			*		MHz	
POWER BANDWIDTH	$R_L = 10\text{k}$, $C_C = 15\text{pF}$, $V_O = 500\text{V p-p}$		5			*		kHz	
PHASE MARGIN	Full temperature range, $A_v = 10$		60			*		$^{\circ}$	
OUTPUT									
VOLTAGE SWING ⁴	$I_O = 75\text{mA}$	$\pm V_S \mp 45$	$\pm V_S \mp 30$		*	*		V	
VOLTAGE SWING ⁴	Full temperature range, $I_O = 20\text{mA}$	$\pm V_S \mp 20$	$\pm V_S \mp 12$		*	*		V	
CURRENT, continuous	Full temperature range	75			*			mA	
SLEW RATE	$C_C = 15\text{pF}$, $A_v = 100$	12	16		*	*		V/ μs	
CAPACITIVE LOAD, $A_v = 10$	Full temperature range			1			*	nF	
CAPACITIVE LOAD, $A_v > 10$	Full temperature range			SOA			*		
SETTLING TIME to .1%	$R_L = 10\text{K}\Omega$, 10V step, $A_v = 10$		2			*		μs	
POWER SUPPLY									
VOLTAGE, V_S ⁴	Full temperature range	± 75	± 500	± 600	*	*	*	V	
CURRENT, quiescent			4.8	6.0		*	*	mA	
THERMAL									
RESISTANCE, AC, junction to case ⁵	Full temperature range, $F > 60\text{Hz}$		2.1	2.3		*	*	$^{\circ}\text{C}/\text{W}$	
RESISTANCE, DC, junction to case	Full temperature range, $F < 60\text{Hz}$		3.3	3.5		*	*	$^{\circ}\text{C}/\text{W}$	
RESISTANCE, junction to air	Full temperature range		15			*		$^{\circ}\text{C}/\text{W}$	
TEMPERATURE RANGE, case	Meets full range specifications	-25		+85	*		*	$^{\circ}\text{C}$	

NOTES: * The specification of PA89A is identical to the specification for PA89 in applicable column to the left.













1. Unless otherwise noted: $T_C = 25^\circ\text{C}$, $C_C = 68\text{pF}$, $R_C = 220\Omega$, and $V_S = \pm 500\text{V}$. Input parameters for bias currents and offset voltage are \pm values given.
2. Long term operation at the maximum junction temperature will result in reduced product life. Derate internal power dissipation to achieve high MTTF.
3. Doubles for every 10°C of temperature increase.
4. $+V_S$ and $-V_S$ denote the positive and negative supply rail respectively.
5. Rating applies only if the output current alternates between both output transistors at a rate faster than 60Hz.

CAUTION

The PA89 is constructed from MOSFET transistors. ESD handling procedures must be observed.

The internal substrate contains beryllia (BeO). Do not break the seal. If accidentally broken, do not crush, machine, or subject to temperatures in excess of 850°C to avoid generating toxic fumes.

TYPICAL PERFORMANCE GRAPHS



GENERAL

Please read Application Note 1 "General Operating Considerations" which covers stability, supplies, heat sinking, mounting, current limit, SOA interpretation, and specification interpretation. Visit www.apexanalog.com for design tools that help automate tasks such as calculations for stability, internal power dissipation, current limit; heat sink selection; Apex Microtechnology's complete Application Notes library; Technical Seminar Workbook; and Evaluation Kits.


STABILITY

Although the PA89 can be operated at unity gain, maximum slew rate and bandwidth performance was designed to be obtained at gains of 10 or more. Use the small signal response and phase response graphs as a guide. In applications where gains of less than 10 are required, use noise gain compensation to increase the phase margin of the application circuit as illustrated in the typical application drawing.

SAFE OPERATING AREA (SOA)

The MOSFET output stage of this power operational amplifier has two distinct limitations:

1. The current handling capability of the MOSFET geometry and the wire bonds.
 2. The junction temperature of the output MOSFETs.
- NOTE: The output stage is protected against transient flyback. However, for protection against sustained, high energy flyback, external fast-recovery diodes should be used.



SAFE OPERATING CURVES

The safe operating area curves define the maximum additional internal power dissipation the amplifier can tolerate when it produces the necessary output to drive an external load. This is not the same as the absolute maximum internal power dissipation listed elsewhere in the specification since the quiescent power dissipation is significant compared to the total.

EXTERNAL COMPONENTS

The very high operating voltages of the PA89 demand consideration of two component specifications rarely of concern in building op amp circuits: voltage rating and voltage coefficient.

The compensation capacitance C_c must be rated for the

full supply voltage range. For example, with supply voltages of ±500V the possible voltage swing across C_c is 1000V. In addition, a voltage coefficient less than 100PPM is recommended to maintain the capacitance variation to less than 5% for this example. It is strongly recommended to use the highest quality capacitor possible rated at least twice the total supply voltage range.

Of equal importance are the voltage rating and voltage coefficient of the gain setting resistances. Typical voltage ratings of low wattage resistors are 150 to 250V. In the above example 1000V could appear across the feedback resistor. This would require several resistors in series to obtain the proper voltage rating. Low voltage coefficient resistors will insure good gain linearity. The wattage rating of the feedback resistor is also of concern. A 1 megohm feedback resistor could easily develop 1 watt of power dissipation.

Though high voltage rated resistors can be obtained, a 1 megohm feedback resistor comprised of five 200Kohm, 1/4 watt metal film resistors in series will produce the proper voltage rating, voltage coefficient and wattage rating.

CURRENT LIMIT

For proper operation the current limit resistor (R_{CL}) must be connected as shown in the external connection diagram. The minimum value is 3.5 ohm, however for optimum reliability the resistor value should be set as high as possible. The value is calculated as follows with the maximum practical value of 150 ohms.

$$R_{CL} = \frac{.7}{I_{LIM}}$$

When setting the value for R_{CL} allow for the load current as well as the current in the feedback resistor. Also allow for the temperature coefficient of the current limit which is approximately -0.3%/°C of case temperature rise.

CAUTIONS

The operating voltages of the PA89 are potentially lethal. During circuit design, develop a functioning circuit at the lowest possible voltages. Clip test leads should be used for "hands off" measurements while troubleshooting.

POWER SUPPLY PROTECTION

Unidirectional zener diode transient absorbers are recommended as protection on the supply pins. The zeners clamp transients to voltages within the power supply rating and also clamp power supply reversals to ground. Whether the zeners are used or not, the system power supply should be evaluated for transient performance including power-on overshoot and power-off polarity reversals as well as line regulation.

Conditions which can cause open circuits or polarity reversals on either power supply rail should be avoided or protected against. Reversals or opens on the negative supply rail is known to induce input stage failure. Unidirectional transzorbs prevent this, and it is desirable that they be both electrically and physically as close to the amplifier as possible.

NEED TECHNICAL HELP? CONTACT APEX SUPPORT!

For all Apex Microtechnology product questions and inquiries, call toll free 800-546-2739 in North America.

For inquiries via email, please contact apex.support@apexanalog.com.

International customers can also request support by contacting their local Apex Microtechnology Sales Representative.

To find the one nearest to you, go to www.apexanalog.com

IMPORTANT NOTICE

Apex Microtechnology, Inc. has made every effort to insure the accuracy of the content contained in this document. However, the information is subject to change without notice and is provided "AS IS" without warranty of any kind (expressed or implied). Apex Microtechnology reserves the right to make changes without further notice to any specifications or products mentioned herein to improve reliability. This document is the property of Apex Microtechnology and by furnishing this information, Apex Microtechnology grants no license, expressed or implied under any patents, mask work rights, copyrights, trademarks, trade secrets or other intellectual property rights. Apex Microtechnology owns the copyrights associated with the information contained herein and gives consent for copies to be made of the information only for use within your organization with respect to Apex Microtechnology integrated circuits or other products of Apex Microtechnology. This consent does not extend to other copying such as copying for general distribution, advertising or promotional purposes, or for creating any work for resale.

APEX MICROTECHNOLOGY PRODUCTS ARE NOT DESIGNED, AUTHORIZED OR WARRANTED TO BE SUITABLE FOR USE IN PRODUCTS USED FOR LIFE SUPPORT, AUTOMOTIVE SAFETY, SECURITY DEVICES, OR OTHER CRITICAL APPLICATIONS. PRODUCTS IN SUCH APPLICATIONS ARE UNDERSTOOD TO BE FULLY AT THE CUSTOMER OR THE CUSTOMER'S RISK.

Apex Microtechnology, Apex and Apex Precision Power are trademarks of Apex Microtechnology, Inc. All other corporate names noted herein may be trademarks of their respective holders.