

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



LOC
AFDIST
50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REDRAWN PER 0G3A-0126-01	22FEB01	JR	ND



VIEW A-A

SECTION
B-B

- 1 SUPPLIED IN LOOSE PIECE.
- 2 0.00381 [.000150] MIN TIN PL
OVER 0.00254 [.000100] MIN
COPPER PL.
- 3 PARTS TO MEET AMP SOLDERABILITY
SPEC 109-11-2, MIDLY ACTIVATED
ROSIN.
- 4 PRINTED CIRCUIT BOARD THK IS
0.81/2.36 [.032/.093] THK WITH A
HOLE DIA OF 1.70/1.60 [.067/.063].

61968-1

62437-1

STRIP P/N

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN JR RUTH 22FEB01

CHK MS FEHER 22FEB01

APVD N DEIBERT 22FEB01

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco
ElectronicsTyco Electronics Corporation
Harrisburg, PA. 17057

NAME

TAB, FASTON, PC BOARD
2.79 [.110] SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-62437

SCALE 5:1

SHEET 1 OF 1

REV B

DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -
MATERIAL 082 BRASS	FINISH - 2