

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0878311020

Status:

Active

Overview:

Description:

2.00mm (.079") Pitch Milli-Grid™ Header, Vertical, Through Hole, Shrouded, Lead-free, 10 Circuits, 0.38µm (15µ") Gold (Au) Plating, Center Polarization Slot, without Locking Window, without PCB Locator, Tube

Documents:

3D Model

Drawing (PDF)

Product Specification PS-87831-027 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Overview

Product Name

PCB Headers

87831

Wire-to-Board

Contact Molex for application in automotive industry

Milli-Grid™

Milli-Grid™

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length (in)

PC Tail Length (mm)

PCB Locator

PCB Retention

PCB Thickness Recommended (in)

PCB Thickness Recommended (mm)

Packaging Type

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Pitch - Term. Interface (in)

Pitch - Term. Interface (mm)

Plating min: Mating (µin)

Plating min: Mating (µm)

Plating min: Termination (µin)

Plating min: Termination (µm)

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

No

10

10

Black

No

94V-0

No

No

None

None

Brass

Gold

Tin

Nylon

2

Vertical

0.098 In

2.50 mm

No

None

0.062 In

1.60 mm

Tube

0.079 In

2.00 mm

0.079 In

2.00 mm

15

0.38

76

1.88

Side Slots (2)


No

Fully

No

Yes

-55°C to +105°C



Series image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

87831 Series

Mates With

50394 Wire-to-Board Terminals. 51110 Wire-to-Board Crimp Housing. 87568 Wire-to-Board IDT Housings. 79107 Board-to-Board Top Entry Through Hole Receptacle. 79108 Board-to-Board FFC/FPC Top Entry Through Hole Receptacle. L

Termination Interface: Style	Through Hole
Electrical	
CSA	LR19980
Current - Maximum	2A
UL	E29179
Voltage - Maximum	125V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	10
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-87831-027
Sales Drawing	SD-87831-011

This document was generated on 11/05/2009

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION