



**Part Number: 73660-8000**

Image not available

**Status:** Active - Custom  
**Series:** [73660](#)  
**Category:** Backplane Connectors  
**Overview:** [HDM®](#)

Series image - Reference only

#### Mates With Part(s):

[73644](#) HDM® Board-to-Board Backplane Header  
[73799](#) HDM® Board-to-Board Duckpin Midplane Header

#### Product Environmental Compliance

[EU RoHS](#): ELV and RoHS Compliant

[China RoHS](#):

[REACH SVHC](#): Contains SVHC: No

[Low-Halogen Status](#): Not Reviewed

#### Part Detail

##### General

<b>Status</b>	<b>Active - Custom</b>
Category	Backplane Connectors
Series	<a href="#">73660</a>
Application	Daughtercard
Component Type	Guide
Overview	<a href="#">HDM®</a>
Product Name	HDM®
Style	N/A

##### Physical

Circuits (Loaded)	N/A
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	250
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Plating Mating	n/a
Material - Resin	High Temperature Thermoplastic
Number of Columns	N/A
Number of Pairs	Open Pin Field
Number of Rows	6
Orientation	Right Angle
PC Tail Length	N/A
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +105°C

##### Electrical

**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1A
Data Rate	N/A
Real Signals (per 25mm)	75
Shielded	No
Voltage - Maximum	250V

##### Material Info

UPC	800755024951
-----	--------------

##### Reference - Drawing Numbers

Sales Drawing	SDA-73660-****
---------------	----------------

#### Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

---

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)