


NOTE

1.52610-**23のアクチュエータはハウジング内に押し下げた状態とする。
詳細寸法については図面 526101002 PSD 000 を参照下さい。
ACTUATOR OF PART NO. 52610-**23 SHOULD BE LOCKED.
RE DETAILD DIMENSIONS, SEE 526101002 PSD 000.

2.梱包数量：1000個/リール
NUMBER OF CONNECTORS：1000 PCS/REEL


3.リードテープ長さ LEAD TAPE LENGTH




4.カバーテープの剥離強度については、IEC60286-3に準拠。
COVER TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

5.材料 MATERIAL
キャリアテープ：ポリプロピレン
トップテープ：PET, PE, PEF
リール：ポリスチレン <リサイクル材を含む>
CARRIER TAPE：POLYPROPYLENE
TOP TAPE：PET, PE, PEF
REEL：POLYSTYRENE (PS) < RECYCLE MATERIAL CONTAINED >

6.ELV及びRoHS適合品。
ELV AND RoHS COMPLIANT.






MODEL NO. 52610-**34

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
RELEASED	EC NO: 106044 DRWN: YMIZUNO02 CHK'D: TKUSUHARA01 APPR: TKUSUHARA01	2016/12/16 2016/12/28 2016/12/28	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®					
					mm		---							
			ANGULAR TOL ± 3.0 °		DRWN BY		DATE		1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG					
			4 PLACES ± 0.2		YMIZUNO02		2016/12/16							
			3 PLACES ± 0.2		CHK'D BY		DATE							
			2 PLACES ± 0.2		YKOBAYASHI02									
			1 PLACE ± 0.2		APPR BY		DATE		PRODUCT CUSTOMER DRAWING					
			0 PLACES ± 0.2		TKUSUHARA01		2016/12/28							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
					A3				52610		SEE CHART		GENERAL	
					DOCUMENT NUMBER		DOC TYPE		DOC PART					
					526100002		PSD		000					
								SHEET NUMBER		1 OF 5				

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.2
10 OVER 30 UNDER		±0.25
30 OVER		±0.3

RELEASE STATUS	P1	RELEASE DATE	2016/12/28	05:20:08
----------------	----	--------------	------------	----------



24	29.4	25.4	15.25	11.32	52610-1034	10
			14.25	10.32	52610-0934	9
			13.25	9.32	52610-0834	8
			12.25	8.32	52610-0734	7
			11.25	7.32	52610-0634	6
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.2
10 OVER 30 UNDER		±0.25
30 OVER		±0.3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED

EC NO: 106044
DRWN: YMIZUNO02
CHK'D: TKUSUHARA01
REV APPR: TKUSUHARA01

2016/12/16
2016/12/28
2016/12/28

GENERAL TOLERANCES
(UNLESS SPECIFIED)

ANGULAR TOL ± 3.0 °

4 PLACES ± 0.2

3 PLACES ± 0.2

2 PLACES ± 0.2

1 PLACE ± 0.2

0 PLACES ± 0.2

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION UNITS
mm

SCALE

DRWN BY
YMIZUNO02

DATE
2016/12/16

CHK'D BY
YKOBAYASHI02

DATE

APPR BY
TKUSUHARA01

DATE
2016/12/28

DRAWING SIZE
A3

THIRD ANGLE PROJECTION

molex®

1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG

PRODUCT CUSTOMER DRAWING

SERIES
52610

MATERIAL NUMBER
SEE CHART




CUSTOMER
GENERAL

DOCUMENT NUMBER
526100002

DOC TYPE
PSD

DOC PART
000

SHEET NUMBER
2 OF 5



32	37.4	33.4	20.25	16.32	52610-1534	15
			19.25	15.32	52610-1434	14
			18.25	14.32	52610-1334	13
			17.25	13.32	52610-1234	12
			16.25	12.32	52610-1134	11
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		± 0.2
10 OVER 30 UNDER		± 0.25
30 OVER		± 0.3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED

EC NO: 106044

DRWN: YMIZUNO02

CHK'D: TKUSUHARA01

APPR: TKUSUHARA01

2016/12/16

2016/12/28

2016/12/28

GENERAL TOLERANCES
(UNLESS SPECIFIED)

ANGULAR TOL $\pm 3.0^\circ$

4 PLACES ± 0.2

3 PLACES ± 0.2

2 PLACES ± 0.2

1 PLACE ± 0.2

0 PLACES ± 0.2

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION UNITS
mm

SCALE

DRWN BY
YMIZUNO02

DATE
2016/12/16

CHK'D BY
YKOBAYASHI02

DATE

APPR BY
TKUSUHARA01

DATE
2016/12/28

DRAWING SIZE
A3

THIRD ANGLE PROJECTION

molex

1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG

PRODUCT CUSTOMER DRAWING

SERIES
52610

MATERIAL NUMBER
SEE CHART




CUSTOMER
GENERAL

DOCUMENT NUMBER
526100002

DOC TYPE
PSD

DOC PART
000


SHEET NUMBER
3 OF 5



44	49.4	45.4	31.25	27.32	52610-2634	26
			30.25	26.32	52610-2534	25
			29.25	25.32	52610-2434	24
			28.25	24.32	52610-2334	23
			27.25	23.32	52610-2234	22
			26.25	22.32	52610-2134	21
			25.25	21.32	52610-2034	20
			24.25	20.32	52610-1934	19
			23.25	19.32	52610-1834	18
			22.25	18.32	52610-1734	17
			21.25	17.32	52610-1634	16
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.2
10 OVER 30 UNDER		±0.25
30 OVER		±0.3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
RELEASED EC NO: 106044 DRWN: YMIZUNO02 CHK'D: TKUSUHARA01 APPR: TKUSUHARA01	2016/12/16	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®			
	2016/12/28	ANGULAR TOL ± 3.0 °		mm		---					
	2016/12/28	4 PLACES	± 0.2	DRWN BY		DATE		1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG			
		3 PLACES	± 0.2	YMIZUNO02		2016/12/16					
		2 PLACES	± 0.2	CHK'D BY		DATE					
		1 PLACE	± 0.2	YKOBAYASHI02				PRODUCT CUSTOMER DRAWING			
		0 PLACES	± 0.2	APPR BY		DATE					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		TKUSUHARA01		2016/12/28					
				DRAWING SIZE		THIRD ANGLE PROJECTION					
				A3							
						SERIES		MATERIAL NUMBER			
						52610		SEE CHART			
						CUSTOMER					
						GENERAL					
						DOCUMENT NUMBER		DOC TYPE			
						526100002		PSD			
						DOC PART		SHEET NUMBER			
						000		4 OF 5			









56	61.4	57.4	35.25	31.32	52610-3034	30
			33.25	29.32	52610-2834	28
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED EC NO: 106044 DRWN: YMIZUNO02 CHK'D: TKUSUHARA01 APPR: TKUSUHARA01	2016/12/16 2016/12/28 2016/12/28	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 3.0 ° 4 PLACES ± 0.2 3 PLACES ± 0.2 2 PLACES ± 0.2 1 PLACE ± 0.2 0 PLACES ± 0.2 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION UNITS mm	SCALE ---	molex®			
			DRWN BY YMIZUNO02	DATE 2016/12/16	1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG			
			CHK'D BY YKOBAYASHI02	DATE	PRODUCT CUSTOMER DRAWING			
			APPR BY TKUSUHARA01	DATE 2016/12/28	SERIES 52610	MATERIAL NUMBER SEE CHART	CUSTOMER GENERAL	
			DRAWING SIZE A3	THIRD ANGLE PROJECTION	DOCUMENT NUMBER 526100002	DOC TYPE PSD	DOC PART 000	SHEET NUMBER 5 OF 5

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.2
10 OVER 30 UNDER		±0.25
30 OVER		±0.3

RELEASE STATUS	P1	RELEASE DATE	2016/12/28	05:20:08
----------------	----	--------------	------------	----------





36.6	34.85	31.2	29	52610-3034	30
34.6	32.85	29.2	27	52610-2834	28
32.6	30.85	27.2	25	52610-2634	26
31.6	29.85	26.2	24	52610-2534	25
30.6	28.85	25.2	23	52610-2434	24
29.6	27.85	24.2	22	52610-2334	23
28.6	26.85	23.2	21	52610-2234	22
27.6	25.85	22.2	20	52610-2134	21
26.6	24.85	21.2	19	52610-2034	20
25.6	23.85	20.2	18	52610-1934	19
24.6	22.85	19.2	17	52610-1834	18
23.6	21.85	18.2	16	52610-1734	17
22.6	20.85	17.2	15	52610-1634	16
21.6	19.85	16.2	14	52610-1534	15
20.6	18.85	15.2	13	52610-1434	14
19.6	17.85	14.2	12	52610-1334	13
18.6	16.85	13.2	11	52610-1234	12
17.6	15.85	12.2	10	52610-1134	11
16.6	14.85	11.2	9	52610-1034	10
15.6	13.85	10.2	8	52610-0934	9
14.6	12.85	9.2	7	52610-0834	8
13.6	11.85	8.2	6	52610-0734	7
12.6	10.85	7.2	5	52610-0634	6
D	(C)	B	(A)	EMBOSSED PACKAGE ORDER NO. オーダー番号	極数 CKT
CONNECTOR SERIES NO. : 52610-**23					

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.2
10 OVER 30 UNDER		±0.25
30 OVER		±0.3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: REVISED			molex						
mm		---											
GENERAL TOLERANCES (UNLESS SPECIFIED)				1.0 FPC CONN ZIF S/T HOUSING ASSY									
ANGULAR TOL ± 3.0 °													
4 PLACES ± 0.03													
3 PLACES ± 0.03													
2 PLACES ± 0.05				PRODUCT CUSTOMER DRAWING									
1 PLACE ± 0.1				DOCUMENT NUMBER			DOC TYPE		DOC PART	REVISION			
0 PLACES ± 0.2				526101002			PSD		000	B			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
						A3-SIZE		52610		SEE TABLE		GENERAL	1 OF 2


DOCUMENT STATUS	P1	RELEASE DATE	2018/04/13	03:51:06
-----------------	----	--------------	------------	----------




36.6	34.85	31.2	29	52610-30 34	30
34.6	32.85	29.2	27	4 -28 34	28
32.6	30.85	27.2	25	-26 34	26
31.6	29.85	26.2	24	-25 34	25
30.6	28.85	25.2	23	-24 34	24
29.6	27.85	24.2	22	-23 34	23
28.6	26.85	23.2	21	-22 34	22
27.6	25.85	22.2	20	-21 34	21
26.6	24.85	21.2	19	-20 34	20
25.6	23.85	20.2	18	-19 34	19
24.6	22.85	19.2	17	-18 34	18
22.6	20.85	17.2	15	-16 34	16
21.6	19.85	16.2	14	-15 34	15
20.6	18.85	15.2	13	-14 34	14
19.6	17.85	14.2	12	-13 34	13
18.6	16.85	13.2	11	-12 34	12
16.6	14.85	11.2	9	-10 34	10
15.6	13.85	10.2	8	-09 34	9
14.6	12.85	9.2	7	-08 34	8
13.6	11.85	8.2	6	-07 34	7
12.6	10.85	7.2	5	52610-06 34	6
D	(C)	B	(A)	EMBOSSED PACKAGE ORDER No. オーダー番号	極数 CKT.

CONNECTOR SERIES NO. : 52610-***23

REVISED EC NO: J2014-0096 DRWN: AISHII CHKD: TAKAHASHI APPR: YNOGAWA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.2	DRAWN BY AISHII	DATE 2013/02/20	TITLE 1.0 FPC CONN ZIF S/T HOUSING ASSY				
		10 OVER 30 UNDER	±0.25	CHECKED BY TAKAHASHI	DATE 2013/02/20					
		30 OVER	±0.3	APPROVED BY KMORIKAWA	DATE 2013/03/15	molex				
		ANGULAR ±3 °		MATERIAL NO.						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		SEE SHEET 2 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
B	REV									




適合FPC推奨寸法
APPLICABLE FPC RECOMMENDED DIM.
仕上がり厚さ(THICKNESS): 0.3 ± 0.05



推奨基板レイアウト
RECOMMENDED P.C.BOARD
PATTERN DIMENSION(REF.)
マスク厚 : $120 \mu\text{m}$
マスク開口率 : 100%
SCREEN THICKNESS : 120 MICROMETER
SCREEN OPEN RATIO : 100%

補強板: ポリイミド
REINFORCE BOARD: POLYIMIDE
熱硬化接着剤
THERMOSETTING ADHESIVE
ベースフィルム: ポリイミド (25 μm)
BASE FILM: POLYIMIDE (25 μm)
熱硬化接着剤
THERMOSETTING ADHESIVE
導体部: 銅箔 (35 μm)
COPPER FOIL (35 μm)
熱硬化接着剤
THERMOSETTING ADHESIVE
カバーレイ: ポリイミド (25 μm)
COVER FILM: POLYIMIDE (25 μm)



FPC構成推奨仕様
STRUCTURE OF FPC

注記 (NOTES):

1. 材質 MATERIAL

ハウジング: ポリアミド (PA), ナチュラル (白色), ガラス充填, UL94V-0
HOUSING: POLYAMIDE, NATURAL (WHITE), GLASS FILLED, UL94V-0
アクチュエータ: ポリフェニレンサルファイド (PPS), ナチュラル (茶色), ガラス充填, UL94V-0
ACTUATOR: POLYPHENYLENE SULFID, NATURAL (BROWN), GLASS FILLED, UL94V-0
ターミナル: リン青銅 ($t=0.32$)
TERMINAL: PHOSPHOR BRONZE ($t=0.32$)

2. めっき仕様 PLATING

ターミナル TERMINAL

錫銀ビスマスめっき ($1.0 \mu\text{m}$ 以上)
TIN SILVER BISMUTH PLATING (1.0 MICROMETER MINIMUM)
下地: ニッケルめっき ($1.0 \mu\text{m}$ 以上)
UNDER PLATING: NICKEL PLATING (1.0 MICROMETER MINIMUM)

- △3. ソルダータール半田付け面のズレ量は、基準面 $\square$ に対し上方向0.05MAX., 下方向0.15MAX.とする。
MISALIGNMENT OF SOLDER TAILS FROM $\square$ UPPER DIRECTION : 0.05 MAX. LOWER DIRECTION : 0.15 MAX.

- △4. 偶数極に適用
APPLY FOR EVEN CIRCUIT.

- △5. R0.3はFPCの導体部にかからないこと。
R0.3 MUST NOT BE OVERLAPED TO PATTERN OF FPC.

6. エンボステープ梱包時は、アクチュエータがロックした状態とする。
IN THE PACKAGE, ACTUATOR OF PART NO.52610-**23 SHOULD BE LOCKED.

- △7. ソルダータールの平坦度は0.1mm以下とする。
SOLDERTAIL COPLANARITY IS 0.1MM MAXIMUM.

8. ELV及びRoHS適合品
ELV AND RoHS COMPLIANT

FPCについて ABOUT FPC

打ち抜き方向は導体側から補強板側を推奨します。
導体部については軟烙銅35 μm または50 μm を推奨します。
補強フィルム材質はポリイミドを推奨します。ベースフィルムは25 μm を推奨します。
接着剤は熱硬化接着剤を推奨します。
尚、接着剤の接点部への付着は導通不良の原因になりますので、染み出しが無い様、お願い致します。
RECOMMENDED PUNCHING DIRECTION: FROM CONDUCTOR SIDE TO STIFFENER SIDE
RECOMMENDED CONDUCTOR SPEC: SOFT COPPER FOIL
RECOMMENDED CONDUCTOR THICKNESS: 35 MICROMETER OR 50 MICROMETER
RECOMMENDED STIFFENER MATERIAL: POLYIMIDE
RECOMMENDED BASE FILM THICKNESS: 25 MICROMETER
RECOMMENDED ADHESIVE: THERMOSETTING ADHESIVE
NOTE: PLEASE PUT APPROPRIATE AMOUNT OF ADHESIVE ON ADHEREND BECAUSE THERE IS A POSSIBILITY THAT THE EXTRA ADHESIVE CAUSES THE DEFECT IN ELECTRICAL CONTINUITY.


SEE SHEET 1 OF 2 EC NO: J2014-0096 DRAWN BY: AISHI CHECKED BY: TAKAHASHI APPR: YNOGAWA 2013/07/18 2013/07/18 2013/08/19	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
		10 UNDER	± 0.2	DRAWN BY AISHI	DATE 2013/02/20	TITLE 1.0 FPC CONN ZIF S/T HOUSING ASSY					
		10 OVER 30 UNDER	± 0.25	CHECKED BY TAKAHASHI	DATE 2013/02/20						
		30 OVER	± 0.3	APPROVED BY KMORIKAWA	DATE 2013/03/15						
		ANGULAR ±3 °		MATERIAL NO.						DOCUMENT NO.	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-52610-050		2 OF 2				
B	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

NOTES

1. 52610-**23のアクチュエータはハウジング内に押し下げた状態とする。
詳細寸法については図面SD-52610-050をご参照ください。
ACTUATOR OF PART NO. 52610-**23 SHULD BE LOCKED.
RE DETAILED DIMENSIONS, SEE SD-52610-050

2. 梱包数量：1000個/リール
NUMBER OF CONNECTORS：1000PCS/REEL


3. リードテープ長さ
LEAD TAPE LENGTH






4. カバーテープの剥離強度については、IEC60286-3に準拠
COVER TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

5. 材料(MATERIAL)
キャリアテープ (CARRIER TAPE)：ポリプロピレン (POLYPROPYLENE)
トップテープ (TOP TAPE)：PET, PE, PEF
リール(REEL)：ポリスチレン(PS)<リサイクル材を含む>
POLYSTYREN(PS) <RECYCLE MATERIAL CONTAINED>

6. ELV及びRoHS適合品
ELV AND RoHS COMPLIANT





RELEASED EC NO: J2013-1003 2013/02/20 DRWNA:ISHII CHKD:K TAKAHASHI 2013/02/20 APPR:KMORIKAWA 2013/03/15	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION					
		10 UNDER	± 0.3	DRAWN BY AISHII	DATE 2013/02/20	TITLE EMBOSS TAPE PACKAGED FOR 1.0 FPC CONN ZIF S/T HOUSING ASSY							
		10 OVER 30 UNDER	± 0.25	CHECKED BY KTAKAHASHI	DATE 2013/02/20								
		30 OVER	± 0.2	APPROVED BY KMORIKAWA	DATE 2013/03/15	molex							
		ANGULAR ±3 °		MATERIAL NO.							DOCUMENT NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-52610-051						1 OF 5		
	0	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							





24	29.4	25.4	15.25	11.32	52610-1034	10
			14.25	10.32	52610-0934	9
			13.25	9.32	52610-0834	8
			12.25	8.32	52610-0734	7
			11.25	7.32	52610-0634	6
キャリアテープ幅 CARRIER TAPE WIDTH		D	C	(B)	(A)	MATERIAL. NO.
						極数 CKT.

SEE SHEET 1 OF 5 EC NO.: J2013-1003 DRAWN: AISHII 2013/02/20 CHKD: TAKAHASHI 2013/02/20 APPR: KMORIKAWA 2013/03/15	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.3	DRAWN BY AISHII		DATE 2013/02/20		TITLE EMBOSS TAPE PACKAGED FOR 1.0 FPC CONN ZIF S/T HOUSING ASSY molex		
		10 OVER 30 UNDER	±0.25	CHECKED BY TAKAHASHI		DATE 2013/02/20				
		30 OVER	±0.2	APPROVED BY KMORIKAWA		DATE 2013/03/15				
	REV	ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-52610-051		2 OF 5				
0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									



tb_frame_A3_J_ME_S
Rev G 2012/01/25



tb_frame_A3_J_ME_S
Rev G 2012/01/25

