







P.C.B. LAYOUT

*Part Number: Add 1 for .3 spacing on 24(1) and 28(1) contacts

P/N	Contact	Dim A	Dim B	Dim C	Dim D	P/N	Contact	Dim A	Dim B	Dim C	Dim D
WMS-060Z	06	7.62	5.08	7.62	10.16	WMS-240Z	24	30.48	27.94	15.24	17.78
WMS-080Z	08	10.16	7.62	7.62	10.16	WMS-280Z	28	35.56	33.02	15.24	17.78
WMS-100Z	10	12.70	10.16	7.62	10.16	WMS-320Z	32	40.64	38.10	15.24	17.78
WMS-140Z	14	17.78	15.24	7.62	10.16	WMS-400Z	40	50.80	48.26	15.24	17.78
WMS-160Z	16	20.32	17.78	7.62	10.16	WMS-420Z	42	53.34	50.80	15.24	17.78
WMS-180Z	18	22.86	20.32	7.62	10.16	WMS-480Z	48	60.96	58.42	15.24	17.78
WMS-200Z	20	25.40	22.86	7.62	10.16	WMS-640Z	64	81.28	78.74	22.86	25.40
WMS-2410Z	24	30.48	27.94	7.62	10.16						
WMS-2810Z	28	35.56	33.02	7.62	10.16						

Technical Data

Material:

Pin/outer sleeve: Brass, machined CuZn38Pb2
 Clip (contact & finger): Beryllium copper, heat treated or PH2Z
 Plating (outer sleeve): Tin plated: 2um/80u nickel, 5um/200u Tin
 Plating clip/contact: 2um/80 u nickel, gold flash

Electrical

Current rating: 3 Amps/contact max.
 Contact resistance: 4m /contact
 Rated voltage: 100 VRMS/150VDC
 Mechanical
 Operating temperature: -40° C to +105° C
 [continuous]
 -67° F to +105° F

Mechanical

Average insertion force with steel pin of EX 0.43mm/0.017" ~ 250g
 Average withdrawal force with steel pin of EX 0.43mm/0.017" ~ 50g
 Mechanical life: min. 200 Cycles
 Environmental data
 Solderability IEC 60068-2-20, Ta1: 235° C, 2s
 Resistance to soldering heat IEC 60068-2-20, Tb1:
 - Through hole mount components: 260° C, 10s

RoHS Compliant

- Biodegradable Carrier
- Environmentally Friendly
- Auto Insertable
- Dissolves in Water: The Wash-Away socket carrier completely dissolves in water as the board is being washed in any of the standard board washing systems.



ON-SHORE TECHNOLOGY, INC.

TITLE		PART NO.		DWG NO.		WMS-0Z.dwg		Tolerance	
WMS-XX0Z	WMS-XX0Z	DESIGNED	DRAWN	CUST NO.	UNIT: mm	SCALE: NONE	REV: D	X, ±0.50	X, ±0.30
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	UNIT: mm	SCALE: NONE	REV: D	X, ±0.50	X, ±0.30
Aaron	Aaron	Aaron	Aaron	Aaron	Aaron	Aaron	Aaron	X, ±0.50	X, ±0.30
2006.011Z	2006.011Z	2006.011Z	2006.011Z	2006.011Z	2006.011Z	2006.011Z	2006.011Z	X, ±0.50	X, ±0.30

THESE DIMENSIONS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC. / PATENTED