

74VCX16245

Low Voltage 16-Bit Bidirectional Transceiver with 3.6V Tolerant Inputs and Outputs

General Description

The VCX16245 contains sixteen non-inverting bidirectional buffers with 3-STATE outputs and is intended for bus oriented applications. The device is byte controlled. Each byte has separate 3-STATE control inputs which can be shorted together for full 16-bit operation. The T/R inputs determine the direction of data flow through the device. The OE inputs disable both the A and B ports by placing them in a high impedance state.

The 74VCX16245 is designed for low voltage (1.8V, 2.5V or 3.3V) V_{CC} applications with I/O compatibility up to 3.6V.

The 74VCX16245 is fabricated with an advanced CMOS technology to achieve high speed operation while maintaining low CMOS power dissipation.

Features


- 1.8V–3.6V V_{CC} supply operation
- 3.6V tolerant inputs and outputs
- t_{PD} :
 - 2.5 ns max for 3.0V to 3.6V V_{CC}
 - 3.2 ns max for 2.3V to 2.7V V_{CC}
 - 5.7 ns max for 1.8V V_{CC}
- Power-down high impedance inputs and outputs
- Support live insertion/withdrawal
- Static Drive (I_{OH}/I_{OL}):
 - ±24 mA @ 3.0V V_{CC}
 - ±18 mA @ 2.3V V_{CC}
 - ±6 mA @ 1.8V V_{CC}
- Uses patented noise/EMI reduction circuitry
- Latchup performance exceeds 300 mA
- ESD performance:
 - Human body model > 2000V
 - Machine model > 200V

Ordering Code:


Ordering Number	Package Number	Package Description
74VCX16245MTD	MTD48	48-Lead Molded, JEDEC

Surface mount packages are also available on Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

Logic Symbol



Connection Diagram



DS012169-2

Pin Descriptions

Pin Names	Description
OE	Output Enable Input
T/R	Transmit/Receive Input
A ₀ –A ₁₅	Side A Inputs or 3-STATE Outputs
B ₀ –B ₁₅	Side B Inputs or 3-STATE Outputs

Truth Tables

Inputs		Outputs
OE ₁	T/R ₁	
L	L	Bus B ₀ –B ₇ Data to Bus A ₀ –A ₇
L	H	Bus A ₀ –A ₇ Data to Bus B ₀ –B ₇
H	X	HIGH Z State on A ₀ –A ₇ , B ₀ –B ₇

Inputs		Outputs
OE ₂	T/R ₂	
L	L	Bus B ₈ –B ₁₅ Data to Bus A ₈ –A ₁₅
L	H	Bus A ₈ –A ₁₅ Data to Bus B ₈ –B ₁₅
H	X	HIGH Z State on A ₈ –A ₁₅ , B ₈ –B ₁₅

H = High Voltage Level

L = Low Voltage Level

X = Immaterial (HIGH or LOW, inputs and I/O's may not float)

Z = High Impedance

Absolute Maximum Ratings (Note 1)

Supply Voltage (V_{CC})	-0.5V to +4.6V
DC Input Voltage (V_I)	-0.5V to +4.6V
Output Voltage (V_O)	
Outputs Tri-Stated	-0.5V to +4.6V
Outputs Active (Note 2)	-0.5 to V_{CC} + 0.5V
DC Input Diode Current (I_{IK}) $V_I < 0V$	-50 mA
DC Output Diode Current (I_{OK})	
$V_O < 0V$	-50 mA
$V_O > V_{CC}$	+50 mA
DC Output Source/Sink Current (I_{OH}/I_{OL})	±50 mA
DC V_{CC} or Ground Current per Supply Pin (I_{CC} or Ground)	±100 mA
Storage Temperature Range (T_{STG})	-65°C to +150°C

Recommended Operating Conditions

(Note 3)

Power Supply	
Operating	1.8V to 3.6V
Data Retention Only	1.2V to 3.6V
Input Voltage	-0.3V to 3.6V
Output Voltage (V_O)	
Output in Active States	0V to V_{CC}
Output in 3-State	0.0V to 3.6V
Output Current in I_{OH}/I_{OL}	
$V_{CC} = 3.0V$ to 3.6V	±24 mA
$V_{CC} = 2.3V$ to 2.7V	±18 mA
$V_{CC} = 1.8V$	±6 mA
Free Air Operating Temperature (T_A)	-40°C to +85°C
Minimum Input Edge Rate (dT/dV)	
$V_{IN} = 0.8V$ to 2.0V, $V_{CC} = 3.0V$	10 ns/V

Note 1: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the Absolute Maximum Ratings. The Recommended Operating Conditions tables will define the conditions for actual device operation.

Note 2: I_O Absolute Maximum Rating must be observed.

Note 3: Floating or unused pin (inputs or I/O's) must be held HIGH or LOW.

DC Electrical Characteristics (2.7V < $V_{CC} \leq 3.6V$)

Symbol	Parameter	Conditions	V_{CC} (V)	Min	Max	Units
V_{IH}	High Level Input Voltage		2.7–3.6	2.0		V
V_{IL}	Low Level Input Voltage		2.7–3.6		0.8	V
V_{OH}	High Level Output Voltage	$I_{OH} = -100 \mu A$ $I_{OH} = -12 \text{ mA}$ $I_{OH} = -18 \text{ mA}$ $I_{OH} = -24 \text{ mA}$	2.7–3.6 2.7 3.0 3.0	$V_{CC} - 0.2$ 2.2 2.4 2.2		V
V_{OL}	Low Level Output Voltage	$I_{OL} = 100 \mu A$ $I_{OL} = 12 \text{ mA}$ $I_{OL} = 18 \text{ mA}$ $I_{OL} = 24 \text{ mA}$	2.7–3.6 2.7 3.0 3.0		0.2 0.4 0.4 0.55	V
I_I	Input Leakage Current	$0V \leq V_I \leq 3.6V$	2.7–3.6		±5.0	μA
I_{OZ}	3-STATE Output Leakage	$0V \leq V_O \leq 3.6V$ $V_I = V_{IH}$ or V_{IL}	2.7–3.6		±10	μA
I_{OFF}	Power Off Leakage Current	$0V \leq (V_I, V_O) \leq 3.6V$	0		10	μA
I_{CC}	Quiescent Supply Current	$V_I = V_{CC}$ or GND $V_{CC} \leq (V_I, V_O) \leq 3.6V$	2.7–3.6 2.7–3.6		20 ±20	μA
ΔI_{CC}	Increase in I_{CC} per Input	$V_{IH} = V_{CC} - 0.6V$	2.7–3.6		750	μA

DC Electrical Characteristics ($2.3V \leq V_{CC} \leq 2.7V$)

Symbol	Parameter	Conditions	V_{CC} (V)	Min	Max	Units
V_{IH}	High Level Input Voltage		2.3–2.7	1.6		V
V_{IL}	Low Level Input Voltage		2.3–2.7		0.7	V
V_{OH}	High Level Output Voltage	$I_{OH} = -100 \mu A$ $I_{OH} = -6 \text{ mA}$ $I_{OH} = -12 \text{ mA}$ $I_{OH} = -18 \text{ mA}$	2.3–2.7 2.3 2.3 2.3	$V_{CC} - 0.2$ 2.0 1.8 1.7		V
V_{OL}	Low Level Output Voltage	$I_{OL} = 100 \mu A$ $I_{OL} = 12 \text{ mA}$ $I_{OL} = 18 \text{ mA}$	2.3–2.7 2.3 2.3		0.2 0.4 0.6	V
I_I	Input Leakage Current	$0 \leq V_I \leq 3.6V$	2.3–2.7		± 5.0	μA
I_{OZ}	3-STATE Output Leakage	$0 \leq V_O \leq 3.6V$ $V_I = V_{IH} \text{ or } V_{IL}$	2.3–2.7		± 10	μA
I_{OFF}	Power Off Leakage Current	$0 \leq (V_I, V_O) \leq 3.6V$	0		10	μA
I_{CC}	Quiescent Supply Current	$V_I = V_{CC} \text{ or GND}$ $V_{CC} \leq (V_I, V_O) \leq 3.6V$	2.3–2.7 2.3–2.7		20 ± 20	μA

DC Electrical Characteristics ($1.8V \leq V_{CC} < 2.3V$)

Symbol	Parameter	Conditions	V_{CC} (V)	Min	Max	Units
V_{IH}	High Level Input Voltage		1.8–2.3	$0.7 \times V_{CC}$		V
V_{IL}	Low Level Input Voltage		1.8–2.3		$0.2 \times V_{CC}$	V
V_{OH}	High Level Output Voltage	$I_{OH} = -100 \mu A$ $I_{OH} = -6 \text{ mA}$	1.8 1.8	$V_{CC} - 0.2$ 1.4		V
V_{OL}	Low Level Output Voltage	$I_{OL} = 100 \mu A$ $I_{OL} = 6 \text{ mA}$	1.8 1.8		0.2 0.3	V
I_I	Input Leakage Current	$0 \leq V_I \leq 3.6V$	1.8		± 5.0	μA
I_{OZ}	3-STATE Output Leakage	$0 \leq V_O \leq 3.6V$ $V_I = V_{IH} \text{ or } V_{IL}$	1.8		± 10	μA
I_{OFF}	Power Off Leakage Current	$0 \leq (V_I, V_O) \leq 3.6V$	0		10	μA
I_{CC}	Quiescent Supply Current	$V_I = V_{CC} \text{ or GND}$ $V_{CC} \leq (V_I, V_O) \leq 3.6V$	1.8 1.8		20 ± 20	μA

AC Electrical Characteristics

(Note 4)

Symbol	Parameter	T _A = −40°C to +85°C, C _L = 30 pF, R _L = 500Ω						Units
		V _{CC} = 3.3V ±0.3V		V _{CC} = 2.5 ±0.2V		V _{CC} = 1.8V		
		Min	Max	Min	Max	Min	Max	
t _{PHL} , t _{PLH}	Prop Delay	0.8	2.5	1.0	3.2	1.5	5.7	ns
t _{PZL} , t _{PZH}	Output Enable Time	0.8	3.8	1.0	4.9	1.5	7.5	ns
t _{PLZ} , t _{PHZ}	Output Disable Time	0.8	3.7	1.0	4.2	1.5	5.5	ns
t _{OSHL} t _{OSLH}	Output to Output Skew (Note 5)		0.5		0.5		0.5	ns

Note 4: For $C_L = 50\text{pF}$, add approximately 300ps to the Ac maximum specification.

Note 5: Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH to LOW (t_{OSHL}) or LOW to HIGH (t_{OSLH}).


Dynamic Switching Characteristics

Symbol	Parameter	Conditions	V_{CC} (V)	$T_A = +25^{\circ}\text{C}$	Units
				Typical	
V_{OLP}	Quiet Output Dynamic Peak V_{OL}	$C_L = 30\text{ pF}, V_{IH} = V_{CC}, V_{IL} = 0\text{V}$	1.8 2.5 3.3	0.25 0.6 0.8	V
V_{OLV}	Quiet Output Dynamic Valley V_{OL}	$C_L = 30\text{ pF}, V_{IH} = V_{CC}, V_{IL} = 0\text{V}$	1.8 2.5 3.3	-0.25 -0.6 -0.8	V
V_{OHV}	Quiet Output Dynamic Valley V_{OH}	$C_L = 30\text{ pF}, V_{IH} = V_{CC}, V_{IL} = 0\text{V}$	1.8 2.5 3.3	1.5 1.9 2.2	V

Capacitance

Symbol	Parameter	Conditions	$T_A = +25^{\circ}\text{C}$	Units
C_{IN}	Input Capacitance	$V_{CC} = 1.8\text{V}, 2.5\text{V}, \text{ or } 3.3\text{V}, V_I = 0\text{V or } V_{CC}$	6	pF
$C_{I/O}$	Output Capacitance	$V_I = 0\text{V}, \text{ or } V_{CC}, V_{CC} = 1.8\text{V}, 2.5\text{V or } 3.3\text{V}$	7	pF
C_{PD}	Power Dissipation Capacitance	$V_I = 0\text{V or } V_{CC}, F = 10\text{ MHz}$ $V_{CC} = 1.8\text{V}, 2.5\text{V or } 3.3\text{V}$	20	pF


AC Loading and Waveforms



DS012169-3


FIGURE 1. AC Test Circuit

TEST	SWITCH
t_{PLH} , t_{PHL}	Open
t_{PZL} , t_{PLZ}	6V at $V_{CC} = 3.3 \pm 0.3V$; $V_{CC} \times 2$ at $V_{CC} = 2.5 \pm 0.2V$; 1.8V
t_{PZH} , t_{PHZ}	GND




DS012169-4

FIGURE 2. Waveform for Inverting and Non-inverting Functions



DS012169-5

FIGURE 3. 3-STATE Output High Enable and Disable Times for Low Voltage Logic



DS012169-6

FIGURE 4. 3-STATE Output Low Enable and Disable Times for Low Voltage Logic

Symbol	V_{CC}		
	3.3V $\pm 0.3V$	2.5V $\pm 0.2V$	1.8V
V_{mi}	1.5V	$V_{CC}/2$	$V_{CC}/2$
V_{mo}	1.5V	$V_{CC}/2$	$V_{CC}/2$
V_x	$V_{OL} + 0.3V$	$V_{OL} + 0.15V$	$V_{OL} + 0.15V$
V_y	$V_{OH} - 0.3V$	$V_{OH} - 0.15V$	$V_{OH} - 0.15V$

The device number is used to form part of a simplified purchasing code where the package type and temperature range are defined as follows:

DS012169-7

The drawing illustrates the mechanical specifications for a 48-pin D-sub connector. It includes three main views: a front view, a side view, and a detail view of the lead profile.

Front View: Shows the connector's footprint with 48 pins (24 on each side). Key dimensions include a total width of 12.5 ± 0.1 , a pin pitch of 0.25 , and a body height of 8.1 . A centerline is indicated by a dashed line. A feature callout 0.1 C is shown for the lead tips.

Side View: Shows the connector's profile with a total height of 6.1 ± 0.1 . It includes a feature callout 0.2 C B A for the lead tips and a note "ALL LEAD TIPS".

Detail View: A cross-sectional view of the lead profile. It shows the "GAGE PLANE" at a height of 0.25 and the "SEATING PLANE" at a height of 0.60 . The lead thickness is specified as $+0.15 / -0.10$. The lead angle is indicated as $0^\circ - 8^\circ$. A note "SEE DETAIL A" points to the lead profile.

Additional Dimensions and Callouts:

- Pin 1 is indicated on the left side.
- Pin 24 is indicated on the right side.
- A feature callout 0.1 C is shown for the lead tips.
- A feature callout 0.2 C B A is shown for the lead tips.
- A note "ALL LEAD TIPS" is present.
- A dimension of 1.1 MAX is shown for the lead height.
- A dimension of $0.10 \pm 0.05 \text{ TYP}$ is shown for the lead thickness.
- A dimension of $0.09 - 0.20 \text{ TYP}$ is shown for the lead width.
- A dimension of $0.17 - 0.27 \text{ TYP}$ is shown for the lead length.
- A dimension of 0.5 TYP is shown for the lead width.
- A feature callout 0.13 M A B S C S is shown for the lead tips.
- A feature callout 0.1 C is shown for the lead tips.
- A feature callout 0.2 C B A is shown for the lead tips.
- A note "ALL LEAD TIPS" is present.
- A note "SEE DETAIL A" points to the lead profile.

48-Lead Thin Shrink Small Outline Package, JEDEC, 6.1 mm Body Width
Order Number 74VCX16245MTD or 74VCX16245MTDX
Package Number MTD48

MTD48 (REV A)

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Fairchild Semiconductor
Corporation
Americas
Customer Response Center
Tel: 1-888-522-5372

www.fairchildsemi.com

Fairchild Semiconductor
Europe
Fax: +49 (0) 1 80-530 85 86
Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 8 141-35-0
English Tel: +44 (0) 1 793-85-68-56
Italy Tel: +39 (0) 2 57 5631

Fairchild Semiconductor
Hong Kong Ltd.
13th Floor, Straight Block,
Ocean Centre, 5 Canton Rd.
Tsimshatsui, Kowloon
Hong Kong
Tel: +852 2737-7200
Fax: +852 2314-0061

National Semiconductor
Japan Ltd.
Tel: 81-3-5620-6175
Fax: 81-3-5620-6179