






- NOTES:**
- 1 MATERIAL CONTACT; PHOSPHORBRONZE
 - 2 MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY) UL-RATING 49V0
 - 3 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
 - 4 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
 - 5 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
 - 6 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
 - 7 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
 - 8 CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.
 - 9 CONNECTOR MARKED WITH PARTNUMBER AND DATECODE. THE MARKING CAN APPEAR ON THE FRONT SIDE OR ON THE BACK SIDE.
 - 10 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID. 110 HOLES.
 - 11 FITS WITH INTEGRATED GROUND RETURN UPPERSHIELD, BASIC P.N. 5338107 AND INTEGRATED GROUND RETURN LOWERSHIELD, BASIC P.N. 5338108
 - 12 AREA RESERVED FOR CODING KEY, BASIC P.N. 100526
 - 13 CONNECTOR ASSEMBLED WITH ALTERNATE FEMALE CONTACTS.
 - 0.76µm MIN. GOLD PLATING AT MATING SURFACES.



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
F		ECR-16-013297	21JUL2017	FL	SY



		2 3 3		1	3-5100147-0	1 2
OBSOLETE		2 6 7		1	1-5100147-9	1 2
		2 5 7		1	5100147-9	1 2
OBSOLETE		2 4		1	5100147-4	1 2
		2 3		1	5100147-1	1 2
		FINISH		MATERIAL		PARTNUMBER
ENT.		DWN K.N.KIRAN	05AUG2004	TE TE Connectivity		
CHK		B.MOOIJ	22SEP2004			
APVD		B.MOOIJ	22SEP2004			
PRODUCT SPEC						
S.ED:		Z-PACK 2mm HM TYPE A				
		110 POS. FEMALE CONNECTOR				
0.2		-				
		APPLICATION SPEC				
		108-19082				
		114-19029				
		RESTRICTED TO				
		-				
		WEIGHT 0.00000				
		A2 00779 C=5100147				
		CUSTOMER DRAWING				
		SCALE 5:1				
		SHEET 1 of 1				
		REV F				