



SINGLE COLOR LED


3mm Round Shape



KR3301X

HIGH BRIGHTNESS COLOR

Outline Dimensions



Absolute Maximum Ratings

(Ta=25°C)

Item	Symbol	Red	Units
		KR	
Power Dissipation	Pd	125	mW
Forward Current	If	50	mA
Peak Forward Current	Ifm	300	mA
Reverse Voltage	Vr	4	V
Operating Temperature	Topr	-30 to +85	°C
Storage Temperature	Tstg	-30 to +100	°C
Derating (DC)*	If	0.67	mA/°C


* Ta=25°C, Ifm applies for the pulse width 1msec. and duty cycle 1/20
The current derating for operation applies when the temperature is above 25°C

Electro-Optical Characteristics

*The viewing angle is an average and will vary by color (Ta=25°C)

Part No.	Material	Emitted Color	Lens Color	Luminous Intensity I _v			Wavelength				Forward Voltage V _f			Reverse Current I _r		Viewing Angle (2 1/2)
				MIN.	TYP.	If	Peak p TYP.	Dominant d TYP.	Spectral Line Half Width TYP.	If	TYP.	MAX.	If	MAX.	Vr	
KR3301X	GaAlAs	Red	Water Clear	70	140	20	660	647	25	20	1.8	2.5	20	100	4	50°
Units				mcd		mA	nm			mA	V		mA	μA	V	Deg.

Spatial Distribution (x)



Operation Current Derating Chart

