

STRUCTURE                      Silicon Monolithic Integrated Circuit

PRODUCT SERIES              Low Voltage Detector IC

TYPE                              **BU49XXFVE Series**

FEATURES                      •Detection voltage lineup :0.9V~4.8V  
                                          •High precision detection voltage :  $\pm 1\%$

# ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

| Parameter                     | Symbol    | Limit              | Unit |
|-------------------------------|-----------|--------------------|------|
| Supply Voltage ※1             | VDD – GND | -0.3 to +7         | V    |
| Output Voltage ※1 CMOS Output | VOUT      | GND-0.3 to VDD+0.3 | V    |
| Power Dissipation ※2          | Pd        | 210                | mW   |
| Operating Temperature ※1      | Topr      | -40 to +125        | °C   |
| Storage Temperature Range     | Tstg      | -55 to +125        | °C   |
| Junction Temperature          | Tjmax     | 125                | °C   |

※1 Do not exceed Pd.

※2 Mounted on 70mm × 70mm × 1.6mm Glass Epoxy PCB, Pd derated at 2.1mW/°C for tempearture above Ta=25°C

NOTE : The product described in this specification is a strategic product (and/or service) subject to COCOM regulations. It should not be exported without authorization from the appropriate government.

NOTE : This product is not designed for protection against radioactive rays.

## Status of this document

The Japanese version of this document is the formal specification.


A customer may use this translation version only for a reference to help reading the formal version.

If there are any differences in translation version of this document, formal version takes priority.


**OELECTRICAL CHARACTERISTICS (Unless Otherwise Specified Ta=-25 to 125°C)**

| Parameter                                 | Symbol               | Condition                                                                   | Limit                          |                         |                                | Unit   |
|-------------------------------------------|----------------------|-----------------------------------------------------------------------------|--------------------------------|-------------------------|--------------------------------|--------|
|                                           |                      |                                                                             | Min.                           | Typ.                    | Max.                           |        |
| Detection Voltage                         | V <sub>DET</sub>     | V <sub>DD</sub> =H→L Ta=25°C                                                | V <sub>DET</sub> (T)<br>× 0.99 | V <sub>DET</sub> (T)    | V <sub>DET</sub> (T)<br>× 1.01 | V      |
| Circuit Current when ON                   | I <sub>DD1</sub>     | V <sub>DD</sub> =V <sub>DET</sub> -0.2V, V <sub>DET</sub> =0.9-1.3V         | -                              | 0.15                    | 0.88                           | μA     |
|                                           |                      | V <sub>DET</sub> =1.4-2.1V                                                  | -                              | 0.20                    | 1.05                           |        |
|                                           |                      | V <sub>DET</sub> =2.2-2.7V                                                  | -                              | 0.25                    | 1.23                           |        |
|                                           |                      | V <sub>DET</sub> =2.8-3.3V                                                  | -                              | 0.30                    | 1.40                           |        |
|                                           |                      | V <sub>DET</sub> =3.4-4.2V                                                  | -                              | 0.35                    | 1.58                           |        |
|                                           |                      | V <sub>DET</sub> =4.3-4.8V                                                  | -                              | 0.40                    | 1.75                           |        |
| Circuit Current when OFF                  | I <sub>DD2</sub>     | V <sub>DD</sub> =V <sub>DET</sub> +2.0V, V <sub>DET</sub> =0.9-1.3V         | -                              | 0.30                    | 1.40                           | μA     |
|                                           |                      | V <sub>DET</sub> =1.4-2.1V                                                  | -                              | 0.35                    | 1.58                           |        |
|                                           |                      | V <sub>DET</sub> =2.2-2.7V                                                  | -                              | 0.40                    | 1.75                           |        |
|                                           |                      | V <sub>DET</sub> =2.8-3.3V                                                  | -                              | 0.45                    | 1.93                           |        |
|                                           |                      | V <sub>DET</sub> =3.4-4.2V                                                  | -                              | 0.50                    | 2.10                           |        |
|                                           |                      | V <sub>DET</sub> =4.3-4.8V                                                  | -                              | 0.55                    | 2.28                           |        |
| Operating Voltage Range                   | V <sub>OPL</sub>     | V <sub>OL</sub> ≤ 0.4V<br>Ta = 25°C ~ 125°C                                 | 0.70                           | -                       | -                              | V      |
|                                           |                      | V <sub>L</sub> ≤ 0.4V<br>Ta = -25°C ~ 25°C                                  | 0.90                           | -                       | -                              |        |
| 'Low' Output Current (Nch)                | I <sub>OL</sub>      | V <sub>DS</sub> =0.05V, V <sub>DD</sub> =0.85V                              | 20                             | 100                     | -                              | μA     |
|                                           |                      | V <sub>DS</sub> =0.5V, V <sub>DD</sub> =1.5V, V <sub>DET</sub> =1.7-4.8V    | 1.0                            | 3.3                     | -                              | mA     |
|                                           |                      | V <sub>DS</sub> =0.5V, V <sub>DD</sub> =2.4V, V <sub>DET</sub> =2.7-4.8V    | 3.6                            | 6.5                     | -                              |        |
| 'High' Output Current (Pch)               | I <sub>OH</sub>      | V <sub>DS</sub> =0.5V, V <sub>DD</sub> =4.8V,<br>V <sub>DET</sub> =0.9-3.9V | 1.7                            | 3.4                     | -                              | mA     |
|                                           |                      | V <sub>DS</sub> =0.5V, V <sub>DD</sub> =6.0V,<br>V <sub>DET</sub> =4.0-4.8V | 2.0                            | 4.0                     | -                              |        |
| Detection Voltage Temperature Coefficient | V <sub>DET</sub> /ΔT | Ta = -40°C ~ 125°C (Designed Guarantee)                                     | -                              | ±30                     | -                              | ppm/°C |
| Hysteresis Voltage                        | ΔV <sub>DET</sub>    | V <sub>DD</sub> =L→H→L<br>Ta = -40°C ~ 125°C                                | V <sub>DET</sub> ≤ 1.0V        | V <sub>DET</sub> × 0.03 | V <sub>DET</sub> × 0.05        | V      |
|                                           |                      |                                                                             | V <sub>DET</sub> ≥ 1.1V        | V <sub>DET</sub> × 0.03 | V <sub>DET</sub> × 0.07        |        |

V<sub>DET</sub>(T) : Standard Detection Voltage (9V to 4.8V, 0.1V step)  
Designed Guarantee. (Outgoing inspection is not done on all products.)

**OPHYSICAL DIMENSIONS, MARKING**


## OBLOCK DIAGRAM



## OPIN NO. , PIN NAME

| Pin Number | Pin Name |
|------------|----------|
| 1          | VOUT     |
| 2          | SUB      |
| 3          | N.C.     |
| 4          | VDD      |
| 5          | GND      |

NOTE: Substrate Pin should be connected with VDD

※ Please refer to technical note concerning application circuit, and etc.

## OSTANDARD DETECTION VOLTAGE AND MARKING

| Type   | Standard Detection Voltage [V] | Marking | Type   | Standard Detection Voltage [V] | Marking |
|--------|--------------------------------|---------|--------|--------------------------------|---------|
| BU4948 | 4.800                          | LH      | BU4928 | 2.800                          | KM      |
| BU4947 | 4.700                          | LG      | BU4927 | 2.700                          | KL      |
| BU4946 | 4.600                          | LF      | BU4926 | 2.600                          | KK      |
| BU4945 | 4.500                          | LE      | BU4925 | 2.500                          | KJ      |
| BU4944 | 4.400                          | LD      | BU4924 | 2.400                          | KH      |
| BU4943 | 4.300                          | LC      | BU4923 | 2.300                          | KG      |
| BU4942 | 4.200                          | LB      | BU4922 | 2.200                          | KF      |
| BU4941 | 4.100                          | LA      | BU4921 | 2.100                          | KE      |
| BU4940 | 4.000                          | KZ      | BU4920 | 2.000                          | KD      |
| BU4939 | 3.900                          | KY      | BU4919 | 1.900                          | KC      |
| BU4938 | 3.800                          | KX      | BU4918 | 1.800                          | KB      |
| BU4937 | 3.700                          | KW      | BU4917 | 1.700                          | KA      |
| BU4936 | 3.600                          | KV      | BU4916 | 1.600                          | JZ      |
| BU4935 | 3.500                          | KU      | BU4915 | 1.500                          | JY      |
| BU4934 | 3.400                          | KT      | BU4914 | 1.400                          | JX      |
| BU4933 | 3.300                          | KS      | BU4913 | 1.300                          | JW      |
| BU4932 | 3.200                          | KR      | BU4912 | 1.200                          | JV      |
| BU4931 | 3.100                          | KQ      | BU4911 | 1.100                          | JU      |
| BU4930 | 3.000                          | KP      | BU4910 | 1.000                          | JT      |
| BU4929 | 2.900                          | KN      | BU4909 | 0.900                          | JS      |

## ONOTES FOR USE

### 1 . Absolute maximum range

Absolute Maximum Ratings are those values beyond which the life of a device may be destroyed. We cannot be defined the failure mode, such as short mode or open mode. Therefore a physical security countermeasure, like fuse, is to be given when a specific mode to be beyond absolute maximum ratings is considered.

### 2 . GND potential

GND terminal should be a lowest voltage potential every state.

Please make sure all pins which are over ground even if include transient feature.

### 3 . Electrical Characteristics

Be sure to check the electrical characteristics, that is one the tentative specification will be changed by temperature, supply voltage, and external circuit.

### 4 . Bypass Capacitor for Noise Rejection

Please put into the to reject noise between VDD pin and GND. If extremely big capacitor is used, transient response might be late. Please confirm sufficiently for the point.

### 5 . Short Circuit between Terminal and Soldering

Don't short-circuit between Output pin and VDD pin, Output pin and GND pin, or VDD pin and GND pin. When soldering the IC on circuit board, please be unusually cautious about the orientation and the position of the IC. When the orientation is mistaken the IC may be destroyed.

### 6 . Electromagnetic Field

Mal-function may happen when the device is used in the strong electromagnetic field.

### 7 . The VDD line inpedance might cause oscillation because of the detection current.

### 8 . A VDD -GND capacitor (as close connection as possible) should be used in high VDD line impedance condition.

### 9 . BU49XXFVE has extremely high impedance terminals. Small leak current due to the uncleanness of PCB surface might cause unexpected operations. Application values in these conditions should be selected carefully. assumed leak resistance.

### 10. Power on reset operation

Please note that the power on reset output varies with the Vcc rise up time.

Please verify the actual operation.

### Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

#### About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.

Thank you for your accessing to ROHM product informations.  
More detail product informations and catalogs are available,  
please contact your nearest sales office.

Please contact our sales offices for details ;

|                         |                           |                            |
|-------------------------|---------------------------|----------------------------|
| U.S.A / San Diego       | TEL : +1(858)625-3630     | FAX : +1(858)625-3670      |
| Atlanta                 | TEL : +1(770)754-5972     | FAX : +1(770)754-0691      |
| Dallas                  | TEL : +1(972)312-8818     | FAX : +1(972)312-0330      |
| Germany / Dusseldorf    | TEL : +49(2154)9210       | FAX : +49(2154)921400      |
| United Kingdom / London | TEL : +44(1)908-282-666   | FAX : +44(1)908-282-528    |
| France / Paris          | TEL : +33(0)1 56 97 30 60 | FAX : +33(0) 1 56 97 30 80 |
| China / Hong Kong       | TEL : +852(2)740-6262     | FAX : +852(2)375-8971      |
| Shanghai                | TEL : +86(21)6279-2727    | FAX : +86(21)6247-2066     |
| Dalian                  | TEL : +86(411)8230-8549   | FAX : +86(411)8230-8537    |
| Beijing                 | TEL : +86(10)8525-2483    | FAX : +86(10)8525-2489     |
| Taiwan / Taipei         | TEL : +866(2)2500-6956    | FAX : +866(2)2503-2869     |
| Korea / Seoul           | TEL : +82(2)8182-700      | FAX : +82(2)8182-715       |
| Singapore               | TEL : +65-6332-2322       | FAX : +65-6332-5662        |
| Malaysia / Kuala Lumpur | TEL : +60(3)7958-8355     | FAX : +60(3)7958-8377      |
| Philippines / Manila    | TEL : +63(2)807-6872      | FAX : +63(2)809-1422       |
| Thailand / Bangkok      | TEL : +66(2)254-4890      | FAX : +66(2)256-6334       |

Japan /  
(Internal Sales)

|                                                   |                                                                                              |                       |                        |
|---------------------------------------------------|----------------------------------------------------------------------------------------------|-----------------------|------------------------|
| Tokyo                                             | 2-1-1, Yaesu, Chuo-ku, Tokyo 104-0082                                                        | TEL : +81(3)5203-0321 | FAX : +81(3)5203-0300  |
| Yokohama                                          | 2-4-8, Shin Yokohama, Kohoku-ku, Yokohama, Kanagawa 222-8575                                 | TEL : +81(45)476-2131 | FAX : +81(45)476-2128  |
| Nagoya                                            | Dainagayo Building 9F 3-28-12, Meieki, Nakamura-ku, Nagoya, Aichi 450-0002                   | TEL : +81(52)581-8521 | FAX : +81(52)561-2173  |
| Kyoto                                             | 579-32 Higashi Shiokouji-cho, Karasuma Nishi-iru, Shiokoujidori, Shimogyo-ku, Kyoto 600-8216 | TEL : +81(75)311-2121 | FAX : +81(75)314-6559  |
| (Contact address for overseas customers in Japan) |                                                                                              |                       |                        |
| Yokohama                                          |                                                                                              | TEL : +81(45)476-9270 | FAX : +81(045)476-9271 |