


**Small Signal Product**

**500mW, 2% Tolerance SMD Zener Diode**

**FEATURES**

- Wide zener voltage range selection : 2.4V to 75V
- Surface Mount Device Type
- Moisture sensitivity level 1
- Pb free and RoHS compliant
- Green compound (Halogen free) with suffix "G" on packing code and prefix "G" on date code
- Ideal for Surface Mounted Applications
- $V_Z$  Tolerance Selection of  $\pm 2\%$
- Matte Tin(Sn) lead finish with Nickel(Ni) underplate



**SOD-123F**




**MECHANICAL DATA**

- Case: Flat lead SOD-123 small outline plastic package
- Terminal: Matte tin plated, lead free, solderable per MIL-STD-202, Method 208 guaranteed
- High temperature soldering guaranteed: 260°C/10s
- Polarity: Indicated by cathode band
- Weight : 8.85  $\pm$  0.5mg

| MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T <sub>A</sub> =25°C unless otherwise noted) |                  |               |      |
|----------------------------------------------------------------------------------------------|------------------|---------------|------|
| PARAMETER                                                                                    | SYMBOL           | VALUE         | UNIT |
| Forward Voltage @ I <sub>F</sub> = 10mA                                                      | V <sub>F</sub>   | 1             | V    |
| Power Dissipation                                                                            | P <sub>D</sub>   | 500           | mW   |
| Thermal Resistance from Junction to Ambient (Note 1)                                         | R <sub>θJA</sub> | 350           | °C/W |
| Junction Temperature                                                                         | T <sub>J</sub>   | 150           | °C   |
| Storage Temperature                                                                          | T <sub>STG</sub> | - 65 to + 150 | °C   |

Notes: 1. Valid provided that electrodes are kept at ambient temperature

**ZENER I vs. V CHARACTERISTICS**



- V<sub>BR</sub> : Voltage at I<sub>ZK</sub>
- I<sub>ZK</sub> : Test current for voltage V<sub>BR</sub>
- Z<sub>ZK</sub> : Dynamic impedance at I<sub>ZK</sub>
- I<sub>ZT</sub> : Test current for voltage V<sub>Z</sub>
- V<sub>Z</sub> : Voltage at current I<sub>ZT</sub>
- Z<sub>ZT</sub> : Dynamic impedance at I<sub>ZT</sub>
- I<sub>ZM</sub> : Maximum steady state current
- V<sub>ZM</sub> : Voltage at I<sub>ZM</sub>

## Small Signal Product

### ELECTRICAL CHARACTERISTICS

(Ratings at TA=25°C ambient temperature unless otherwise specified, and V<sub>F</sub> Forward Voltage = 1V Maximum @ I<sub>F</sub> = 10 mA for all part numbers)

| Device Type | Marking code | Zener Voltage Range              |        |        |                 | Maximun Zener Impedance           |                                   |                 | Maximun Reverse Current |                |
|-------------|--------------|----------------------------------|--------|--------|-----------------|-----------------------------------|-----------------------------------|-----------------|-------------------------|----------------|
|             |              | V <sub>Z</sub> @ I <sub>ZT</sub> |        |        | I <sub>ZT</sub> | Z <sub>ZT</sub> @ I <sub>ZT</sub> | Z <sub>ZK</sub> @ I <sub>ZK</sub> | I <sub>ZK</sub> | I <sub>R</sub>          | V <sub>R</sub> |
|             |              | Min(V)                           | Nom(V) | Max(V) | mA              | Ohm                               |                                   | mA              | uA                      | V              |
| BZT52B2V4   | 2V4B         | 2.35                             | 2.40   | 2.45   | 5               | 100                               | 564                               | 1               | 45                      | 1              |
| BZT52B2V7   | 2V7B         | 2.65                             | 2.70   | 2.75   | 5               | 100                               | 564                               | 1               | 18                      | 1              |
| BZT52B3V0   | 3V0B         | 2.94                             | 3.00   | 3.06   | 5               | 100                               | 564                               | 1               | 9                       | 1              |
| BZT52B3V3   | 3V3B         | 3.23                             | 3.30   | 3.37   | 5               | 95                                | 564                               | 1               | 4.5                     | 1              |
| BZT52B3V6   | 3V6B         | 3.53                             | 3.60   | 3.67   | 5               | 90                                | 564                               | 1               | 4.5                     | 1              |
| BZT52B3V9   | 3V9B         | 3.82                             | 3.90   | 3.98   | 5               | 90                                | 564                               | 1               | 2.7                     | 1              |
| BZT52B4V3   | 4V3B         | 4.21                             | 4.30   | 4.39   | 5               | 90                                | 564                               | 1               | 2.7                     | 1              |
| BZT52B4V7   | 4V7B         | 4.61                             | 4.70   | 4.79   | 5               | 80                                | 470                               | 1               | 2.7                     | 2.0            |
| BZT52B5V1   | 5V1B         | 5.00                             | 5.10   | 5.20   | 5               | 60                                | 451                               | 1               | 1.8                     | 2.0            |
| BZT52B5V6   | 5V6B         | 5.49                             | 5.60   | 5.71   | 5               | 40                                | 376                               | 1               | 0.9                     | 2.0            |
| BZT52B6V2   | 6V2B         | 6.08                             | 6.20   | 6.32   | 5               | 10                                | 141                               | 1               | 2.7                     | 4.0            |
| BZT52B6V8   | 6V8B         | 6.66                             | 6.80   | 6.94   | 5               | 15                                | 75                                | 1               | 1.8                     | 4.0            |
| BZT52B7V5   | 7V5B         | 7.35                             | 7.50   | 7.65   | 5               | 15                                | 75                                | 1               | 0.9                     | 5.0            |
| BZT52B8V2   | 8V2B         | 8.04                             | 8.20   | 8.36   | 5               | 15                                | 75                                | 1               | 0.63                    | 5.0            |
| BZT52B9V1   | 9V1B         | 8.92                             | 9.10   | 9.28   | 5               | 15                                | 94                                | 1               | 0.45                    | 6.0            |
| BZT52B10    | 10VB         | 9.80                             | 10.00  | 10.20  | 5               | 20                                | 141                               | 1               | 0.18                    | 7.0            |
| BZT52B11    | 11VB         | 10.78                            | 11.00  | 11.22  | 5               | 20                                | 141                               | 1               | 0.09                    | 8.0            |
| BZT52B12    | 12VB         | 11.76                            | 12.00  | 12.24  | 5               | 25                                | 141                               | 1               | 0.09                    | 8.0            |
| BZT52B13    | 13VB         | 12.74                            | 13.00  | 13.26  | 5               | 30                                | 160                               | 1               | 0.09                    | 8.0            |
| BZT52B15    | 15VB         | 14.70                            | 15.00  | 15.30  | 5               | 30                                | 188                               | 1               | 0.045                   | 10.5           |
| BZT52B16    | 16VB         | 15.68                            | 16.00  | 16.32  | 5               | 40                                | 188                               | 1               | 0.045                   | 11.2           |
| BZT52B18    | 18VB         | 17.64                            | 18.00  | 18.36  | 5               | 45                                | 212                               | 1               | 0.045                   | 12.6           |
| BZT52B20    | 20VB         | 19.60                            | 20.00  | 20.40  | 5               | 55                                | 212                               | 1               | 0.045                   | 14.0           |
| BZT52B22    | 22VB         | 21.56                            | 22.00  | 22.44  | 5               | 55                                | 235                               | 1               | 0.045                   | 15.4           |
| BZT52B24    | 24VB         | 23.52                            | 24.00  | 24.48  | 5               | 70                                | 235                               | 1               | 0.045                   | 16.8           |
| BZT52B27    | 27VB         | 26.46                            | 27.00  | 27.54  | 2               | 80                                | 282                               | 0.5             | 0.045                   | 18.9           |
| BZT52B30    | 30VB         | 29.40                            | 30.00  | 30.60  | 2               | 80                                | 282                               | 0.5             | 0.045                   | 21.0           |
| BZT52B33    | 33VB         | 32.34                            | 33.00  | 33.66  | 2               | 80                                | 306                               | 0.5             | 0.045                   | 23.0           |
| BZT52B36    | 36VB         | 35.28                            | 36.00  | 36.72  | 2               | 90                                | 329                               | 0.5             | 0.045                   | 25.2           |
| BZT52B39    | 39VB         | 38.22                            | 39.00  | 39.78  | 2               | 130                               | 329                               | 0.5             | 0.045                   | 27.3           |
| BZT52B43    | 43VB         | 42.14                            | 43.00  | 43.86  | 2               | 150                               | 353                               | 0.5             | 0.045                   | 30.1           |
| BZT52B47    | 47VB         | 46.06                            | 47.00  | 47.94  | 2               | 170                               | 353                               | 0.5             | 0.045                   | 33.0           |
| BZT52B51    | 51VB         | 49.98                            | 51.00  | 52.02  | 2               | 180                               | 376                               | 0.5             | 0.045                   | 35.7           |
| BZT52B56    | 56VB         | 54.88                            | 56.00  | 57.12  | 2               | 200                               | 400                               | 0.5             | 0.045                   | 39.2           |
| BZT52B62    | 62VB         | 60.76                            | 62.00  | 63.24  | 2               | 215                               | 423                               | 0.5             | 0.045                   | 43.4           |
| BZT52B68    | 68VB         | 66.64                            | 68.00  | 69.36  | 2               | 240                               | 447                               | 0.5             | 0.045                   | 47.6           |
| BZT52B75    | 75VB         | 73.50                            | 75.00  | 76.50  | 2               | 255                               | 470                               | 0.5             | 0.045                   | 52.5           |

Notes : 1. The Zener Voltage (V<sub>Z</sub>) is tested under pulse condition of 10ms.

2. The device numbers listed have a standard tolerance on the nominal zener voltage of ±2%.

3. For detailed information on price, availability and delivery of nominal zener voltages between the voltages shown and tighter voltage tolerances, contact your nearest **Taiwan Semiconductor** representative.

4. The Zener impedance is derived from the 60-cycle ac voltage, which results when an ac current having an RMS value equal to 10% of the dc zener current is superimposed to I<sub>ZT</sub> or I<sub>ZK</sub>.

## Small Signal Product

### RATINGS AND CHARACTERISTICS CURVES

( $T_A=25^\circ\text{C}$  unless otherwise noted)

Fig. 1 Typical Forward Characteristics




Fig. 2 Zener Breakdown Characteristics




Fig. 3 Zener Breakdown Characteristics




Fig. 4 Admissible Power Dissipation Curve




Fig. 5 Typical Capacitance





Fig. 6 Effect of Zener Voltage on Impedance



**Small Signal Product**

| ORDERING INFORMATION |                          |              |                     |          |              |
|----------------------|--------------------------|--------------|---------------------|----------|--------------|
| PART NO.             | MANUFACTURE CODE (Note1) | PACKING CODE | GREEN COMPOUND CODE | PACKAGE  | PACKING      |
| BZT52Bxxx (Note2)    |                          | RH           | G                   | SOD-123F | 3K / 7" Reel |


Note1: Manufacture special control, if empty means no special control requirement.

Note2: "xxx" is Device Code from "2V4" thru "75", detail could follow the previous page

| EXAMPLE          |           |                  |              |                     |                |
|------------------|-----------|------------------|--------------|---------------------|----------------|
| PREFERRED P/N    | PART NO.  | MANUFACTURE CODE | PACKING CODE | GREEN COMPOUND CODE | DESCRIPTION    |
| BZT52B2V4 RHG    | BZT52B2V4 |                  | RH           | G                   | Green compound |
| BZT52B2V4-B0 RHG | BZT52B2V4 | B0               | RH           | G                   | Green compound |
| BZT52B2V4-L0 RHG | BZT52B2V4 | L0               | RH           | G                   | Green compound |


**Small Signal Product**

**DIMENSIONS**



| DIM. | Unit (mm) |      | Unit (inch) |       |
|------|-----------|------|-------------|-------|
|      | Min       | Max  | Min         | Max   |
| A    | 1.50      | 1.70 | 0.059       | 0.067 |
| B    | 3.30      | 3.90 | 0.130       | 0.154 |
| C    | 0.50      | 0.70 | 0.020       | 0.028 |
| D    | 2.50      | 2.70 | 0.098       | 0.106 |
| E    | 0.80      | 1.15 | 0.031       | 0.045 |
| F    | 0.05      | 0.20 | 0.002       | 0.008 |

**SUGGESTED PAD LAYOUT**



| DIM. | Unit (mm) | Unit (inch) |
|------|-----------|-------------|
|      | Typ.      | Typ.        |
| C    | 2.86      | 0.113       |
| G    | 1.52      | 0.060       |
| X    | 1.34      | 0.053       |
| X1   | 4.20      | 0.165       |
| Y    | 1.80      | 0.071       |

**Small Signal Product****Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors in accuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.