





MOLEX P/N	MATERIAL	COLOR	MFLB CKTS
45609-0001	VALOX 357	BLACK	POSITION 16
45609-0002	VALOX 357	BLACK	POSITION 8 & 16


TERMINALS ARE TO BE ORIENTED AND LOADED
IN TO THE HOUSING AS SHOWN ABOVE

- NOTES:
1. MATERIAL: POLYESTER, UL94V-0, COLOR: BLACK.
 2. PRODUCT SPECIFICATION: TBD.
 3. USE FEMALE CRIMP TERMINAL, 08-70-1047 ONLY.
(NOTE ORIENTATION OF TERMINALS)
 4. PART MATES WITH MOLEX HEADER ASSEMBLY
SERIES 45608.
 5. PACKAGING: BULK.
 6. SEE PAGE 2 OF 2 FOR PANEL CUOUT DIMENSIONS AND
THE ALLOWED BOARD TO PANEL MISALIGNMENT.


REVISE NOTE 3 EC NO: UCP2013-1206 2012/09/25 DRWN:BBE 2012/09/28 CHKD:MK/PPER 2012/10/12 APPR:FSMITH	DESCRIPTION REV	QUALITY SYMBOLS F=0 F=6 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION
				MM ONLY		3:1	METRIC	
				DRAWN BY DATE		TITLE SPOX BMI RECEPTACLE HOUSING DUAL ROW PANEL MOUNT, 16 CKT molex		
				TGREGORI 2003/12/18				
				CHECKED BY DATE				
				MCARRANZ		DOCUMENT NO. SD-45609-001		
				APPROVED BY DATE				
JCOMERCI 2009/07/24								
MATERIAL NO.		SHEET NO.						
SEE TABLE		1 OF 3						
SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						





PANEL CUTOUT
PANEL THICKNESS 1.20±0.12mm




Normal pin-wipe
Max=3.43mm
Min= 2.07mm
First make last break-wipe
Max=4.48mm
Min=3.02mm




REAR-ENTRY PANEL MOUNT ISOMETRIC VIEW



PANEL TO PCB STACK HEIGHT




RECEPTACLE
INSERT POSITION




RECEPTACLE SLIDES
INTO MOUNTED POSITION

SEE SHEET 1 EC NO: UCP2013-1206 DRWN:BBEE 2012/09/25 CHKD:MKIPPER 2012/09/28 APPR:FSMITH 2012/10/12 B2	DESCRIPTION	QUALITY SYMBOLS FA=0 FE=1 FO=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY TGREGORI	DATE 2003/12/18	TITLE SPOX BMI RECEPTACLE HOUSING DUAL ROW PANEL MOUNT, 16 CKT molex			
			4 PLACES	± ---	± ---	CHECKED BY MCARRANZ	DATE				
			3 PLACES	± ---	± ---						
			2 PLACES	± 0.25	± ---						
			1 PLACE	± 0.3	± ---	APPROVED BY JCOMERCI	DATE 2009/07/24				
			0 PLACE	±	±						
			ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.			SHEET NO.	
			DRAFT WHERE APPLICABLE		SEE TABLE		SD-45609-001			2 OF 3	
			MUST REMAIN WITHIN DIMENSIONS		SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					



MOLEX P/N	MATERIAL	COLOR	MFLB CKTS
45609-0001	VALOX 357	BLACK	POSITION 16
45609-0002	VALOX 357	BLACK	POSITION 8 & 16

FIRST MAKE
LAST BREAK
CKTS 8 & 16



SEE SHEET 1 EC NO: UCP2013-1206 DRAWN:BBEE 2012/09/25 CHKD:MKIPPER 2012/09/28 APPR:FSMITH 2012/10/12 B2	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		F_A=0 F_G=0 F_P=0		mm	INCH	DRAWN BY TGREGORI		DATE 2003/12/18	TITLE SPOX BMI RECEPTACLE HOUSING DUAL ROW PANEL MOUNT, 16 CKT		
			4 PLACES	± ---	± ---	CHECKED BY		DATE			
			3 PLACES	± ---	± ---	MCARRANZ					
			2 PLACES	± 0.25	± ---	APPROVED BY		DATE	DOCUMENT NO. SD-45609-001		
			1 PLACE	± 0.3	± ---	JCOMERC I		2009/07/24			
			0 PLACE	±	±	MATERIAL NO.					
ANGULAR ±1/2°				SEE TABLE		SHEET NO. 3 OF 3					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					