

---


**FAIRCHILD**

---

SEMICONDUCTOR™


**0.54 INCH (13.7MM)  
14 SEGMENT, DUAL DIGIT  
ALPHA - NUMERIC STICK DISPLAY**

---



BRIGHT RED MDA6110C, MDA6140C  
YELLOW MDA6310C, MDA6340C  
GREEN MDA6410C, MDA6440C  
HIGH EFF. RED MDA6910C, MDA6940C

---

**PACKAGE DIMENSIONS**

NOTES: Dimensions are in mm (inch).  
All pins are 0.5 (0.02) diameter  
Tolerances are  $\pm 0.25$  (0.1) unless otherwise noted.

---

**FEATURES**

Easy to read digits.  
2 digit common anode or cathode.  
Low power consumption.  
Bold segments that are highly visible.  
High brightness with high contrast  
White segments on a grey face.  
Directly compatible with integrated circuits.  
Rugged plastic/epoxy construction.

**APPLICATIONS**

Digital readout displays.  
Instrument panels.

---

**MODEL NUMBERS**

---

| <u>Part number</u> | <u>Color</u>  | <u>Description</u>                        |
|--------------------|---------------|-------------------------------------------|
| MDA6110C           | Bright Red    | 2 Digit; Common Anode; Rt. Hand Decimal   |
| MDA6140C           | Bright Red    | 2 Digit; Common Cathode; Rt. Hand Decimal |
| MDA6310C           | Yellow        | 2 Digit; Common Anode; Rt. Hand Decimal   |
| MDA6340C           | Yellow        | 2 Digit; Common Cathode; Rt. Hand Decimal |
| MDA6410C           | Green         | 2 Digit; Common Anode; Rt. Hand Decimal   |
| MDA6440C           | Green         | 2 Digit; Common Cathode; Rt. Hand Decimal |
| MDA6910C           | High Eff. Red | 2 Digit; Common Anode; Rt. Hand Decimal   |
| MDA6940C           | High Eff. Red | 2 Digit; Common Cathode; Rt. Hand Decimal |

(For other colour options, contact your local area Sales Office)

### ABSOLUTE MAXIMUM RATING (T<sub>A</sub>=25°C unless otherwise specified)


| Part number                                                                             | B.Red<br>MDA<br>6110C<br>6140C | Yellow<br>MDA<br>6310C<br>6340C | Green<br>MDA<br>6410C<br>6440C | High Eff. Red<br>MDA<br>6910C<br>6940C | Unit  |
|-----------------------------------------------------------------------------------------|--------------------------------|---------------------------------|--------------------------------|----------------------------------------|-------|
| Continuous forward current (I <sub>F</sub> )                                            |                                |                                 |                                |                                        |       |
| Per Segment.....                                                                        | 15                             | 20                              | 30                             | 30                                     | mA    |
| Peak forward current per die (I <sub>P</sub> ).<br>(at f = 1.0 KHz, Duty factor = 1/10) | 50                             | 80                              | 90                             | 160                                    | mA    |
| Power dissipation (P <sub>D</sub> ).....                                                | 40*                            | 70*                             | 70*                            | 90*                                    | mW    |
| *Derate Linearly From 25°C.....                                                         | 0.17                           | 0.25                            | 0.33                           | 0.33                                   | mW/°C |
| Reverse voltage per dice.....                                                           | 5V                             |                                 |                                |                                        |       |
| Operating and Storage temperature range.....                                            | - 40°C to +85°C                |                                 |                                |                                        |       |
| Lead soldering time (at 1/16 inch from the bottom of lamp).....                         | 5 seconds @ 230°C              |                                 |                                |                                        |       |

### ELECTRO - OPTICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise specified)


| Part number                                 | B. Red<br>MDA<br>6110C<br>6140C | Yellow<br>MDA<br>6310C<br>6340C | Green<br>MDA<br>6410C<br>6440C | High Eff. Red<br>MDA<br>6910C<br>6940C | Test<br>Condition       |
|---------------------------------------------|---------------------------------|---------------------------------|--------------------------------|----------------------------------------|-------------------------|
| Luminous intensity (ucd)                    |                                 |                                 |                                |                                        | I <sub>F</sub> = 20 mA  |
| minimum                                     | 500                             | 1000                            | 750                            | 1000                                   |                         |
| typical                                     | 1400                            | 4000                            | 5000                           | 4000                                   |                         |
| Forward voltage (V <sub>F</sub> )           |                                 |                                 |                                |                                        | I <sub>F</sub> = 20 mA  |
| typical                                     | 2.1                             | 2.1                             | 2.1                            | 2.0                                    |                         |
| maximum                                     | 2.6                             | 2.8                             | 2.8                            | 2.8                                    |                         |
| Peak wavelength (nm)                        | 697                             | 590                             | 570                            | 635                                    | I <sub>F</sub> = 20 mA  |
| Spectral line half width (nm)               | 90                              | 35                              | 30                             | 45                                     | I <sub>F</sub> = 20 mA  |
| Reverse breakdown voltage (V <sub>R</sub> ) | 5                               | 5                               | 5                              | 5                                      | I <sub>R</sub> = 100 uA |

## PINOUT

**MDA6X10C - Common Anode; Pin 3 - no connection**



**MDA6X40C - Common Cathode; Pin 3 - no connection**



**GRAPHICAL DETAIL: Bright Red ( $T_A = 25^\circ\text{C}$  unless otherwise specified)**




Fig.1 FORWARD CURRENT VS. FORWARD VOLTAGE.




Fig.2 SPECTRAL RESPONSE




Fig.3 RELATIVE LUMINOUS INTENSITY  
VS. FORWARD CURRENT




Fig.5 LUMINOUS INTENSITY VS. DUTY CYCLE




Fig.4 MAXIMUM ALLOWABLE DC CURRENT PER  
SEGMENT VS. A FUNCTION OF AMBIENT  
TEMPERATURE.




Fig. 6 MAX PEAK CURRENT VS. DUTY CYCLE %  
(REFRESH RATE  $f = 1 \text{ KHz}$ )

**GRAPHICAL DETAIL: Green** ( $T_A = 25^\circ\text{C}$  unless otherwise specified)




Fig.1 FORWARD CURRENT VS. FORWARD VOLTAGE.




Fig.2 SPECTRAL RESPONSE




Fig.3 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig.5 LUMINOUS INTENSITY VS. DUTY CYCLE




Fig.4 MAXIMUM ALLOWABLE DC CURRENT PER SEGMENT CS. A FUNCTION OF AMBIENT TEMPERATURE.




Fig. 6 MAX PEAK CURRENT VS. DUTY CYCLE %  
(REFRESH RATE  $f = 1 \text{ KHz}$ )

**GRAPHICAL DETAIL: High Efficiency Red ( $T_A = 25^\circ\text{C}$  unless otherwise specified)**




Fig.1 FORWARD CURRENT VS. FORWARD VOLTAGE.




Fig.2 SPECTRAL RESPONSE




Fig.3 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig.5 LUMINOUS INTENSITY VS. DUTY CYCLE




Fig.4 MAXIMUM ALLOWABLE DC CURRENT PER SEGMENT VS. A FUNCTION OF AMBIENT TEMPERATURE.




Fig. 6 MAX PEAK CURRENT VS. DUTY CYCLE %  
(REFRESH RATE  $f = 1 \text{ KHz}$ )

**GRAPHICAL DETAIL: Yellow** ( $T_A = 25^\circ\text{C}$  unless otherwise specified)




Fig.1 FORWARD CURRENT VS. FORWARD VOLTAGE.




Fig.2 SPECTRAL RESPONSE




Fig.3 RELATIVE LUMINOUS INTENSITY  
VS. FORWARD CURRENT




Fig.5 LUMINOUS INTENSITY VS. DUTY CYCLE




Fig.4 MAXIMUM ALLOWABLE DC CURRENT PER  
SEGMENT VS. A FUNCTION OF AMBIENT  
TEMPERATURE.




Fig. 6 MAX PEAK CURRENT VS. DUTY CYCLE %  
(REFRESH RATE  $f = 1 \text{ KHz}$ )



# 0.54 INCH (13.7MM) 14 SEGMENT, DUAL DIGIT ALPHA - NUMERIC STICK DISPLAY

---

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.