

# SMA 30 + L version Multi-Application buzzer

The Sonitron Multi-Application buzzers are low cost commercial grade components for large volume applications. The SMA series are designed to meet a wide range of current consumption, voltage, sound pressure, mounting methods, connection, dimensions and packing requirements. The buzzers have a built-in oscillator generating their working frequency. They produce a highly reliable audible tone signal, giving either an extremely clear and penetrating tone or a soft sound for non-aggressive signals.



## ADVANTAGES & APPLICATIONS

### ADVANTAGES :

- octagonal form
- models with different pin pitches
- light but solid state construction
- little power consumption, especially the extra loud LC-versions
- important voltage range (1,5V to 24V)
- easy mountable
- SMT models with heat resistant label for protection during automatic soldering, packed in trays for automatic placing

### APPLICATIONS :

- portable battery operating devices
- audible alarms
- gas detectors
- weighing and measuring equipment
- medical instrumentation
- timers
- control instrumentation and systems
- copiers
- automobiles
- games and toys
- computer peripherals
- cash registers, etc.

## SPECIFICATIONS

Model	Sound pressure dB(A) *	Frequency (+/- 15%) Hz	Operating voltage	Operating current	Weight
SMA-30	87 dB(A)	2.5 kHz	1.5 to 24 Vdc	4.1 mA	5 g
SMA-30L	97 dB(A) at 9V	2.5 kHz	3 to 9 Vdc	5 mA at 9V	5 g

\* All measurements are made in free air at 21°C, at 30 cm, at 12V. Buzzers soldered on a PCB board dimensions 24 cm x 11 cm.

Operating temperature	-20°C to +70°C
Storage temperature	-40°C to +85°C
Life time (at 21°C)	See expected life time curve in addendum
Case material	ABS (UL rating: 94 HB) for pin-versions PPS (UL rating: 94 V0/5V) for SMD-versions
Standard colour of case	Grey

# SMA 30 + L version Multi-Application buzzer

## ELECTRICAL PARAMETERS

	Sound pressure level vs. operating voltage	Consumption vs. operating voltage
<b>SMA-30 + L version</b>		


All measurements are made at 30 cm in free air at 21°C.

°°: standard versions, respectively SMA-30


## DIMENSIONS (All dimensions are in mm)

### SMA 30 + L Version

#### Pin version



#### SMD version



## PRODUCT CODIFICATION

<b>SMA</b>	<b>30</b>	<b>L</b>	<b>P10 P15 P 17.5 P 20.32 S</b>
↓	↓		↓
Sonitron Multi-Application	Square diameter (mm)	L : Loud	P : Pin distance (in mm) S : SMD terminals

## LIST OF AVAILABLE PRODUCT TYPES

Version	Standard (°°)	Loud (L)
SMA-30 serie	SMA-30 P15	SMA-30L P15
	SMA-30 P17.5	SMA-30L P17.5
	SMA-30 P20.32	SMA-30L P20.32
	SMA-30 S	SMA-30L S

## MODELS ON REQUEST

The SMA series can be delivered, upon special request, with the following protection :

- **Wash tabs**  
A wash tab is glued on the sound emitting hole of the buzzer to protect it from water penetrating into the hole of the cavity. The PCB at the back is also sealed with a silicon film. To order this part, please add WASHTAB to the model number of the SMA series.
- **Acryl coating**  
For applications in aggressive humid conditions, models containing a membrane with a protective coating are available. The protective coating gives a complementary assurance against smog. Add MC to the model number of the SMA series.