


# Pocket Thickness Gage

## SERIES 7



7309

A very compact thickness gage is designed for carrying convenience and is ideally suited for quick inspection of paper, leather, wire, plastic, sheet metal and similar materials. The spindle is pre-loaded to provide a constant measuring force (2N or less).

### FEATURES

- Measuring faces are hardened, ground and lapped for accuracy.
- Easy adjustment for zero point.


### SPECIFICATIONS

#### Metric

Graduation	Range	Order No.	Accuracy	Mass
0.01mm	0 - 10mm	7309	$\pm 0.01$ mm	80g

#### Inch

Graduation	Range	Order No.	Accuracy	Mass
.001"	0 - .4"	7308	$\pm .001$ "	.18 lbs.




# Female Screw Thread Comparators

## SERIES 243



243-101

### Application



### FEATURES

- Quick inspection of pitch diameters of female screw threads can be done by using interchangeable inserts (optional).
- Adjustable measuring jaws for a wide range of I.D. comparison measurements.

### SPECIFICATIONS

#### Metric

Graduation	Range	Order No.	Probe depth	Mass
0.01mm	25 - 100mm	243-101	20mm	530g
	25 - 200mm	243-102	25mm	700g
	25 - 300mm	243-103	30mm	870g

### Interchangeable Inserts Sets (Optional)

Applications	Order No.	Assortment of inserts (pair)
Metric screw, Unified screw	243-800	0.4 - 0.5mm/64 - 48TPI (243-801)
		0.6 - 0.9mm/44 - 28TPI (243-802)
		1 - 1.75mm/24 - 14TPI (243-803)
		2 - 3mm/13 - 9TPI (243-804)
		3.5 - 5mm/8 - 5TPI (243-805)
		5.5 - 7mm/4.5 - 3.5TPI (243-806)
Whitworth screw	243-810	60 - 48TPI (243-811)
		48 - 40TPI (243-812)
		40 - 32TPI (243-813)
		32 - 24TPI (243-814)
		24 - 18TPI (243-815)
		18 - 14TPI (243-816)
		14 - 10TPI (243-817)
		10 - 7TPI (243-818)
		7 - 4.5TPI (243-819)
		4.5 - 3.5TPI (243-820)