

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION ,19 .					
© COPYRIGHT 19				BY AMP INCORPORATED. ALL RIGHTS RESERVED.					
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
					F	REV PER 063A-0189-00	15MAY00	JR	TM

INSULATION

BODY

SERRATIONS

7.95 MAX DIA

[.313]

12.14 MAX

[.478]

1. USE FOR STRIPPED (SINGLE) WIRE END ONLY

2. WIRE INSUL DIA, 5.33 [.210] MAX

-		-		-		-	
MS25274/4 CLASS 1 & 2		1000		LOOSE PIECE		328309	
MILITARY P/N & CLASS		QTY		PACKAGE TYPE		PART NO	

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN L OLMEDA 21MAR96		AMP Incorporated	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [in]		CHK M ELLIS 21MAR96		Harrisburg, PA 17105-3608	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K FEREK 21MAR96		NAME	
FOR ORDER ENTRY		1-800-526-5142		VOLTAGE RATING: -		PRODUCT SPEC		SPARE WIRE CAP, WIRE SIZE, 12-10 AWG	
		CIRCULAR MIL AREA: 2.62mm ² -6.64mm ² [5,180-13,100]		MATERIAL BODY, CU PER ASTM B152		APPLICATION SPEC		DRAWING NO	
				INSUL, NYLON, COLOR, YELLOW,		WEIGHT -		SCALE 8:1	
						CUSTOMER DRAWING		SHEET 1 OF 1	
								REV F	