

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

25-02-2062

Status:

Active

Overview:

C-Grid® Products

Description:

2.54mm Pitch C-Grid® Header, Dual Row, Shrouded, with PC Slot and Guide Ear, 62 Circuits, Tin (Sn) Plating

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70204 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

70204

Application

Board-to-Board, Signal

Overview

C-Grid® Products

Product Name

C-Grid®

UPC

800753780583

Physical

Breakaway

No

Circuits (Loaded)

62

Circuits (maximum)

62

Durability (mating cycles max)

25

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

Yes

Lock to Mating Part

None

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Number of Rows

2

Orientation

Vertical

PC Tail Length

2.79mm

PCB Locator

No

PCB Retention

None

Packaging Type

Tray

Pitch - Mating Interface

2.54mm

Plating min - Mating

3.810µm

Plating min - Termination

3.810µm

Polarized to Mating Part

Yes

Polarized to PCB

No

Shrouded

Fully

Stackable

No

Temperature Range - Operating

-40°C to +105°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

3A

Voltage - Maximum


250V

Solder Process Data

Lead-free Process Capability

Wave Capable (TH only)

Material Info



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

70204Series

Mates With

71973

Old Part Number	70204-0414
Reference - Drawing Numbers	
Product Specification	PS-70204
Sales Drawing	SDA-70204-0385-0448

This document was generated on 10/15/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION