

LM98722 3 Channel, 16-Bit, 45 MSPS Analog Front End with LVDS/CMOS Output, Integrated CCD/CIS Sensor Timing Generator and Spread Spectrum Clock Generation

Check for Samples: [LM98722](#)

FEATURES

- LVDS/CMOS Outputs
- LVDS/CMOS/Crystal Clock Source with PLL Multiplication
- Integrated Flexible Spread Spectrum Clock Generation
- CDS or S/H Processing for CCD or CIS sensors
- Independent Gain/Offset Correction for Each Channel
- Automatic per-Channel Gain and Offset Calibration
- Programmable Input Clamp Voltage
- Flexible CCD/CIS Sensor Timing Generator

KEY SPECIFICATIONS

- **Maximum Input Level:**
 - 1.2 or 2.4 Volt Modes
 - (both with + or - polarity option)
- **ADC Resolution: 16-Bit**
- **ADC Sampling Rate: 45 MSPS**
- **INL: +18/-25 LSB (typ)**
- **Channel Sampling Rate: 22.5/22.5/15 MSPS**
- **PGA Gain Steps: 256 Steps**
- **PGA Gain Range: 0.64 to 8.3x**
- **Analog DAC Resolution: +/-9 Bits**
- **Analog DAC Range: +/-307mV or +/-614mV**
- **Digital DAC Resolution: +/-6 Bits**
- **Digital DAC Range: -2048 LSB to + 2016 LSB**
- **SNR: -74dB (@0dB PGA Gain)**
- **Power Dissipation: 630mW (LVDS)**
- **Operating Temp: 0 to 70°C**
- **Supply Voltage: 3.3V Nominal (3.0V to 3.6V range)**

APPLICATIONS

- **Multi-Function Peripherals**
- **High-speed Currency/Check Scanners**
- **Flatbed or Handheld Color Scanners**
- **High-speed Document Scanners**

DESCRIPTION

The LM98722 is a fully integrated, high performance 16-Bit, 45 MSPS signal processing solution for digital color copiers, scanners, and other image processing applications. High-speed signal throughput is achieved with an innovative architecture utilizing Correlated Double Sampling (CDS), typically employed with CCD arrays, or Sample and Hold (S/H) inputs (for higher speed CCD or CMOS image sensors). The signal paths utilize 8 bit Programmable Gain Amplifiers (PGA), a +/-9-Bit offset correction DAC and independently controlled Digital Black Level correction loops for each input. The PGA and offset DAC are programmed independently allowing unique values of gain and offset for each of the three analog inputs. The signals are then routed to a 45MHz high performance analog-to-digital converter (ADC). The fully differential processing channel shows exceptional noise immunity, having a very low noise floor of -74dB. The 16-bit ADC has excellent dynamic performance making the LM98722 transparent in the image reproduction chain.

A very flexible integrated Spread Spectrum Clock Generation (SSCG) modulator is included to assist with EM compliance and reduce system costs.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.


Copyright © 2009–2013, Texas Instruments Incorporated

The diagram illustrates the system architecture centered around the LM98722. The components and their interconnections are as follows:

- CCD/CIS Sensor:** Represented by a grid of 16 columns and 8 rows. It is connected to the **Analog Front End** of the LM98722 via four parallel lines.
- Sensor Drivers:** Connected to the **CCD/CIS Sensor** via a single line.
- LM98722:** The central IC, which contains several internal blocks:
 - Analog Front End:** Receives data from the **CCD/CIS Sensor** and sends it to the **Image Processor/ASIC** via an **SPI** interface.
 - CCD Timing Generator:** Receives control signals from the **Image Processor/ASIC** and sends them to the **Sensor Drivers**.
 - SSCG:** Receives a **CLK** (clock) signal from the **Image Processor/ASIC**.
- Image Processor/ASIC:** Receives data from the **Analog Front End** and sends **Data Output** to the **Motor Controllers**. It also provides control signals to the **CCD Timing Generator** and **SSCG**.
- Motor Controllers:** Receive the **Data Output** from the **Image Processor/ASIC**.

Product Folder Links: [LM98722](#)

LM98722 Pin Out Diagram



**Figure 2. TSSOP Package
See Package Number DGG0056A**

Typical Application Diagram




Figure 3. Typical Application Diagram

Pin Descriptions⁽¹⁾

Pin	Name	I/O	Typ	Res	Description
1	PHIC2	O	D	PU	Configurable high speed sensor timing output.
2	PHIC1	O	D	PD	Configurable high speed sensor timing output.
3	SH1	O	D	PU	Configurable low speed sensor timing output.
4	CE	I	D		Chip Serial Interface Address Setting Input
					CE Level Address
					V _D 01
					Float 10
					DGND 00
5	CAL	I	D	PD	Initiate calibration sequence. Leave unconnected or tie to DGND if unused.
6	RESET	I	D	PU	Active-low master reset. NC when function not being used.
7	SH_R	I	D	PD	External request for an SH interval.
8	SDI	I	D	PD	Serial Interface Data Input.
9	SDO	O	D		Serial Interface Data Output.
10	SCLK	I	D	PD	Serial Interface shift register clock.
11	SEN	I	D	PU	Active-low chip enable for the Serial Interface.
12	V _A		P		Analog power supply. Bypass voltage source with 4.7µF and pin with 0.1µF to AGND.
13	AGND		P		Analog ground return.
14	V _A		P		Analog power supply. Bypass voltage source with 4.7µF and pin with 0.1µF to AGND.
15	VREFB	O	A		Bottom of ADC reference. Bypass with a 0.1µF capacitor to ground.
16	VREFT	O	A		Top of ADC reference. Bypass with a 0.1µF capacitor to ground.
17	V _A		P		Analog power supply. Bypass voltage source with 4.7µF and pin with 0.1µF to AGND.
18	AGND		P		Analog ground return.
19	VCLP	IO	A		Input Clamp Voltage. Normally bypassed with a 0.1µF , and a 4.7µF capacitor to AGND. An external reference voltage may be applied to this pin.
20	V _A		P		Analog power supply. Bypass voltage source with 4.7µF and pin with 0.1µF to AGND.
21	IBIAS	O	A		Bias setting pin. Connect a 9.0 kOhm 1% resistor to AGND.
22	AGND		P		Analog ground return.
23	OS _R	I	A		Analog input signal. Typically sensor Red output AC-coupled thru a capacitor.
24	AGND		P		Analog ground return.
25	OS _G	I	A		Analog input signal. Typically sensor Green output AC-coupled thru a capacitor.
26	AGND		P		Analog ground return.
27	OS _B	I	A		Analog input signal. Typically sensor Blue output AC-coupled thru a capacitor.
28	CPOFILT2		A		Charge Pump Filter Capacitor. Bypass this supply pin with a 0.1µF capacitor to CPOFILT1.
29	DGND		P		Digital ground return.
30	CPOFILT1		A		Charge Pump Filter Capacitor. Bypass this supply pin with a 0.1µF capacitor to CPOFILT2.
31	DVB	O	D		Digital Core Voltage bypass. Not an input. Bypass with 0.1µF capacitor to DGND.
32	INCLK+	I	D		Clock Input. Non-Inverting input for LVDS clocks or CMOS clock input. CMOS clock is selected when pin 29 is held at DGND, otherwise clock is configured for LVDS operation.
33	INCLK-	I	D		Clock Input. Inverting input for LVDS clocks, connect to DGND for CMOS clock.
34	DOUT7/ TXCLK+	O	D		Bit 7 of the digital video output bus in CMOS Mode, LVDS Frame Clock+ in LVDS Mode.
35	DOUT6/ TXCLK-	O	D		Bit 6 of the digital video output bus in CMOS Mode, LVDS Frame Clock- in LVDS Mode.
36	DOUT5/ TXOUT2+	O	D		Bit 5 of the digital video output bus in CMOS Mode, LVDS Data Out2+ in LVDS Mode.

(1) (I=Input), (O=Output), (IO=Bi-directional), (P=Power), (D=Digital), (A=Analog), (PU=Pull Up with an internal resistor), (PD=Pull Down with an internal resistor.).

Pin Descriptions⁽¹⁾ (continued)

Pin	Name	I/O	Typ	Res	Description
37	DOUT4/ TXOUT2-	O	D		Bit 4 of the digital video output bus in CMOS Mode, LVDS Data Out2- in LVDS Mode.
38	DOUT3/ TXOUT1+	O	D		Bit 3 of the digital video output bus in CMOS Mode, LVDS Data Out1+ in LVDS Mode.
39	DOUT2/ TXOUT1-	O	D		Bit 2 of the digital video output bus in CMOS Mode, LVDS Data Out1- in LVDS Mode.
40	DOUT1/ TXOUT0+	O	D		Bit 1 of the digital video output bus in CMOS Mode, LVDS Data Out0+ in LVDS Mode.
41	DOUT0/ TXOUT0-	O	D		Bit 0 of the digital video output bus in CMOS Mode, LVDS Data Out0- in LVDS Mode.
42	DGND	O	D	PD	Configurable sensor control output.
43	V _D		P		Power supply for the digital circuits. Bypass this supply pin with 0.1µF capacitor. A single 4.7µF capacitor should be used between the supply and the VD, VR and VC pins.
44	V _C		P		Power supply for the sensor control outputs. Bypass this supply pin with 0.1µF capacitor.
45	CLKOUT/SH2	O	D		Output clock for registering output data when using CMOS outputs, or a configurable low speed sensor timing output.
46	SH3	O	D		Configurable low speed sensor timing output.
47	RS	O	D		Configurable high speed sensor timing output.
48	CP	O	D		Configurable high speed sensor timing output.
49	PHIA1	O	D		Configurable high speed sensor timing output.
50	PHIA2	O	D		Configurable high speed sensor timing output.
51	DGND		P		Digital ground return.
52	V _C		P		Power supply for the sensor control outputs. Bypass this supply pin with 0.1µF capacitor.
53	PHIB1	O	D		Configurable high speed sensor timing output.
54	PHIB2	O	D		Configurable high speed sensor timing output.
55	SH4	O	D		Configurable low speed sensor timing output.
56	SH5	O	D		Configurable low speed sensor timing output.



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

Absolute Maximum Ratings⁽¹⁾⁽²⁾⁽³⁾

Supply Voltage (V _A , V _R , V _D , V _C)		4.2V
Voltage on Any Input Pin(Not to exceed 4.2V)		–0.3V to (V _A + 0.3V)
Voltage on Any Output Pin(except DVB and not to exceed 4.2V)		–0.3V to (V _A + 0.3V)
DVB Output Pin Voltage		2.0V
Input Current at any pin other than Supply Pins ⁽⁴⁾		±25 mA
Package Input Current (except Supply Pins) ⁽⁴⁾		±50 mA
Maximum Junction Temperature (T _A)		150°C
Thermal Resistance (θ _{JA})		<66°C/W
Package Dissipation at T _A = 25°C ⁽⁵⁾		>1.89W
ESD Rating ⁽⁶⁾	Human Body Model	2500V
	Machine Model	250V
Storage Temperature		–65°C to +150°C
<i>Soldering process must comply with Texas Instrument's Reflow Temperature Profile specifications. Refer to www.ti.com/packaging ⁽⁷⁾</i>		

- (1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not ensure specific performance limits. For ensured specifications and test conditions, see the Electrical Characteristics. The ensured specifications apply only for the test conditions listed. Some performance characteristics may degrade when the device is not operated under the listed test conditions. Operation of the device beyond the Operating Ratings is not recommended.
- (2) All voltages are measured with respect to AGND = DGND = 0V, unless otherwise specified.
- (3) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/ Distributors for availability and specifications.
- (4) When the input voltage (V_{IN}) at any pin exceeds the power supplies (V_{IN} < GND or V_{IN} > V_A or V_D), the current at that pin should be limited to 25 mA. The 50 mA maximum package input current rating limits the number of pins that can simultaneously safely exceed the power supplies with an input current of 25 mA to two.
- (5) The maximum power dissipation must be derated at elevated temperatures and is dictated by T_{JMAX}, θ_{JA} and the ambient temperature, T_A. The maximum allowable power dissipation at any temperature is P_D = (T_{JMAX} – T_A)/θ_{JA}. The values for maximum power dissipation listed above will be reached only when the device is operated in a severe fault condition (e.g. when input or output pins are driven beyond the power supply voltages, or the power supply polarity is reversed). Such conditions should always be avoided.
- (6) Human body model is 100 pF capacitor discharged through a 1.5 kΩ resistor. Machine model is 220 pF discharged through 0Ω.
- (7) Reflow temperature profiles are different for lead-free and non-lead-free packages.

Operating Ratings⁽¹⁾⁽²⁾

Operating Temperature Range	0°C ≤ T _A ≤ +70°C
All Supply Voltage	+3.0V to +3.6V

- (1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not ensure specific performance limits. For ensured specifications and test conditions, see the Electrical Characteristics. The ensured specifications apply only for the test conditions listed. Some performance characteristics may degrade when the device is not operated under the listed test conditions. Operation of the device beyond the Operating Ratings is not recommended.
- (2) All voltages are measured with respect to AGND = DGND = 0V, unless otherwise specified.

Electrical Characteristics

The following specifications apply for $V_A = V_D = V_C = 3.3V$, $C_L = 10pF$, and $f_{INCLK} = 15MHz$ unless otherwise specified.

Boldface limits apply for $T_A = T_{MIN}$ to T_{MAX} ; all other limits $T_A = 25^\circ C$.

Parameter		Test Conditions	Min ⁽¹⁾	Typ ⁽²⁾	Max ⁽¹⁾⁽³⁾	Units
CMOS Digital Input DC Specifications (RESETb, SH_R, SCLK, SENb)						
V _{IH}	Logical “1” Input Voltage		2.0			V
V _{IL}	Logical “0” Input Voltage				0.8	V
V _{IHYS}	Logic Input Hysteresis			0.6		
I _{IH}	Logical “1” Input Current	V _{IH} = V _D RESET,SEN SH_R, SCLK, SDI, CAL CE		100 65 30		nA μA nA
I _{IL}	Logical “0” Input Current	V _{IL} = DGND RESETSEN SH_R, SCLK, SDI, CAL CE		-65 -100 -30		μA nA μA
CMOS Digital Output DC Specifications (SH1 to SH5, RS, CP, PHIA, PHIB, PHIC)						
V _{OH}	Logical “1” Output Voltage	I _{OUT} = -0.5mA	3.0			V
V _{OL}	Logical “0” Output Voltage	I _{OUT} = 1.6mA			0.21	V
I _{OS}	Output Short Circuit Current	V _{OUT} = DGND V _{OUT} = V _D		18 -25		mA
I _{OZ}	CMOS Output TRI-STATE Current	V _{OUT} = DGND V _{OUT} = V _D		20 -25		nA
CMOS Digital Output DC Specifications (CMOS Data Outputs)						
V _{OH}	Logical “1” Output Voltage	I _{OUT} = -0.5mA		2.3		V
V _{OL}	Logical “0” Output Voltage	I _{OUT} = 1.6mA		0.12		V
I _{OS}	Output Short Circuit Current	V _{OUT} = DGND		12		mA
		V _{OUT} = V _D		-14		
I _{OZ}	CMOS Output TRI-STATE Current	V _{OUT} = DGND		20		nA
		V _{OUT} = V _D		-25		
LVDS/CMOS Clock Receiver DC Specifications (INCLK+ and INCLK- Pins)						
V _{IHL}	Differential LVDS Clock High Threshold Voltage	R _L = 100Ω V _{CM} (LVDS Input Common Mode Voltage)= 1.25V			200	mV
V _{ILL}	Differential LVDS Clock Low Threshold Voltage		-200			mV
V _{IHC}	CMOS Clock High Threshold Voltage	INCLK- = DGND	2.0			V
V _{ILC}	CMOS Clock Low Threshold Voltage				0.8	V
I _{IHL}	CMOS Clock Input High Current			230	260	μA
I _{ILC}	CMOS Clock Input Low Current		-135	-120		μA

(1) Test limits are ensured to TI's AOQL (Average Outgoing Quality Level).

(2) Typical figures are at $T_A = 25^\circ C$, and represent most likely parametric norms at the time of product characterization. The typical specifications are not ensured.

(3) The analog inputs are protected as shown in Figure 4. Input voltage magnitudes beyond the supply rails will not damage the device, provided the current is limited per Note 4 under the Absolute Maximum Ratings Table. However, input errors will be generated if the input goes above V_A and below AGND.

Electrical Characteristics (continued)

The following specifications apply for $V_A = V_D = V_C = 3.3V$, $C_L = 10pF$, and $f_{INCLK} = 15MHz$ unless otherwise specified.

Boldface limits apply for $T_A = T_{MIN}$ to T_{MAX} ; all other limits $T_A = 25^\circ C$.

Parameter		Test Conditions	Min ⁽¹⁾	Typ ⁽²⁾	Max ⁽¹⁾⁽³⁾	Units
LVDS Output DC Specifications						
V _{OD}	Differential Output Voltage	R _L = 100Ω	280	390	490	mV
V _{OS}	LVDS Output Offset Voltage		1.08	1.20	1.33	V
I _{OS}	Output Short Circuit Current	V _{OUT} = 0V, R _L = 100Ω		8.5		mA
Power Supply Specifications						
IA	VA Analog Supply Current	LVDS Output Data Format		139	162	mA
		LVDS Output Data Format (Powerdown)		3.1	4.5	mA
		CMOS Output Data Format (40 MHz)		137	161	mA
ID	VD Digital Output Driver Supply Current	LVDS Output Data Format		50	65	mA
		LVDS Output Data Format (Powerdown)		5.5	8	mA
		CMOS Output Data Format (ATE Loading of CMOS Outputs > 50 pF) (40 MHz)		48	62	mA
IC	VC CCD Timing Generator Output Driver Supply Current	Typical sensor outputs: SH1-SH5, PHIA, PHIB, PHIC, RS, CP (ATE Loading of CMOS Outputs > 50pF)		1	4	mA
PWR	Average Power Dissipation	LVDS Output Data Format		630	736	mW
		LVDS Output Data Format (Powerdown)		28	32	mW
		CMOS Output Data Format (ATE Loading of CMOS Outputs > 50pF) (40 MHz)		600	740	mW
Input Sampling Circuit Specifications						
V _{IN}	Input Voltage Level	CDS Gain=1x, PGA Gain=1x CDS Gain=2x, PGA Gain= 1x		2.3 1.22		Vp-p
I _{IN_SH}	Sample and Hold Mode Input Leakage Current	Source Followers Off CDS Gain = 1x OS _X = VA (OS _X = AGND)	(-103)	19 (-95)	25	μA
		Source Followers Off CDS Gain = 2x OS _X = VA (OS _X = AGND)	(-152)	33 (-141)	50	μA
		Source Followers On CDS Gain = 2x OS _X = VA (OS _X = AGND)	(-250)	20 (-50)	250	nA
C _{SH}	Sample/Hold Mode Equivalent Input Capacitance	CDS Gain = 1x		2.5		pF
		CDS Gain = 2x		4		pF
I _{IN_CDS}	CDS Mode Input Leakage Current	Source Followers Off OS _X = VA (OS _X = AGND)	(-250)	10 (-50)	250	nA
R _{CLPIN}	CLPIN Switch Resistance (OS _X to VCLP Node)			16	55	Ω

Electrical Characteristics (continued)

The following specifications apply for $V_A = V_D = V_C = 3.3V$, $C_L = 10pF$, and $f_{INCLK} = 15MHz$ unless otherwise specified.

Boldface limits apply for $T_A = T_{MIN}$ to T_{MAX} ; all other limits $T_A = 25^\circ C$.

Parameter		Test Conditions	Min ⁽¹⁾	Typ ⁽²⁾	Max ⁽¹⁾⁽³⁾	Units
VCLP Reference Circuit Specifications						
V _{VCLP}	VCLP Voltage 000	VCLP Voltage Setting = 000		0.85VA		V
	VCLP Voltage 001	VCLP Voltage Setting = 001		0.9VA		V
	VCLP Voltage 010	VCLP Voltage Setting = 010		0.95VA		V
	VCLP Voltage 011	VCLP Voltage Setting = 011		0.6VA		V
	VCLP Voltage 100	VCLP Voltage Setting = 100		0.55VA		V
	VCLP Voltage 101	VCLP Voltage Setting = 101		0.4VA		V
	VCLP Voltage 110	VCLP Voltage Setting = 110		0.35VA		V
	VCLP Voltage 111	VCLP Voltage Setting = 111		0.15VA		V
I _{sc}	VCLP DAC Short Circuit Output Current	0001 xxxxb VCLP Config. Register =		30		mA
Black Level Offset DAC Specifications						
	Resolution			10		Bits
	Monotonicity		Ensured by characterization			
	Offset Adjustment Range Referred to AFE Input	CDS Gain = 1x Minimum DAC Code = 0x000 Maximum DAC Code = 0x3FF				mV
				-614		
				614		
	Offset Adjustment Range Referred to AFE Output	CDS Gain = 2x Minimum DAC Code = 0x000 Maximum DAC Code = 0x3FF		-307 307		mV
	Offset Adjustment Range Referred to AFE Output	Minimum DAC Code = 0x000 Maximum DAC Code = 0x3FF	-17500 +16130		-16130 +17500	LSB
	DAC LSB Step Size	CDS Gain = 1x Referred to AFE Output		1.2 (32)		mV (LSB)
DNL	Differential Non-Linearity		-0.85	+0.74/ -0.37	+2.4	LSB
INL	Integral Non-Linearity		-2.5	+0.72/ -0.56	+2.5	LSB
PGA Specifications						
	Gain Resolution			8		Bits
	Monotonicity		Ensured by characterization			
	Maximum Gain	CDS Gain = 1x	7.7	8.3	8.8	V/V
		CDS Gain = 1x	17.7	18.4	18.9	dB
	Minimum Gain	CDS Gain = 1x	0.58	0.64	0.70	V/V
		CDS Gain = 1x	-4.7	-4.2	-3.5	dB
	PGA Function	Gain (V/V) = (180/(277-PGA Code)) Gain (dB) = 20LOG10(180/(277-PGA Code))				
	Channel Matching	Minimum PGA Gain Maximum PGA Gain		3 12.7		%
ADC Specifications						
V _{REFT}	Top of Reference			2.07		V
V _{REFB}	Bottom of Reference			0.89		V
V _{REFT} - V _{REFB}	Differential Reference Voltage		1.06	1.18	1.30	V
	Overrange Output Code			65535		
	Underrange Output Code			0		

Electrical Characteristics (continued)

The following specifications apply for $V_A = V_D = V_C = 3.3V$, $C_L = 10pF$, and $f_{INCLK} = 15MHz$ unless otherwise specified.

Boldface limits apply for $T_A = T_{MIN}$ to T_{MAX} ; all other limits $T_A = 25^\circ C$.

Parameter		Test Conditions	Min ⁽¹⁾	Typ ⁽²⁾	Max ⁽¹⁾⁽³⁾	Units
Digital Offset “DAC” Specifications						
	Resolution			7		Bits
	Digital Offset DAC LSB Step Size	Referred to AFE Output		32		LSB
	Offset Adjustment Range	Min DAC Code =7b0000000		-2048		LSB
	Referred to AFE Output	Mid DAC Code =7b1000000		0		
		Max DAC Code = 7b1111111		+2016		
Full Channel Performance Specifications						
DNL	Differential Non-Linearity	See ⁽⁴⁾	-0.999	+0.8/-0.7	2.5	LSB
INL	Integral Non-Linearity	See ⁽⁴⁾	-75	+18/-25	75	LSB
SNR	Total Output Noise	Minimum PGA Gain ⁽⁴⁾		-76		dB
				10	26	LSB RMS
		Maximum PGA Gain ⁽⁴⁾		-56		dB
				96		LSB RMS
	Channel to Channel Crosstalk	Mode 3		26		LSB
		Mode 2		17		

(4) This parameter ensured by design and characterization.

AC Timing Specifications

The following specifications apply for $V_A = V_D = V_C = 3.3V$, $C_L = 10pF$, and $f_{INCLK} = 15MHz$ unless otherwise specified.

Boldface limits apply for $T_A = T_{MIN}$ to T_{MAX} ; all other limits $T_A = 25^\circ C$.⁽¹⁾

Parameter		Test Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
Input Clock Timing Specifications						
f _{INCLK}	Input Clock Frequency	INCLK = PIXCLK (Pixel Rate Clock)	0.66 1 1		15 (Mode 3) 22.5 (Mode 2) 22.5 (Mode 1)	MHz
		INCLK = ADCCLK (ADC Rate Clock)	2		45 (Mode 3) 45 (Mode 2) 22.5 (Mode 1)	MHz
T _{dc}	Input Clock Duty Cycle		40/60	50/50	60/40	%
Full Channel Latency Specifications						
t _{LAT3}	3 Channel Mode Pipeline Delay	PIXPHASE0		24		T _{ADC}
		PIXPHASE1		23 1/2		
		PIXPHASE2		23		
		PIXPHASE3		22 1/2		
t _{LAT2}	2 Channel Mode Pipeline Delay	PIXPHASE0		21		T _{ADC}
		PIXPHASE1		20 1/2		
		PIXPHASE2		20		
		PIXPHASE3		19 1/2		

(1) The analog inputs are protected as shown in Figure 4. Input voltage magnitudes beyond the supply rails will not damage the device, provided the current is limited per Note 4 under the Absolute Maximum Ratings Table. However, input errors will be generated if the input goes above V_A and below AGND.

(2) Test limits are ensured to TI's AOQL (Average Outgoing Quality Level).

(3) Typical figures are at $T_A = 25^\circ C$, and represent most likely parametric norms at the time of product characterization. The typical specifications are not ensured.

AC Timing Specifications (continued)

The following specifications apply for $V_A = V_D = V_C = 3.3V$, $C_L = 10pF$, and $f_{INCLK} = 15MHz$ unless otherwise specified.

Boldface limits apply for $T_A = T_{MIN}$ to T_{MAX} ; all other limits $T_A = 25^\circ C$.⁽¹⁾

Parameter		Test Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
t _{LAT1}	1 Channel Mode Pipeline Delay	PIXPHASE0		19		T _{ADC}
		PIXPHASE1		18 1/2		
		PIXPHASE2		18		
		PIXPHASE3		17 1/2		
SH_R Timing Specifications						
t _{SHR_S}	SH_R Setup Time			2		ns
t _{SHR_H}	SH_R Hold Time			2		ns
LVDS Output Timing Specifications						
TX _{pp0}	TXCLK to Pulse Position 0	LVDS Output	-0.46	0	0.46	ns
TX _{pp1}	TXCLK to Pulse Position 1	Specifications not tested in production. Min/Max ensured by design, characterization and statistical analysis.	2.71	3.17	3.63	ns
TX _{pp2}	TXCLK to Pulse Position 2		5.89	6.35	6.81	ns
TX _{pp3}	TXCLK to Pulse Position 3		9.06	9.52	9.98	ns
TX _{pp4}	TXCLK to Pulse Position 4		12.24	12.70	13.16	ns
TX _{pp5}	TXCLK to Pulse Position 5		15.41	15.87	16.33	ns
TX _{pp6}	TXCLK to Pulse Position 6		18.59	19.05	19.51	ns
CMOS Output Timing Specifications						
t _{CRDO}	CLKOUT Rising Edge to CMOS Output Data Transition	f _{INCLK} = 40MHz INCLK = ADCCLK (ADC Rate Clock)	2	6	9	ns
Serial Interface Timing Specifications						
f _{SCLK}	Input Clock Frequency	f _{SCLK} <= f _{INCLK} INCLK = PIXCLK (Pixel Rate Clock) Mode 3/2/1			15/22.5/22.5	MHz
		f _{SCLK} <= f _{INCLK} INCLK = ADCCLK (ADC Rate Clock) Mode 3/2/1			45/45/22.5	MHz
	SCLK Duty Cycle			50/50		ns
t _{IH}	Input Hold Time		1.5			ns
t _{IS}	Input Setup Time		2.5			ns
t _{SENSC}	SCLK Start Time After \overline{SEN} Low		1.5			ns
t _{SCSEN}	\overline{SEN} High after last SCLK Rising Edge		2.5			ns
t _{SENV}	\overline{SEN} Pulse Width	INCLK present INCLK stopped ⁽⁴⁾⁽⁵⁾	6 50			T _{INCLK} ns
t _{OD}	Output Delay Time			11	14	ns
t _{HZ}	Data Output to High Z				0.5	T _{SCLK}

(4) If the input INCLK is divided down to a lower internal clock rate via the PLL, the parameter t_{SENV} will be increased by the same factor.

(5) When the Spread Spectrum Clock Generation feature is enabled, t_{SENV} should be increased by 1.




Figure 4.

REVISION HISTORY

Changes from Original (April 2013) to Revision A

Page

- Changed layout of National Data Sheet to TI format [13](#)

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish	MSL Peak Temp (3)	Op Temp (°C)	Top-Side Markings (4)	Samples
LM98722CCMT/NOPB	ACTIVE	TSSOP	DGG	56	34	Green (RoHS & no Sb/Br)	CU SN	Level-2-260C-1 YEAR	0 to 70	LM98722CCMT	Samples
LM98722CCMTX/NOPB	ACTIVE	TSSOP	DGG	56	1000	Green (RoHS & no Sb/Br)	CU SN	Level-2-260C-1 YEAR	0 to 70	LM98722CCMT	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) Multiple Top-Side Markings will be inside parentheses. Only one Top-Side Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Top-Side Marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LM98722CCMTX/NOPB	TSSOP	DGG	56	1000	330.0	24.4	8.6	14.5	1.8	12.0	24.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LM98722CCMTX/NOPB	TSSOP	DGG	56	1000	367.0	367.0	45.0

DGG (R-PDSO-G**)

PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.
 B. This drawing is subject to change without notice.
 C. Body dimensions do not include mold protrusion not to exceed 0,15.
 D. Falls within JEDEC MO-153

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com