





NOTE:

1. MATERIAL:
HOUSING: PA46 , UL 94V-0, COLOR: NATURAL.
CONTACTS: BRASS.
2. FINISH:
CONTACTS: $3.05\mu\text{m}$ [120μ "] MIN. MATTE-TIN PLATING ALL OVER
 $1.27\mu\text{m}$ [50μ "]. NICKEL UNDERPLATED ALL OVER.
3. WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC.
109-202, CONDITION B.
4. WEIGHT: SEE TABLE



TE LOGO & DATE CODE

WEIGHT:

4.55g	4.52g	3.95g	20P
5.16g	5.13g	5.10g	24P
W/POST	W/R OR L POST	W/O POST	ITEM

47.20	37.8	41.60	43.1	20P
55.60	46.2	50.00	51.5	24P
DIM.D	DIM.C	DIM.B	DIM.A	POS.NO

OBSOLETE	TRAY		W/	W/O	3—	—4	20P
			W/O	W/	3—	—3	
			W/O	W/O	3—	—2	
			W/	W/	3—1775034—1		
	TRAY		W/	W/O	2—	—4	
			W/O	W/	2—	—3	
			W/O	W/O	2—	—2	
			W/	W/	2—1775034—1		
OBSOLETE	TRAY	#20	W/O	W/O	1—	—5	24P
			W/	W/O	1—	—4	
			W/O	W/	1—	—3	
			W/O	W/O	1—	—2	
			W/	W/	1—	—1	
			#20	W/O	W/O		
TRAY		W/	W/O		—4		
		W/O	W/		—3		
		W/O	W/O		—2		
		W/	W/	1775034—1			
		PKG.	LACK POS #	POST L	POST R	PART NUMBER	POS.NO.

CUSTOMER

CUSTOMER



TE Connectivity

ATX POWER CONN.,V/T,
PLUG,4.2 PITCH,DIP TYPE

RESTRICTED TO

C-1775034


REV ☐ 1

CUSTOMER DRAWING


REV ☐ 1

1470-19 (3/11)


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	-	SEE SHEET 1.	-	-	-	




RECOMMENDED PCB LAYOUT
TOLERANCE: ± 0.05
FOR P/N: X-1775034-1



RECOMMENDED PCB LAYOUT
TOLERANCE: ± 0.05
FOR P/N: X-1775034-3



RECOMMENDED PCB LAYOUT
TOLERANCE: ± 0.05
FOR P/N: X-1775034-2



RECOMMENDED PCB LAYOUT
TOLERANCE: ± 0.05
FOR P/N: X-1775034-4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$ -

1 PLC $\pm$ -

2 PLC $\pm$ -

3 PLC $\pm$ -

4 PLC $\pm$ -

ANGLES $\pm$ -

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

ATX POWER CONN.,V/T,
PLUG,4.2 PITCH,DIP TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1775034

SCALE

SHEET


REV

D


C

B


A







TRAY COVER





ATX CONNECTOR





TRAY



10 TRAY



BOX



NOTES:
1. TRAY : PVC, SIZE: 330mm(L)X 265mm(W)X 22mm(H).
2. BOX : CORRUGATED, SIZE: 350mm(L)X 279mm(W)X 195mm(H).
3. QUANTITY: SEE TABLE.

5.68	4.08	80	10	800	24	W/O	W/O
5.55	3.95	100	10	1000	20		
5.70	4.10	80	10	800	24		
6.12	4.52	100	10	1000	20	W/	W/O
5.70	4.10	80	10	800	24		
6.12	4.52	100	10	1000	20	W/O	W/
5.73	4.13	80	10	800	24		
6.15	4.55	100	10	1000	20	W/	W/
GROSS WEIGHT	NET WEIGHT	PCS /TRAY	TRAYS /BOX	PCS /BOX	POS.		
						LEFT BOARD	RIGHT LOCK

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

ATX POWER CONN.,V/T, PLUG,4.2 PITCH,DIP TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1775034

SCALE

SHEET 3 OF 3

REV E1