




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID .020 SQ.(4) [.50]

PART IS SYMMETRICAL. PCB AND MARKING ORIENTATION MAY BE ROTATED 180°.



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	10.05 ohms ±10%
D.C. RESISTANCE	3-4 @20°C	10.05 ohms ±10%
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	45mH typ., 36mH min.
INDUCTANCE	3-4 10kHz, 100mVAC, Ls	45mH typ., 36mH min.
SATURATION CURRENT	20% rolloff from initial	200mA
LEAKAGE INDUCTANCE	tie(2+3), 100kHz, 100mVAC, Ls	4.0mH min.
SELF RESONANT FREQUENCY		300kHz min.
DIELECTRIC	1-4 1875VAC, 1 second	1500VAC, 1 minute

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

6C RATED CURRENT: 180mA causes 40°C temp rise from ambient.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 Footprint: ±.001	DRAWING TITLE	PART NO.
6D	9/12	Method: Tray PKG-0888			TRANSFORMER	750311650
6C	12/10	www.we-online.com/midcom				
6A	11/10	SEE REVISION SHEET FOR				
		REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750311650	SPECIFICATION SHEET 1 OF 1