

PRODUCT NUMBER
10082201-YXX-XXLF

PLATING

1 = 0.76µm GOLD OR
0.76µm GXT (PdNi WITH
GOLD FLASH)
ON CONTACT AREA
2µm MATTE TIN ON TAIL

4 = 2µm MATTE TIN
ON CONTACT AREA
AND TAIL

8 = 0.38µm GOLD
ON CONTACT AREA
2µm MATTE TIN
ON TAIL

RoHS COMPATIBLE, NOTE 7.

TOTAL NB OF POSITIONS
02 TO 36

PACKAGING, NOTE 3.

PIN STYLE	MATING SIDE	DIM "B"
01	5.84	2.50
02	6.75	2.50
03	5.84	3.00
04	6.75	3.00
05	11.60	3.00
06	9.50	4.30
07	8.07	3.00

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE
THERMOPLASTIC. UL94V-0 COLOR: BLACK

2. PIN MATERIAL : PHOSPHOR BRONZE

3. PACKAGING.

- = POLY BAGS

A = TAPE & REEL WITH CAP, SEE TA840
FOR PRODUCT AVAILABILITY.

PICK-UP CAP 90° ROTATED FOR ODD NB OF CONTACTS

K = TAPE & REEL WITHOUT PICK UP CAP

4. 9N MIN RETENTION IN EITHER DIRECTION

5. TO DETERMINE DIMENSIONS :

N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm

6. UNDERPLATING : 1.27µm Ni MIN

7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.



b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDES
IN A CONVECTION, INFRA-RED OR VAPOR
PHASE REFLOW OVEN.



c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004



RECOMMENDED HOLE PATTERN



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family BERGSTIK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
A	F08-0104	LMU	08.01.15		angles	.X ±0.3	UNSHR.HEADER
B	F09-0072	JCO	09.07.23		linear	.XX ±0.15	RA SR PIN IN PASTE
C	F12-0032	LMU	12.05.04			.XXX ±0.05	
D	B-18990	LMU	14.10.06	dr	L.MULIN	08.01.15	dwg no
E	B-20031	AMA	15.01.20	enr	J.COMPAGNON	08.01.15	sheet 1 of 1 size
				chr			10082201 A3
				appd	J.M.C	08.01.15	type CUSTOMER Drawing
sheet	revision						
index	sheet						