



### FEATURES:

- Shield extends to within 1.5" of the probe tip
- BNC center contact is connected to the .080" diameter probe tip

### MATERIALS:

Connector: 1<sup>st</sup> end: Pin Tip, Brass

Finish: Nickel plated

Insulation: Nylon molded to probe tip and BNC

Marking: POMONA ELECTRONICS MODEL 4856 500V Max.

Connector: 2<sup>nd</sup> end: BNC female

Finish: Body and fittings, tarnish resistant

### RATINGS:

Operating Temperature: +80°C (+176°F) Max.

Operating Voltage: 500 VRMS Max.

### ORDERING INFORMATION: Model 4856-\*

\*Standard Colors: -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4856-2