


DASH NO.	DESCRIPTION	MADE FROM
----------	-------------	-----------



STAMP: KINGS KH-39-12

STAMP: PAT. 3195098

$\frac{10}{4}$ - 20 UNEF-2A THREAD

NOTES:

1. FOR USE WITH RG-9, 9A, 9B & 214/U CABLE.
2. FOR CABLING INSTRUCTION SEE CP-208A.
3. FOR CABLE TRIMMING USE KTJ-23 & KTD-82.
4. FOR FORMING USE CRIMP DIE SIZE 04.

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS $\pm .010$
3 PLACE DECIMALS $\pm .004$
T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.
2. REMOVE ALL BURRS. BREAK SHARP EDGES .005 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.

9	1	BODY	
8	1	INSULATOR	
7	1	HN CONTACT ASS'Y F	60D-6-M07
6	1	RETAINER	
5	1	K-GRIP	S-89-35-M07
4	1	GASKET	571-3-M99
3	1	GLAND	S-89-35-M07
2	1	K-GRIP SLEEVE	S-89-24-2-M07
1	1	CLAMP NUT	S-89-35-M07
ITEM	REQ'D	DESCRIPTION	PART NO.

REVISIONS

ISSUE	CHANGES
9	CN 16734 E GA 1 FEB 77

KH-39-12

USED ON:

REF:

FINISH

SPEC.

MATL

SPEC.

HN JACK

DRAWN BG. DATE 21 FEB 73

APPR BT. DATE 22 FEB 73

KINGS ELECTRONICS
40 HARBLEDALE ROAD
TUCKAHOE, N. Y. 10707

KH-39-12