





REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD



P.C.B. Layout (TOP VIEW) t=1

NOTES:

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : NYLON FR52(HIGH TEMPERATURE)
2. CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
3. PLATING : 1: CONTACT AREA- SELECTIVE GOLD PLATING.
2: TAILS- 150u" TIN-LEAD MIN OVER 50u" NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
2. OPERATION: 0°C TO 70°C.
3. REFLOW SOLDERING TEMPERTUR: 255°C TO 265°C 5-10SECOND.

MATES WITH MODULAR PLUG CONFORMING TO

FCC PART 68, SUBPART F.

ROHS PART NUMBER: E666X-1X026X-L

2C-2 1-3u" 2-6u"
4C-4 3-15u" 4-30u"
6C-6 1-TIN 5-50u"
2-NICKEL

DETAIL 3:1

DETACHED LISTS	MM (INCH)		DFTO SAMMY	DATE 04/11/05	FULL RISE ELECTRONIC CO., LTD			
	TOLERANCES EXCEPT AS NOTED		CHKDQIANPU	DATE2005/4/11				
			MFO	DATE	TITLE			
			APPVILUSHENG	DATE2005/4/12				
			MATERIAL :		RJ11 SIDE ENTRY PCB JACK (SMD)			
			QT*Y :					
	ANGLES ±		FINISH :		DRAWING NO. GE663004-LA		SIZE	REV
			SCALE :		/PART NO. SEE NOTE		A3	0
	THIRD ANGLE PROJECTION				DO NOT SCALE DRAWING		SHEET X	OF Y