

Common Mode Filters(SMD)

For High-speed Differential Signal Line

Conformity to RoHS Directive

TCM Series TCM1210G Type

FEATURES

- The TCM1210G(L1.25×W1.00×T0.60mm) is compact sized common mode filter.
- By providing wide bandwidth (cutoff frequency: 3GHz) for differential mode, this product has almost no effect for high-speed differential signals and can suppress the radiated emission.
- This product contains no lead and supports lead-free soldering.

APPLICATIONS

- High speed interface(LVDS, IEEE1394 and USB2.0) in electronics devices.
- PDP/LCD/DLP/PJ TVs, DVD players, notebook PCs, DVC, DSC, amusement machines, portable audio, digital cellular phones, etc.


TEMPERATURE RANGE

Operating	-25 to +85°C
-----------	--------------

PACKAGING STYLE AND QUANTITIES

Packaging style	Quantity
Taping	4000 pieces/reel

SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM/RECOMMENDED PC BOARD PATTERN



ELECTRICAL CHARACTERISTICS

Part No.	Common mode impedance (Ω) [100MHz]	DC resistance (Ω)[1 line]	Rated current Idc(A)max.	Rated voltage Edc(V)max.	Insulation resistance (M Ω)min.
TCM1210G-350-2P	35±30%	0.70±30%	0.10	10	10
TCM1210G-650-2P	65±20%	0.85±30%	0.10	10	10
TCM1210G-900-2P	90±20%	1.20±30%	0.10	10	10
TCM1210G-201-2P	200±20%	3.00±30%	0.05	10	10
TCM1210G-301-2P	300±20%	3.50±30%	0.05	10	10

- Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.

- All specifications are subject to change without notice.

TYPICAL ELECTRICAL CHARACTERISTICS
IMPEDANCE vs. FREQUENCY CHARACTERISTICS

