


PRODUCT NUMBER
75915-YXXXLF


RoHS COMPATIBLE, SEE NOTE 6
OPTIONAL LETTER.

G: HIGH TEMPERATURE BLACK PRODUCT.
H: HIGH TEMPERATURE GREY PRODUCT.
NUMBER OF POSITIONS: 02 TO 50.

PLATING CODE
3 = 0.76µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.
4 = 2µm MIN MATTE TIN FULL PLATED
8 = 0.38µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.
1.27µm Ni MIN UNDERPLATING



(N x 2.54) - 0.08



2.5 REF

8.5 REF

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54

0.6

2.54

0.2

2.54


0.6

2.54

0.2

A

A





B

B

C

C

mat'l. code SEE SHEET 1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX																							
ltr		ecn no		dr		date		tolerances unless otherwise specified						title																			
A		F04-0347		DLE		04.09.23		angles linear		±0.3		mm 		BtB RECEPT. VERT SR TMT																			
B		F05-0230		DLE		05.08.08																											
C		F06-0204		DLE		06.06.20				±2'																							
D		F07-0109		DLE		07.01.16		dr		D.LEGRAND		04.09.23				dwg no														sheet 2 of -		size	
								enr		P.NIZZI		04.09.23				75915														A4			
								chr		D.LEGRAND		04.09.23																					
								appd		P.NIZZI		04.09.23				type														CUSTOMER		Drawing	
sheet index		revision																															
		sheet																															

D

D