



Micro Commercial Components



Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

DFLZ6V2 THRU DFLZ39

Features

- Halogen free available upon request by adding suffix "-HF"
- 1.0W Power Dissipation
- High Surge Capability
- Ideally Suited for Automatic Assembly
- Standard V_z Tolerance is $\pm 5\%$
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Lead Free Finish/Rohs Compliant (Note1) ("P" Suffix designates Compliant. See ordering information)

Maximum Ratings


- Storage Temperature Range(T_{STG}): -55°C to $+150^{\circ}\text{C}$
- Operating Temperature Range(T_i): -55°C to $+150^{\circ}\text{C}$

	Symbol	Value	Units
Zener Current	I_{ZM}	P_d/V_z	mA
Power Dissipation @ $T_A=50^{\circ}\text{C}$	P_{tot}	1000	mW
Forward Voltage @ $I_F = 200\text{mA}$	V_F	1.2	V
Junction to Soldering Point	R_{thJS}	9	$^{\circ}\text{C/W}$
Thermal resistance	R_{thJA}	110	$^{\circ}\text{C/W}$

Note :1.High Temperature Solder Exemptions Applied,See EU Directive Annex 7.


1 Watt Zener Diode 6.2V - 39V Volts

SOD-123FL



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.140	.152	3.55	3.85	
B	.100	.122	2.55	3.10	
C	.055	.075	1.40	1.90	
D	.035	.053	0.90	1.35	
E	.020	.041	0.50	1.05	
G	.010	----	0.25	----	
H	----	.010	----	.25	

SUGGESTED SOLDER PAD LAYOUT



Electrical Characteristics @ 25°C Unless Otherwise Specified

Part Number	Zener Voltage V_Z Voltages				Maximum Zener Impedance $Z_{ZT}@I_{ZT}$		Reverse Current $I_R(\text{Max}) @ V_R$		Typical Temperature Coefficient $@I_{ZTC}(\%/^{\circ}\text{C})$		Marking
	Nom	Min	Max	$I_{ZT}(\text{mA})$	Typ (Ω)	Max (Ω)	$I_R(\mu\text{A})$	$V_R(\text{V})$	Min	Max	
DFLZ6V2	6.20	5.80	6.40	100	1.0	3.0	5	2.0	-0.01	0.06	6V2
DFLZ6V8	6.80	6.40	7.20	100	1.0	3.0	5	3.0	0	0.07	6V8
DFLZ7V5	7.50	7.00	7.90	100	1.0	2.0	5	3.0	0	0.07	7V5
DFLZ8V2	8.20	7.70	8.70	100	1.0	2.0	5	3.0	0.03	0.08	8V2
DFLZ9V1	9.10	8.50	9.60	50	1.0	4.0	5	5.0	0.03	0.08	9V1
DFLZ10	10.00	9.40	10.60	50	1.0	4.0	5	7.5	0.05	0.09	Z10
DFLZ11	11.00	10.40	11.60	50	1.0	7.0	4	8.2	0.05	0.10	Z11
DFLZ12	12.00	11.40	12.70	50	1.0	7.0	3	9.1	0.05	0.10	Z12
DFLZ13	13.00	12.40	14.10	50	1.0	10.0	2	10.0	0.05	0.10	Z13
DFLZ15	15.00	13.80	15.60	50	1.0	10.0	1	11.0	0.05	0.10	Z15
DFLZ16	16.00	15.30	17.10	25	1.0	15.0	1	12.0	0.06	0.11	Z16
DFLZ18	18.00	16.80	19.10	25	2.0	15.0	1	13.0	0.06	0.11	Z18
DFLZ20	20.00	18.80	21.20	25	3.0	15.0	1	15.0	0.06	0.11	Z20
DFLZ22	22.00	20.80	23.30	25	3.0	15.0	1	16.0	0.06	0.11	Z22
DFLZ24	24.00	22.80	25.60	25	2.0	15.0	1	18.0	0.06	0.11	Z24
DFLZ27	27.00	25.10	28.90	25	3.0	15.0	1	20.0	0.06	0.11	Z27
DFLZ30	30.00	28.00	32.00	25	8.0	15.0	1	22.0	0.06	0.11	Z30
DFLZ33	33.00	31.00	35.00	25	5.0	15.0	1	24.0	0.06	0.11	Z33
DFLZ36	36.00	34.00	38.00	10	5.0	40.0	1	27.0	0.06	0.11	Z36
DFLZ39	39.00	37.00	41.00	10	5.0	40.0	1	30.0	0.06	0.11	Z39

Notes: 1. Short duration pulse test used to minimize self-heating effect.






Fig. 3 Typical Total Capacitance vs. Nominal Zener Voltage

Ordering Information :

Device	Packing
Part Number-TP	Tape&Reel: 2.5Kpcs/Reel

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.