

Type DMM Polyester Film Capacitors

Metallized



DC Applications

Self Healing

Type DMM radial-leaded, metallized polyester capacitors have non-inductive windings and multi-layered epoxy resin enhancing performance characteristics and humidity resistance. Self healing characteristics prevent permanent shorting due to high-voltage transients. When long life and performance stability are critical **Type DMM** is the ideal solution.

Specifications

Voltage Range: 100-630 Vdc

Capacitance Range: .01-10 μ F

Capacitance Tolerance: $\pm 10\%$ (K) standard
 $\pm 5\%$ (J) optional

Operating Temperature Range: -55 °C to 125 °C*

*Full-rated voltage at 85 °C—Derate linearly to 50%-rated voltage at 125 °C


Dielectric Strength: 150% (1 minute)

Dissipation Factor: 1% Max. (25 °C, 1 kHz)

Insulation Resistance: 5,000 M Ω x μ F
10,000 M Ω Min.

Life Test: 1,000 Hours at 85 °C at
125% Rated Voltage

NOTE: Other cap:
sizes and performan
are available. Conta



Complies with the EU Directive 2002/95/EC requirement restricting the use of Lead (Pb), Mercury (Hg), Cadmium (Cd), Hexavalent chromium (Cr(VI)), PolyBrominated Biphenyls (PBB) and PolyBrominated Diphenyl Ethers (PBDE).

Pulse Capability					
Rated Volts	Body Length				
	0.55	0.71	0.94	1.024-1.220	1.38
	dV/dt—volts per microsecond, maximum				
100	20	12	8	6	
250	28	17	12	8	7
400	46	28	15	14	12
630	72	43	28	21	17

Ratings

Cap. (μ F)	Catalog Part Number	T Max. Inches (mm)	H Max. Inches (mm)	L Max. Inches (mm)	S $\pm .06$ (± 1.5) Inches (mm)	d Inches (mm)
100 Vdc						
0.15	DMM1P15K-F	0.236 (6.0)	0.394 (10.0)	0.551 (14.0)	0.394 (10.0)	0.024 (0.6)
0.22	DMM1P22K-F	0.236 (6.0)	0.414 (10.5)	0.551 (14.0)	0.394 (10.0)	0.024 (0.6)
0.33	DMM1P33K-F	0.236 (6.0)	0.414 (10.5)	0.709 (18.0)	0.591 (15.0)	0.024 (0.6)
0.47	DMM1P47K-F	0.236 (6.0)	0.473 (12.0)	0.709 (18.0)	0.591 (15.0)	0.024 (0.6)
0.68	DMM1P68K-F	0.276 (7.0)	0.551 (14.0)	0.709 (18.0)	0.591 (15.0)	0.024 (0.6)
1.00	DMM1W1K-F	0.354 (9.0)	0.591 (15.0)	0.709 (18.0)	0.591 (15.0)	0.032 (0.8)
1.50	DMM1W1P5K-F	0.354 (9.0)	0.670 (17.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
2.20	DMM1W2P2K-F	0.433 (11.0)	0.788 (20.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
3.30	DMM1W3P3K-F	0.453 (11.5)	0.788 (20.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
4.70	DMM1W4P7K-F	0.512 (13.0)	0.906 (23.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
6.80	DMM1W6P8K-F	0.630 (16.0)	1.024 (26.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
10.00	DMM1W10K-F	0.709 (18.0)	1.221 (31.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
250 Vdc						
0.068	DMM2S68K-F	0.236 (6.0)	0.394 (10.0)	0.551 (14.0)	0.390 (10.0)	0.024 (0.6)
0.10	DMM2P1K-F	0.276 (7.0)	0.394 (10.0)	0.551 (14.0)	0.390 (10.0)	0.024 (0.6)
0.15	DMM2P15K-F	0.276 (7.0)	0.433 (11.0)	0.709 (18.0)	0.590 (15.0)	0.024 (0.6)
0.22	DMM2P22K-F	0.276 (7.0)	0.473 (12.0)	0.709 (18.0)	0.590 (15.0)	0.024 (0.6)
0.33	DMM2P33K-F	0.276 (7.0)	0.512 (13.0)	0.709 (18.0)	0.590 (15.0)	0.024 (0.6)
0.47	DMM2P47K-F	0.315 (8.0)	0.591 (15.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
0.68	DMM2P68K-F	0.354 (9.0)	0.610 (15.5)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)

Type DMM Polyester Film Capacitors

RoHS Compliant

Cap. (μ F)	Catalog Part Number	T Max. Inches (mm)	H Max. Inches (mm)	L Max. Inches (mm)	S $\pm$.06 ($\pm$ 1.5) Inches (mm)	d Inches (mm)
250 Vdc						
1.00	DMM2W1K-F	0.394 (10.0)	0.670 (17.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
1.50	DMM2W1P5K-F	0.394 (10.0)	0.768 (19.5)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
2.20	DMM2W2P2K-F	0.512 (13.0)	0.866 (22.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
3.30	DMM2W3P3K-F	0.630 (16.0)	1.024 (26.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
4.70	DMM2W4P7K-F	0.630 (16.0)	1.024 (26.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
400 Vdc						
0.033	DMM4S33K-F	0.236 (6.0)	0.414 (10.5)	0.551 (14.0)	0.394 (10.0)	0.024 (0.6)
0.047	DMM4S47K-F	0.315 (8.0)	0.433 (11.0)	0.551 (14.0)	0.394 (10.0)	0.024 (0.6)
0.068	DMM4S68K-F	0.236 (6.0)	0.512 (13.0)	0.709 (18.0)	0.591 (15.0)	0.024 (0.6)
0.10	DMM4P1K-F	0.256 (6.5)	0.512 (13.0)	0.709 (18.0)	0.591 (15.0)	0.024 (0.6)
0.15	DMM4P15K-F	0.276 (7.0)	0.551 (14.0)	0.709 (18.0)	0.591 (15.0)	0.032 (0.8)
0.22	DMM4P22K-F	0.354 (9.0)	0.630 (16.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
0.33	DMM4P33K-F	0.354 (9.0)	0.630 (16.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
0.47	DMM4P47K-F	0.394 (10.0)	0.709 (18.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
0.68	DMM4P68K-F	0.414 (10.5)	0.709 (18.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
1.00	DMM4W1K-F	0.473 (12.0)	0.866 (22.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
630 Vdc						
0.01	DMM6S1K-F	0.236 (6.0)	0.394 (10.0)	0.551 (14.0)	0.394 (10.0)	0.024 (0.6)
0.015	DMM6S15K-F	0.256 (6.5)	0.453 (11.5)	0.551 (14.0)	0.394 (10.0)	0.024 (0.6)
0.022	DMM6S22K-F	0.276 (7.0)	0.492 (12.5)	0.551 (14.0)	0.394 (10.0)	0.024 (0.6)
0.033	DMM6S33K-F	0.315 (8.0)	0.532 (13.5)	0.709 (18.0)	0.591 (15.0)	0.024 (0.6)
0.047	DMM6S47K-F	0.295 (7.5)	0.492 (12.5)	0.709 (18.0)	0.591 (15.0)	0.024 (0.6)
0.068	DMM6S68K-F	0.335 (8.5)	0.571 (14.5)	0.709 (18.0)	0.591 (15.0)	0.032 (0.8)
0.10	DMM6P1K-F	0.374 (9.5)	0.630 (16.0)	0.709 (18.0)	0.591 (15.0)	0.032 (0.8)
0.15	DMM6P15K-F	0.394 (10.0)	0.670 (17.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
0.22	DMM6P22K-F	0.433 (11.0)	0.788 (20.0)	1.024 (26.0)	0.886 (22.5)	0.032 (0.8)
0.33	DMM6P33K-F	0.512 (13.0)	0.866 (22.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
0.47	DMM6P47K-F	0.512 (13.0)	0.866 (22.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
0.68	DMM6P68K-F	0.591 (15.0)	1.024 (26.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)
1.00	DMM6W1K-F	0.689 (17.5)	1.182 (30.0)	1.221 (31.0)	1.083 (27.5)	0.032 (0.8)

Type DMM Polyester Film Capacitors

Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.