

**M·C·C·**

Micro Commercial Components




Micro Commercial Components  
20736 Marilla Street Chatsworth  
CA 91311  
Phone: (818) 701-4933  
Fax: (818) 701-4939

**SI3139K**

## Features

- Lead Free Product is Acquired
- Halogen free available upon request by adding suffix "-HF"
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Operated at Low Logic Level Gate Drive
- P-Channel Switch with Low  $R_{DS(on)}$
- Surface Mount Package
- Marking : KD



### Absolute maximum ratings @ 25°C


Symbol	Parameter	Value	Unit
$V_{DS}$	Drain-source Voltage	-20	V
$V_{GS}$	Gate-source Voltage	$\pm 6$	V
$I_D$	Continuous Drain Current	-0.66	A
$I_{DM}$	Pulsed Drain Current	-1.2	A
$P_D$	Total Power Dissipation	150	mW
$T_J$	Operating Junction Temperature	-55 to +150	°C
$T_{STG}$	Storage Temperature	-55 to +150	°C
$T_L$	Lead Temperature for Soldering Purposes	260	°C
$R_{thJA}$	Thermal Resistance from Junction to Ambient	833	°C/W

### Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Typ	Max	Units
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage ( $V_{GS}=0$ Vdc, $I_D=-250\mu$ Adc)	-20	---	---	Vdc
$V_{GS(th)}$	Gate-Threshold Voltage ( $V_{DS}=V_{GS}$ , $I_D=-250\mu$ Adc)	-0.35	---	-0.8	Vdc
$I_{GSS}$	Gate-body Leakage ( $V_{DS}=0$ Vdc, $V_{GS}=\pm 12$ Vdc)	---	---	20	$\mu$ A
$I_{DSs}$	Zero Gate Voltage Drain Current ( $V_{DS}=-20$ Vdc, $V_{GS}=0$ Vdc)	---	---	-1	$\mu$ Adc
$V_{SD}$	Diode Forward Voltage ( $I_S=0.5$ A, $V_{GS}=0$ V)	---	---	-1.2	Vdc
$r_{DS(on)}$	Drain-Source On-Resistance ( $V_{GS}=-4.5$ Vdc, $I_D=-1$ Adc) ( $V_{GS}=-2.5$ Vdc, $I_D=-0.80$ Adc) ( $V_{GS}=-1.8$ Vdc, $I_D=0.5$ Adc)	---	---	0.52 0.70 0.95	$\Omega$
$g_{FS}$	Forward transconductance ( $V_{DS}=-10$ Vdc, $I_D=0.54$ Adc)	---	1.2	---	S
$C_{iss}$	Input Capacitance	---	113	170	pF
$C_{oss}$	Output Capacitance	---	15	25	
$C_{rss}$	Reverse Transfer capacitance	---	9	15	
$t_{d(on)}$	Turn-on Time	$V_{GS}=-4.5$ V, $V_{DS}=-10$ V, $I_D=-200$ mA, $R_{GEN}=10\Omega$	9.0	---	ns
$t_{d(off)}$	Turn-off Time		32.7	---	
$t_r$	Rise Time		5.8	---	
$t_f$	Fall Time		20.3	---	

### P-Channel MOSFET

**SOT-723**



#### DIMENSIONS

DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.045	.049	1.15	1.25	
B	.045	.049	1.15	1.25	
C	.030	.033	0.75	0.85	
D	.011	.015	0.27	0.37	
E	0.031TYP.		0.80TYP.		
F	.007	.011	0.17	0.27	
G	.017	.020	0.43	0.50	
H	.003	.006	0.08	0.15	
J	.000	.002	0.00	0.05	

<sup>TM</sup>

Micro Commercial Components

## Ordering Information :

Device	Packing
Part Number-TP	Tape&Reel: 8Kpcs/Reel

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

[www.mccsemi.com](http://www.mccsemi.com)