







mat'l. code —				surface ISO 1302 ✓				tolerance ISO 406 ISO 1101				projection 				product family RIBCAGE											
ltr ecn no dr date				tolerances unless otherwise specified												 INCH/MM scale 3:1				title RIBCAGE III SMT VERT. HEADER ASS'Y							
AA M08-0245 MHT 8/27/08				angles				linear				.XX±.01/0.3															
AB M09-0058 MHT 4/04/09												.XXX±.005/0.13				dwg no 95781 sheet 1 of 8 size A3											
AC M09-0087 MHT 06/10/09				±2'								.XXXX±.0020/0.05'															
AD N10-0174 YO 6/17/10				dr				M. CORNMAN				6/07/95				type Product Customer Drawing											
AE ELX-N-004143 YO 06/20/11				engr				D. WHITING				6/07/95															
AF ELX-N-004656 YO 07/27/11				chr				D. WHITING				6/07/95															
AG ELX-N-009746 YO 1/20/12				appd				D. WHITING				6/07/95															
sheet revision				AG AG AG AG AG AG AG AG																							
index sheet				1 2 3 4 5 6 7 8																							

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28






SECTION X-X
ROTATED 90° CW







SECTION Y-Y

mat'l. code —				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		scale 3:1	title		
AG					angles	linear		RIBCAGE III SMT VERT. HEADER ASS'Y		
					±2°	.XX±.01/0.3 .XXX±.005/0.13 .XXXX±.0020/0.051		dwg no		
					dr	M. CORNMAN	6/07/95	sheet 2 of 8		size
					enr	D. WHITING	6/07/95	95781		A3
					chr	D. WHITING	6/07/95	type		
					appd	D. WHITING	6/07/95	Product Customer Drawing		
sheet index	revision sheet									



LOCATOR/HOLDDOWN VARIATIONS



$\phi .0520$ [1.321]
 $\phi .004/0.10$ (M) A (S) B (S) (ALL PEG CONFIGURATIONS)





STYLE 5





$.0470^{+.0005}_{-.0010}$ [1.194 $^{+0.013}_{-0.025}$]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]
 $.0470^{+.0005}_{-.0010}$ [1.194 $^{+0.013}_{-0.025}$]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]

STYLE 6
 SEE NOTE 9



$.0520^{+.0005}_{-.0010}$ [1.321 $^{+0.013}_{-0.025}$]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]
 $.0520^{+.0005}_{-.0010}$ [1.321 $^{+0.013}_{-0.025}$]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]

STYLE 7




$.0065 \pm .001$ [0.165 ± 0.025]
 $\phi .0400$ [1.02]
 $.052 \pm .001$ [1.32 ± 0.025]
 R.002 [0.05] MAX

$.008$ [0.20] X 45°
 $.0520^{+.0005}_{-.0010}$ [1.321 $^{+0.013}_{-0.025}$]
 $.0030$ [0.076]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]
 $.008 \pm .003$ [0.20 ± 0.08]
 $\phi .034 \pm .001$ [0.86 ± 0.03]


mat'l. code				surface	tolerance	projection	product family
-				ISO 1302 ✓	ISO 406 ISO 1101		RIBCAGE
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM	title
AG					angles linear	scale 3:1	RIBCAGE III SMT VERT. HEADER ASS'Y
					$\pm 2^\circ$		
					dr M. CORNMAN 6/07/95		dwg no sheet 3 of 8 size
					enr D. WHITING 6/07/95		95781 A3
					chr D. WHITING 6/07/95		
					appd D. WHITING 6/07/95		type Product Customer Drawing
sheet index	revision sheet						

RECOMMENDED PCB MOUNTING PAD PATTERN


STYLE 1




STYLE 5




STYLE 4




STYLE 2




STYLE 7



STYLE 6



STYLE 3



mat'l. code —					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE						
ltr	ecn	no	dr	date	tolerances unless otherwise specified							title					
AG					angles		linear		.XX±.01/0.3 .XXX±.005/0.13 ±2' .XXX±.0020/0.051		INCH/MM		RIBCAGE III SMT VERT. HEADER ASS'Y				
											scale 3:1						
					dr	M. CORNMAN		6/07/95				dwg no		sheet 4 of 8		size	
					enrg	D. WHITING		6/07/95				95781				A3	
					chr	D. WHITING		6/07/95									
					appd	D. WHITING		6/07/95									
sheet index		revision sheet															

FCI

FCIconnect.com

Copyright FCI

1

2

3

4

5

6

PRODUCT
NUMBER
NOTE 1,4A & 4B

DIM P
HEIGHT ABOVE
BOARD (REF.)

HOLDDOWN
STYLE

72428-1XX

73546-1XX

73547-1XX

73548-1XX

84700-1XX

84701-1XX

84734-1XX

87401-1XX

87409-1XX

87849-1XX

88566-1XX

90098-1XX

90863-1XX

91036-1XX

91423-1XX

91855-1XX

92099-1XX

92412-1XX

93206-1XX

93221-1XX

93289-1XX

.244/6.20

.364/9.25

.364/9.25

.364/9.25

.226/5.74

.298/7.57

.364/9.25

.226/5.74

.226/5.74

.226/5.74

.260/6.60

.298/7.57

.226/5.74

.364/9.25

.226/5.74

.226/5.74

.226/5.74

.298/7.57

.298/7.57

.298/7.57

1

1

2

4

7

7

7

6

2

1

2

1

5

2

5

4

4

3

1

5

OBSOLETE

OBSOLETE

OBSOLETE

SEE NOTE 10

* OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

TABLE A

CUSTOMER SPECIAL

mat'l. code
—

surface
ISO 1302 ✓

tolerance
ISO 406
ISO 1101

projection
INCH/MM

product family
RIBCAGE

litr
AG

ecn no

dr

date

tolerances unless otherwise specified

angles

linear

.XX±.01/0.3

.XXX±.005/0.13

.XXXX±.0020/0.051

scale 3:1

title
RIBCAGE III SMT
VERT. HEADER ASS'Y

dr

M. CORNMAN

6/07/95

enrg

D. WHITING

6/07/95

chr

D. WHITING

6/07/95

appd

D. WHITING

6/07/95

FCI

dwg no

sheet 5 of 8

size
A3

type

Product Customer Drawing


sheet index

revision sheet

41

STATUS: Released

Printed: Feb 17, 2012



Copyright FCI

FCIconnect.com

PRODUCT NUMBER NOTE 11,4C	QTY. REEL	TAPE WIDTH PITCH MM	CONNECTOR ORIENTATION IN TAPE POCKET
87409-135TR	500	72/12	VIEW 1
87409-140TR	↑	72/12	↑
87409-145TR		72/12	
87409-150TR		88/12	
87849-105TR		24/12	
87849-110TR		24/12	
87849-115TR		44/12	
87849-120TR		44/12	
87849-125TR		56/12	
87849-130TR		56/12	
87849-135TR		72/12	
87849-140TR		72/12	
87849-145TR		72/12	
87849-150TR		88/12	
88566-110TR		24/12	
88566-115TR	↓	44/12	
88566-130TR	500	56/12	
90098-105TR	400	24/12	
90098-110TR	400	32/12	
90098-115TR	500	44/12	
90098-120TR	500	44/12	
90098-125TR	400	56/12	
90098-130TR	500	56/12	
90098-135TR	↑	72/12	
90098-140TR	↓	72/12	
90098-145TR		72/12	
90098-150TR		88/12	
90863-110	↓	24/12	↓
90863-115	500	44/12	VIEW 1

TABLE C

mat'l. code		surface		tolerance		projection		product family	
-		ISO 1302 ✓		ISO 406 ISO 1101				RIBCAGE	
ltr	ecn	no	dr	date		tolerances unless otherwise specified		title	
AG						angles linear		INCH/MM	
						.XX±.01/0.3		RIBCAGE III SMT	
						.XXX±.005/0.13		VERT. HEADER ASS'Y	
						±2'		.XXXX±.0020/0.051	
						dr		scale 3:1	
						M. CORNMAN		FCI	
						6/07/95		dwg no	
						enrg		sheet 7 of 8	
						D. WHITING		size	
						6/07/95		95781	
						chr		A3	
						D. WHITING		type	
						6/07/95		Product Customer Drawing	
sheet index		revision sheet							

PDS: Rev :AGSTATUS:ReleasedPrinted: Feb 17, 2012

