



RECOMMENDED CABLE STRIPPING AND CRIMPING DIMENSIONS

- NOTES:
- 1. BODY: COPPER ALLOY, NICKEL PLATED.
 - 2. CONTACT PIN: COPPER ALLOY, GOLD PLATED.
 - 3. SPRING: BERYLLIUM COPPER, NICKEL PLATED.
 - 4. TINE CONTACT: BERYLLIUM COPPER, GOLD PLATED.
 - 5. INSULATOR: TEFLON
 - 6. FERRULE: COPPER ALLOY, NICKEL PLATED.
 - 7. CHARACTERISTIC IMPEDANCE: 75 OHMS, 3 GHz BANDWIDTH.
 - 8. RETURN LOSS: MEETS HDTV SMPTE 424M SPECIFICATION.
 - 9. DIMENSIONS ARE FOR REFERENCE ONLY.
 - 10. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

| | | | | | | | | | | | | |
|-----------|------------|----------|----|------|---|--|-----------------|-----------------|-----------------------|-------------------------|--|---|
| | | | | | <div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div> | THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY. | | | | | | |
| | | | | | | SIZE * | WIDTH * | MULT * | LBS/M * | TEMPER * | | |
| | | | | | | FINISH * | | | MATERIAL SEE NOTES | | | |
| | | | | | | SPEC No. * | | | SPEC No. * | | | |
| | | | | | | FIRST USED ON * | | SCALE 4:1 | | <div>Switchcraft®</div> | | |
| B | 26729 | 01/24/12 | TS | BDS | | DATE DRAWN | BY | CHKD | APVD | | | |
| A | 26641 | 11/24/10 | ZS | SRC | 04/29/10 | ZS | 04/29/10 SRC | 04/29/10 SRC | SHEET 1 OF 1 | | | |
| REV | ECO NUMBER | DATE | BY | APVD | NAME | | | | PART No. | REV | | |
| REVISIONS | | | | | DO NOT SCALE DRAWING | DIN 1.0/2.3 PLUG, 75 OHMS, RoHS | | | | DIN1694A | | B |