



PRODUCT NUMBER

20020037-XXXXXXLF

20020037-□ □ □ □ B 0 □ L F

PITCH

G: 5.00 mm

H: 5.08 mm

POLES

02: 2 POLES

03: 3 POLES

⋮

24: 24 POLES

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

PROPERTY TABLE

PROPERTY TABLE				
FCI SERIES NAME		35-500	35-508	
PITCH (mm)		5.00	5.08	
VOLTAGE RATING (VAC)		300	300	
CURRENT RATING (A)		10	10	
APPLICABLE WIRE RANGE (AWG)	1-WIRE	12~26	12~26	
	2-WIRE	NA	NA	
WIRE CROSS SECTION (mm ²)	SOLID	1-WIRE	2.5	2.5
		2-WIRE	NA	NA
	STRANDED	1-WIRE	2.5	2.5
		2-WIRE	NA	NA
OPENING CONTACT HOUSING(mm ²)		2.4x3.0	2.2x3.0	
WIRE STRIP LENGTH(mm)		9~10	9~10	
WITHSTANDING VOLTAGE (kV)		1.6	1.6	
OPERATING TEMP. (°C)		-40~+115	-40~+115	
POLES AVAILABLE		02~24	02~24	
SAFETY CERTIFICATE				




NOTES:

1. MATERIALS

- 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-2 INSULATING LEVER: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-3 WIRE GUARD : STAINLESS STEEL.
- 1-4 TERMINAL: COPPER ALLOY, TIN PLATED.
2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.
3. PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.
4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.
5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.


mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
A	T11-0004	WL	011811	angles	X.±0.5	MM	TERMINAL BLOCK PLUGGABLE SIGNAL PLUG, UPSIDE CONTACT WITHOUT FLANGE	
B	T-005306	WL	082311	hole	X.X±0.3	[INCH]		
				X*±1"	X.XX±0.1	scale	dwg no	
				dr	WENDY CHEN	122310	sheet 1 of 3	
				enr	JASON HSU	122310	20020037	
				chr	JASON HSU	122310	A4	
				appd	JASON HSU	122310	type	
sheet index		revision sheet	B 1	B 2	B 3		CUSTOMER Drawing	

PRODUCT NUMBER	SERIES NAME	PITCH
20020037-GXXXXXXLF	35-500	5.00 mm






N = Number of poles
 DIM. L = $(N \times 5.0[.197]) + 0.1[.004]$
 DIM. P = $(N - 1) \times 5.0[.197]$
 DIM. T = $N \times 5.0[.197]$

Poles	Dim. L & P & T
2-6p	$\pm 0.15[.006]$
7-12p	$\pm 0.20[.008]$
13-18p	$\pm 0.25[.010]$
19-24p	$\pm 0.30[.012]$




mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																
ltr	ecn	no	dr	date	tolerances unless otherwise specified										title																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
B					angles	linea	X.±0.5		MM	TERMINAL BLOCK																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																
							X.X±0.3		[INCH]	PLUGGABLE SIGNAL PLUG, UPSIDE CONTACT																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																
							X'±1"	X.XX±0.1	scale	WITHOUT FLANGE																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																
					dr	WENDY CHEN	122310																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			</

PRODUCT NUMBER	SERIES NAME	PITCH
20020037-HXXXXXXLF	35-508	5.08 mm




N = Number of poles
DIM. L=(N×5.08[.200])
DIM. P=(N-1)×5.08[.200]

POLES	Dim. L & P
2-6p	±0.15[.006]
7-12p	±0.20[.010]
13-16p	±0.30[.012]
17-24p	±0.40[.016]



SECTION A-A



2P mark

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
B				angles	X.±0.5 X.X±0.3 X°±1°	MM [INCH]	TERMINAL BLOCK PLUGGABLE SIGNAL PLUG, UPSIDE CONTACT WITHOUT FLANGE
				dr	WENDY CHEN 122310	scale	dwg no
				enr	JASON HSU 122310	FCI	sheet 3 of 3
				chr	JASON HSU 122310		20020037
				appd	JASON HSU 122310		A4
sheet index	revision sheet					type	CUSTOMER Drawing