



Features

- SMD Single-Turn / Cermet / Industrial Open Frame
- Cross slot rotor designs suitable for automatic adjustment equipment
- Supplied in 12mm embossed tape, compatible with automatic pick-and-place assembly equipment

- Recommended for reflow solder processing only

3364 - 4mm Square Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range
.....100 ohms to 1 megohm
(see standard resistance table)
Resistance Tolerance±25% std.
End Resistance
<1K20 ohms max.
>1K2%
Contact Resistance Variation
(Voltage Divider)5% max.
ResolutionInfinite
Adjustment Angle260°±20°

Environmental Characteristics

Power Rating (50 volts max.)
70°C0.2 watt
Temperature Range
.....-40°C to +125°C
Temperature Coefficient
.....±250ppm/°C
Humidity500 hours (5% ΔTR)
Load Life500 hours
0.2 watt @ 70°C (5% ΔTR)
Rotational Life20 cycles (15% ΔTR)

Physical Characteristics




Torque20 to 200g-cm
Mechanical AngleContinuous
MarkingResistance code,
manufacturer's full part number
and date code on packaging
TerminalsSolder coated
Standard Packaging
.....1000 pcs./7" reel
Adjustment ToolH-90
Reflow solder processing recommended

How To Order



3364 X - 1 - 103 E

Model _____
Style _____
Orientation of parts in tape:
Styles W,A
Terminals toward sprocket holes
Styles X,B
Terminals away from sprocket holes
Standard Product _____
Resistance Code _____
Embossed Tape Designator _____
E = 1000 pcs./7" reel (-1 standard)
G = 5000 pcs./14.5" reel (-1 optional)
Consult factory for other available options.

Common Dimensions
3364W, X
3-Terminal






SUGGESTED PWB LAYOUT




TOLERANCES: ± 0.25 (.010) EXCEPT WHERE NOTED

DIMENSIONS ARE: METRIC
(INCHES)

3364A, B
3-Terminal





SUGGESTED PWB LAYOUT



3364 - 4mm Square Trimming Potentiometer

BOURNS®

Packaging Specifications



Conforms with EIA specification RS-481.

Standard Resistance Table

Resistance (Ohms)	Resistance Code	Part Marking
100	101	12
200	201	22
500	501	52
1,000	102	13
2,000	202	23
5,000	502	53
10,000	103	14
20,000	203	24
50,000	503	54
100,000	104	15
200,000	204	25
500,000	504	55
1,000,000	105	16

Popular values listed in boldface. Special resistances available.