

Heyco®-Tite EMC Brass Liquid Tight Cordgrips

Straight-Thru, Metric Hubs

EMC Nickel-Plated Brass with Contact Sleeve

The Ultimate in Liquid Tight Strain Relief Protection



CABLE DIA. RANGE		PART NO.	THREAD SIZE	UL or CSA	PART DIMENSIONS		D Wrenching Nut Flat Size
Minimum	Maximum				A Clearance Hole Dia.	B Max. O.A. Length	
in.	mm.	in.	mm.	in.	mm.	in.	mm.

Standard Thread

.098	2,5	.138	3,5	4613	M8 x 1,25	UL CSA	.315	8,0	.94	24,0	.39	10,0	.43	11,0
.118	3,0	.157	4,0	4614	M8 x 1,25	UL CSA	.315	8,0	.94	24,0	.39	10,0	.43	11,0
.118	3,0	.157	4,0	4615	M10 x 1,5	UL CSA	.394	10,0	.98	25,0	.39	10,0	.51	13,0
.157	4,0	.236	6,0	4616	M10 x 1,5	UL CSA	.394	10,0	.98	25,0	.39	10,0	.51	13,0
.177	4,5	.236	6,0	4618	M12 x 1,5	UL CSA	.472	12,0	1.06	27,0	.39	10,0	.59	15,0
.236	6,0	.295	7,5	4619	M12 x 1,5	UL CSA	.472	12,0	1.06	27,0	.39	10,0	.59	15,0
.236	6,0	.312	8,0	4622	M16 x 1,5	UL CSA	.630	16,0	1.18	30,0	.39	10,0	.71	18,0
.315	8,0	.394	10,0	4623	M16 x 1,5	UL CSA	.630	16,0	1.26	32,0	.39	10,0	.71	18,0
.315	8,0	.433	11,0	4625	M20 x 1,5	UL CSA	.787	20,0	1.22	31,0	.39	10,0	.94	24,0
.433	11,0	.551	14,0	4626	M20 x 1,5	UL CSA	.787	20,0	1.30	33,0	.39	10,0	.94	24,0
.512	13,0	.630	16,0	4628	M25 x 1,5	UL CSA	.984	25,0	1.41	36,0	.43	11,0	1.18	30,0
.630	16,0	.748	19,0	4629	M25 x 1,5	UL CSA	.984	25,0	1.53	39,0	.43	11,0	1.18	30,0
.709	18,0	.827	21,0	4631	M32 x 1,5	UL CSA	1.260	32,0	1.65	42,0	.51	13,0	1.42	36,0
.827	21,0	.984	25,0	4632	M32 x 1,5	UL CSA	1.260	32,0	1.65	42,0	.51	13,0	1.42	36,0




Short Thread — ALL NEW PRODUCTS!

.098	2,5	.138	3,5	14613	M8 x 1,25	UL CSA	.315	8,0	.75	19,0	.20	5,0	.43	11,0
.118	3,0	.157	4,0	14614	M8 x 1,25	UL CSA	.315	8,0	.75	19,0	.20	5,0	.43	11,0
.118	3,0	.157	4,0	14615	M10 x 1,5	UL CSA	.394	10,0	.79	20,0	.20	5,0	.51	13,0
.157	4,0	.236	6,0	14616	M10 x 1,5	UL CSA	.394	10,0	.79	20,0	.20	5,0	.51	13,0
.177	4,5	.236	6,0	14618	M12 x 1,5	UL CSA	.472	12,0	.87	22,0	.20	5,0	.59	15,0
.236	6,0	.295	7,5	14619	M12 x 1,5	UL CSA	.472	12,0	.87	22,0	.20	5,0	.59	15,0
.236	6,0	.312	8,0	14622	M16 x 1,5	UL CSA	.630	16,0	.98	25,0	.20	5,0	.71	18,0
.315	8,0	.394	10,0	14623	M16 x 1,5	UL CSA	.630	16,0	1.06	27,0	.20	5,0	.71	18,0
.315	8,0	.433	11,0	14625	M20 x 1,5	UL CSA	.787	20,0	1.06	27,0	.24	6,0	.94	24,0
.433	11,0	.551	14,0	14626	M20 x 1,5	UL CSA	.787	20,0	1.10	29,0	.24	6,0	.94	24,0
.512	13,0	.630	16,0	14628	M25 x 1,5	UL CSA	.984	25,0	1.26	32,0	.28	7,0	1.18	30,0
.630	16,0	.748	19,0	14629	M25 x 1,5	UL CSA	.984	25,0	1.38	35,0	.28	7,0	1.18	30,0
.709	18,0	.827	21,0	14631	M32 x 1,5	UL CSA	1.260	32,0	1.46	37,0	.31	8,0	1.42	36,0
.827	21,0	.984	25,0	14632	M32 x 1,5	UL CSA	1.260	32,0	1.46	37,0	.31	8,0	1.42	36,0

Short Thread, High Temperature*

.236	6,0	.315	8,0	4609	M16 x 1,5	UL CSA	.630	16,0	.98	25,0	.20	5,0	.71	18,0
------	-----	------	-----	------	-----------	--------	------	------	-----	------	-----	-----	-----	------

*Special sealing gland rated to 200°C (392°F).



Material	Nickel-Plated Brass W/TPE Sealing Gland
Certifications	UL CSA Recognized under the Component Program of Underwriters' Laboratories File E51579 to both Canadian and U.S. requirements
Temperature Range	-40°F (-40°C) to 212°F (100°C)
IP Rating	IP 68, IP 69K

Quick Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[4613](#) [4629](#) [4623](#) [4631](#) [4619](#) [4622](#) [4626](#) [4618](#) [4615](#) [4616](#) [4628](#) [4625](#) [4614](#) [4632](#) [14629](#) [14632](#) [14616](#)
[14618](#) [14628](#) [14622](#) [14623](#) [14614](#) [14619](#) [14615](#) [14626](#) [14613](#) [14625](#) [14631](#) [4609](#)