




FCIconnect.com

Copyright FCI

PRODUCT NO

SEE TABLE



mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406		CARD CONN
					ISO 1101		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
G	V31271	MRC	2/10/94	angles	linear	INCH/MM	1X.100/2.54 HORIZ.
H	V61635	MDF	11/21/96				CARD CONN. , 30 Au
J	V70995	JM	10/19/97	0' $\pm$ 2'		scale 4:1	
K	V02518	MDF	10/24/00	dr	B.ASHRAFI	10/8/81	dwg no
L	M05-0199	ERE	09/15/05	enrg	D.NEIDICH	10/12/81	sheet 1 of 4 size
M	M06-0210	MHT	6/03/06	chr	R. ALTHOUSE	4/13/82	A3
				appd	D.NEIDICH	10/12/81	type
sheet	revision	M	M	M	M		Product Customer Drawing
index	sheet	1	2	3	4		

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO
SEE TABLE




FIGURE 1
SCALE 4:1

NOTES

- ①. HOUSING MATERIAL:
FILLED HIGH TEMPERATURE NYLON
COLOR. BLACK
- ②. TERMINAL MATERIAL:
BODY: BRASS. .010/.25 THICK.
SPRING: BE-CU. HEAT-TREATED.
BODY PLATING: 30u"/.76u GOLD OVER 50u"/1.27u Ni
IN CONTACT AREA.
SPRING PLATING: GOLD FLASH
3. MARK FCI PART NUMBER AND DATE CODE LEGIBLE
ON TUBE LABEL.
4. APPLICATION INFORMATION.
A. RECOMMENDED MOUNTING HOLE PATTERN IS
SHOWN IN FIGURE #1.
B. ALL MATING PINS TO BE .025/.64 SQUARE ON
TRUE CENTER OF GIVEN TERMINAL SPACINGS
WITHIN .015/.38 DIA.
C. SUGGESTED MATING PIN LENGTH
.350±.020/8.89±.51.
- ⑤. ADD "LF" SUFFIX AT THE END OF PART NUMBER
FOR LEAD FREE OPTION.
- ⑥. THESE PRODUCT MEET EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN
GS-22-008.
7. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER,
INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family CARD CONN
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
M				angles	linear		1X.100/2.54 HORIZ. CARD CONN. , 30 Au
				0°±2'			dwg no
							sheet 2 of 4 size
				dr	B.ASHRAFI	10/8/81	66945
				enr	D.NEIDICH	10/12/81	A3
				chr	R. ALTHOUSE	4/13/82	
				appd	D.NEIDICH	10/12/81	
sheet	revision						type
index	sheet						Product Customer Drawing



FCIconnect.com

Copyright FCI

PRODUCT NO SEE TABLE	NO. OF POS.	DIM A	DIM B	LEAD FREE OPTION
66945-001		DISCONTINUED		NOTE 5
-002	1X2	.10/2.54	.24/6.10	
-003	1X3	.20/5.08	.34/8.64	
-004	1X4	.30/7.62	.44/11.18	
-005	1X5	.40/10.16	.54/13.72	
-006	1X6	.50/12.70	.64/16.26	
-007	1X7	.60/15.24	.74/18.80	
-008	1X8	.70/17.78	.84/21.34	
-009	1X9	.80/20.32	.94/23.88	
-010	1X10	.90/22.86	1.04/26.42	
-011	1X11	1.00/25.40	1.14/28.96	
-012	1X12	1.10/27.94	1.24/31.50	
-013	1X13	1.20/30.48	1.34/34.04	
-014	1X14	1.30/33.02	1.44/36.58	
-015	1X15	1.40/35.56	1.54/39.12	
-016	1X16	1.50/38.10	1.64/41.66	
-017	1X17	1.60/40.64	1.74/44.20	
-018	1X18	1.70/43.18	1.84/46.74	
-019	1X19	1.80/45.72	1.94/49.28	
-020	1X20	1.90/48.26	2.04/51.82	
-021	1X21	2.00/50.80	2.14/54.36	
-022	1X22	2.10/53.34	2.24/56.90	
-023	1X23	2.20/55.88	2.34/59.44	
-024	1X24	2.30/58.42	2.44/61.98	
-025	1X25	2.40/60.96	2.54/64.52	
-026	1X26	2.50/63.50	2.64/67.06	
-027	1X27	2.60/66.04	2.74/69.60	
-028	1X28	2.70/68.58	2.84/72.14	
-029	1X29	2.80/71.12	2.94/74.68	
-030	1X30	2.90/73.66	3.04/77.22	
-031	1X31	3.00/76.20	3.14/79.76	
-032	1X32	3.10/78.74	3.24/82.30	
-033	1X33	3.20/81.28	3.34/84.84	
-034	1X34	3.30/83.82	3.44/87.38	
-035	1X35	3.40/86.36	3.54/89.92	
-036	1X36	3.50/88.90	3.64/92.46	
-037	1X37	3.60/91.44	3.74/95.00	
-038	1X38	3.70/93.98	3.84/97.54	
-039	1X39	3.80/96.52	3.94/100.08	
66945-040	1X40	3.90/99.06	4.04/102.62	NOTE 5

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family CARD CONN
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 4:1 	title
M				angles	linear		1X.100/2.54 HORIZ. CARD CONN. , 30 Au
				0°±2'			
				dr	B.ASHRAFI	10/8/81	dwg no
				enr	D.NEIDICH	10/12/81	sheet 3 of 4 size
				chr	R. ALTHOUSE	4/13/82	66945 A3
				appd	D.NEIDICH	10/12/81	type Product Customer Drawing
sheet index	revision sheet						



FCIconnect.com

Copyright FCI

form: A3

PRODUCT NO SEE TABLE	NO. OF POS.	DIM A	DIM B	SPECIAL INFORMATION	LEAD FREE OPTION
66945-041	1X41	4.00/101.60	4.14/105.16		NOTE 5
-042	1X42	4.10/104.14	4.24/107.70		
-043	1X43	4.20/106.68	4.34/110.24		
-044	1X44	4.30/109.22	4.44/112.78		
-045	1X45	4.40/111.76	4.54/115.32		
-046	1X46	4.50/114.30	4.64/117.86		
-047	1X47	4.60/116.84	4.74/120.40		
-048	1X48	4.70/119.38	4.84/122.94		
-049	1X49	4.80/121.92	4.94/125.48		
-050	1X50	4.90/124.46	5.04/128.02		
-051	1X51	5.00/127.00	5.14/130.56		
-052	1X52	5.10/129.54	5.24/133.10		
-800	1X24	2.30/58.42	2.44/61.98	CUSTOMER RESTRICTED	NOTE 5
66945-801	1X48	4.70/119.4	4.84/12.29		

OBSOLETE
OBSOLETE

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family CARD CONN		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
M					angles	linear	INCH/MM	1X.100/2.54 HORIZ. CARD CONN. , 30 Au	
					0°±2°		scale 4:1	dwg no	sheet 4 of 4
					dr	B.ASHRAFI	10/8/81	66945	A3
					enr	D.NEIDICH	10/12/81		
					chr	R. ALTHOUSE	4/13/82		
					appd	D.NEIDICH	10/12/81		
sheet index	revision sheet							type	Product Customer Drawing